


tML<sup>®</sup> - FO Fan-out Cable MPO/MTP<sup>®</sup> w. Pins/6x E2000 UPC Compact 12E9/125 $\mu$  LSOH, Length: xx



## tML<sup>®</sup> - tde Modular Link

tML<sup>®</sup> is a patented, modular cabling system consisting of the three key components module, trunk cable and rack mount enclosure. The system components are 100 percent manufactured, pre-assembled and tested in Germany. They enable plug-and-play installation on site – especially in data centres, but also in industrial environments – within the shortest possible time. Heart of the system are the rear MPO/MTP<sup>®</sup> and Telco connectors, which can be used to connect at least six or twelve ports at a time. Depending on the module configuration, transfer rates of up to 200G are currently possible with SR4. The fibre optic and TP modules can be used together in a module carrier with a very high port density. The tde offers its tML<sup>®</sup> cabling system as a proven tML<sup>®</sup> standard system and in the highly innovative variants tML<sup>®</sup> Xtended, tML<sup>®</sup> 24 System and now tML<sup>®</sup> 32 System for extreme scalability and very easy migration to higher transmission rates such as 40G, 100G, 200G and 400G.

The tML<sup>®</sup> - FO Fan-out Cable MPO/MTP<sup>®</sup> is for the use with tML<sup>®</sup>- FO Trunk Cables.



**tde<sup>®</sup> trans data elektronik GmbH**

**Headquarter address:**

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

**Sales office address:**

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 914 36 99  
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

tML<sup>®</sup> - FO Fan-out Cable MPO/MTP<sup>®</sup> w. Pins/6x E2000 UPC Compact 12E9/125 $\mu$  LSOH, Length: xx

## Technical Data

The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP<sup>®</sup> plug has a defined fiber height of 1 - 3.5 $\mu$ . The max. adjacent fiber height difference is 0.2 $\mu$ m and for all fibers 0.3 $\mu$ m. All system components (fan-out cables or modules, trunk cables and patch cords) are co-ordinated for the reaching of the performance particularly. The fanout cable is marked with sequential serial number and article number.

Cable	Round cable, loose tube, LSOH, yellow
Fan-out unit	Metal
Entry	1 x MPO/MTP <sup>®</sup> Male Push Pull (green)
Exit	6 x E2000 UPC Compact (blue)
Pin-out	Crossover (TIA/EIA-568-B.1 Methode C)
Tests	Interferometer, Insertion Loss, Return Loss and Visual Final Inspection; all measured values are electronically archived
	QS-Managementsystem ISO 9001, ISO 14001 and TL 9000

## FO Connectors

Type	E2000 UPC Compact
Ferrule	Ceramic
Ferrule Hole	125.5 $\mu$
Ferrule Concentricity	$\leq 0.6 \mu$
Connector colour	Blue
Lever colour	Blue
Boot colour	Blue
Manufacturer	RDM

## Optical performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
9/125 $\mu$	E2000 UPC	1550 nm	$\leq 0.10$ dB	0.25 dB	55 dB

## FO Connectors

The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP<sup>®</sup> plug has a defined fiber height of 1 - 3.5 $\mu$ . The max. adjacent fiber height difference is 0.2 $\mu$ m and for all fibers 0.3 $\mu$ m.

## Connector

Type	MPO/MTP <sup>®</sup> APC Male Push Pull Locking with Elite Pins (green)
Ferrule	12 Fiber SM Elite <sup>®</sup> ferrule, PPS
Boot colour	Black
Temperature range	-40°C bis +75°C
Manufacturer	tde/US Conec

tML<sup>®</sup> - FO Fan-out Cable MPO/MTP<sup>®</sup> w. Pins/6x E2000 UPC Compact 12E9/125 $\mu$  LSOH, Length: xx

## Optical Performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
9/125 $\mu$ OS2	MPO/MTP <sup>®</sup> APC	1310 / 1550 nm	$\leq$ 0.10 dB	0.20 dB	75 dB

## FO Fan-Out

Length Fan-Out	40 mm
Max. $\varnothing$ Fan-Out	10 mm
Parallel connectors	12

## FO Cables

Standards	EN 50173-5
	IEC 60794-2-20
	ISO/IEC 24764
Flame resistance	IEC 60332-1-2
	IEC 60332-2-2
	IEC 60754-1
	IEC 60754-2
	IEC 61034

## Cable construction

Type	IVH12E09
Loose tube	12 coated fibers within PVC-core tube
Fiber type	SM-G652D, 9/125 $\mu$ , Corning SMF-28e+, OS2
Strength members	Aramid yarn
Outer jacket	LSZH (Halogen free, low smoke, flame retardant thermoplastic compound)
Jacket color	Yellow, RAL 1021
Identification	"t d e – IVH12E09–MPO LSZH" and sequential meter marking + Lot number

## Physical properties

Outer diameter cable	3.0 $\pm$ 0.1 mm
Diameter PVC-core tube	1.8 $\pm$ 0.1 mm
Wall thickness PVC-core tube	0.35 mm – 0.40 mm
Max. tensile load	300 N
Min. bending radius	30 mm
Temperature range (storage, installation, operation)	-20°C to +70°C

## FO Fiber

tML<sup>®</sup> - FO Fan-out Cable MPO/MTP<sup>®</sup> w. Pins/6x E2000 UPC Compact 12E9/125 $\mu$  LSOH, Length: xx

Type	Corning SMF-28e+ <sup>®</sup> 09/125 $\mu$ OS2 G.652.D singlemode fiber
Maximum Attenuation	At 1310 nm max. 0.33 - 0.35 dB/km At 1383 $\pm$ 3 nm max. 0.31 - 0.35 dB/km At 1490 nm max. 0.21 - 0.24 dB/km At 1550 nm max. 0.19 - 0.20 dB/km At 1625 nm max. 0.20 - 0.23 dB/km
Attenuation vs. Wavelength	Range: 1285 - 1330 nm; Ref. $\lambda$ : 1310 nm; Max. Difference: 0.03 dB/km Range: 1525 - 1575 nm; Ref. $\lambda$ : 1550 nm; Max. Difference: 0.02 dB/km
Macrobend Loss	Mandrel Diameter:32mm; Number of Turns: 1; Wavelength: 1550nm; Induced Attenuation: $\leq$ 0.03 dB Mandrel Diameter:50mm; Number of Turns: 100; Wavelength: 1310nm; Induced Attenuation: $\leq$ 0.03 dB Mandrel Diameter:50mm; Number of Turns: 100; Wavelength: 1550nm; Induced Attenuation: $\leq$ 0.03 dB Mandrel Diameter:60mm; Number of Turns: 100; Wavelength: 1625nm; Induced Attenuation: $\leq$ 0.03 dB
Point Discontinuity	Wavelength: 1310 nm; Point Discontinuity: $\leq$ 0.05 dB Wavelength: 1550 nm; Point Discontinuity: $\leq$ 0.05 dB
Cable Cutoff Wavelength ( $\lambda_{ccf}$ )	$\lambda_{ccf} \leq 1260$ nm
Mode-Field Diameter	At 1310 nm = $9.2 \pm 0.4$ $\mu$ m At 1550 nm = $10.4 \pm 0.5$ $\mu$ m
Dispersion	At 1550 nm = $\leq 18.0$ [ps/(nm*km)] At 1625 nm = $\leq 22.0$ [ps/(nm*km)]
	Zero Dispersion Wavelength ( $\lambda_0$ ): 1310 nm $\leq \lambda_0 \leq$ 1324 nm Zero Dispersion Slope ( $S_0$ ): $\leq 0.092$ ps/(nm <sup>2</sup> *km)
Polarization Mode Dispersion (PMD)	PMD Link Design Value = $\leq 0.06$ ps/ $\sqrt$ km Maximum Individual Fiber = $\leq 0.1$ ps/ $\sqrt$ km
Norm	ITU-T Recommendation G.652 (Tables A, B, C, and D) IEC Specifications 60793-2-50 Type B1.3 TIA/EIA 492-CAAB Telcordia Generic Requirements GR-20-CORE ISO 11801 OS2

## Dimensional Specifications

Fiber Curl	$\geq 4.0$ m radius of curvature
Cladding Diameter	$125.0 \pm 0.7$ $\mu$ m
Core-Clad Concentricity	$\leq 0.5$ $\mu$ m
Cladding Non-Circularity	$\leq 0.7\%$
Coating Diameter	$242 \pm 5$ $\mu$ m
Coating-Cladding Concentricity	$< 12$ $\mu$ m

## Environmental Specifications

Environmental Test	Test Condition	Induced Attenuation 1310 nm, 1550 nm & 1625 nm
Temperature Dependence	-60°C to +85°C	$\leq 0.05$
Temperature Humidity Cycling	-10°C to +85°C up to 98% RH	$\leq 0.05$
Water Immersion	23°C $\pm$ 2°C	$\leq 0.05$
Heat Aging	85°C $\pm$ 2°C	$\leq 0.05$
Operating Temperature Range	-60°C to +85°C	

tML<sup>®</sup> - FO Fan-out Cable MPO/MTP<sup>®</sup> w. Pins/6x E2000 UPC Compact 12E9/125 $\mu$  LSOH, Length: xx

## Mechanical Specifications

Proof Test	The entire fiber length is subjected to a tensile stress $\geq$ 100 kpsi (0.7 GPa).
Length	Fiber lengths available up to 63.0 km/spool.

## Performance Characterizations

Core Diameter	8.2 $\mu$ m
Numerical Aperture	0.14
Zero Dispersion Wavelength ( $\lambda_0$ )	1317 nm
Zero Dispersion Slope ( $S_0$ )	0.088 ps/(nm <sup>2</sup> *km)
Effective Group Index of Refraction	1310 nm: 1.4676 1550 nm: 1.4682
Fatigue Resistance Parameter (nd)	20
Coating Strip Force	Dry: 0.6 lbs (3N) Wet: 14 days room temperature: 0.6 lbs (3N)
Rayleigh Backscatter Coefficient (for 1 ns Pulse Width)	1310 nm: -77 dB 1550 nm: -82 dB

## Product variants & accessories

Art.-No.	Description
TMLE2AC/MPP09I12Exx	tML <sup>®</sup> - FO Fan-out Cable MPO/MTP <sup>®</sup> w. Pins/6x E2000 APC Compact 12E9/125 $\mu$ LSOH, Length: xx
TMLE2C/MPP09I12Exx	tML <sup>®</sup> - FO Fan-out Cable MPO/MTP <sup>®</sup> w. Pins/6x E2000 UPC Compact 12E9/125 $\mu$ LSOH, Length: xx
TMLE2C/MPP50I12G3-xx	tML <sup>®</sup> - FO Fan-out Cable MPO/MTP <sup>®</sup> w. Pins/6x E2000 Compact 12G50/125 $\mu$ OM3 LSOH, Length: xx
TMLE2C/MPP50I12G4-xx	tML <sup>®</sup> - FO Fan-out Cable MPO/MTP <sup>®</sup> w. Pins/6x E2000 Compact 12G50/125 $\mu$ OM4 LSOH, Length: xx
TMLE2C/MPP50I12Gxx	tML <sup>®</sup> - FO Fan-out Cable MPO/MTP <sup>®</sup> w. Pins/6x E2000 Compact 12G50/125 $\mu$ OM2 LSOH, Length: xx
TMLE2C/MPP62I12Gxx	tML <sup>®</sup> - FO Fan-out Cable MPO/MTP <sup>®</sup> w. Pins/6x E2000 Compact 12G62,5/125 $\mu$ OM1 LSOH, Length: xx