

tML<sup>®</sup> 24 - FO Micro Distribution Trunk Cable both sides 1x 24F MPO w. Pins 24G50/125µ OM4 LSHF,  
Type A, Length: xx in m



## tML<sup>®</sup> tde Modular Link

tML<sup>®</sup> is a patented, modular cabling system consisting of the three key components module, trunk cable and rack mount enclosure. The system components are 100 percent manufactured, pre-assembled and tested in Germany. They enable plug-and-play installation on site – especially in data centres, but also in industrial environments – within the shortest possible time. Heart of the system are the rear MPO/MTP<sup>®</sup> and Telco connectors, which can be used to connect at least six or twelve ports at a time. Depending on the module configuration, transfer rates of up to 400G are currently possible with SR4. The fibre optic and TP modules can be used together in a module carrier with a very high port density. The tde offers its tML<sup>®</sup> cabling system as a proven tML<sup>®</sup> standard system and in the highly innovative variants tML<sup>®</sup> 12, tML<sup>®</sup> 24, tML<sup>®</sup> 32 and now tML<sup>®</sup> 24+ System for extreme scalability and very easy migration to higher transmission rates such as 40G, 100G, 200G, 400G and 800G and more.

The tML<sup>®</sup> - FO Micro Distribution trunk cable is intended for the connection of two tML<sup>®</sup> 24 - FO Modules.



**tde<sup>®</sup> trans data elektronik GmbH**

**Headquarter address:**

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

**Sales office address:**

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 8805 61 13  
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

tML<sup>®</sup> 24 - FO Micro Distribution Trunk Cable both sides 1x 24F MPO w. Pins 24G50/125 $\mu$  OM4 LSHF, Type A, Length: xx in m

## Technical Data

The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP<sup>®</sup>plug has a defined fiber height of 1 - 3.5 $\mu$ . The max. adjacent fiber height difference is 0.2 $\mu$ m and for all fibers 0.3 $\mu$ m.

|            |  |
|------------|--|
| Cable      | Round cable 3.6 mm, loose tube, LSOH, magenta  |
| Connectors | MPO/MTP <sup>®</sup> Push Pull (magenta)   |
| Pin out    | Type A   |
| Tests      | Interferometer, Insertion Loss, Return Loss and Visual Final Inspection; all measured values are electronically archived |
|            | QS-Managementsystem ISO 9001, ISO 14001 and TL 9000  |

## FO Connectors

The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP<sup>®</sup> plug has a defined fiber height of 1 - 3.5 $\mu$ . The max. adjacent fiber height difference is 0.2 $\mu$ m and for all fibers 0.3 $\mu$ m.

### Connector

|                   |   |
|-------------------|---|
| Type              | MPO/MTP <sup>®</sup> Male Push Pull Locking with Elite Pins (magenta) |
| Ferrule           | 24 Fiber MM Elite <sup>®</sup> ferrule, PPS                           |
| Boot colour       | Red   |
| Temperature range | -40°C to +75°C  |
| Manufacturer      | tde/US Conec  |

### Optical Performance

| Fiber            | Type                 | Wavelength | Insertion loss typ. | Insertion loss max. | Return loss min. |
|------------------|----------------------|------------|---------------------|---------------------|------------------|
| 50/125 $\mu$ OM4 | MPO/MTP <sup>®</sup> | 850 nm     | ≤ 0.12 dB           | 0.25 dB             | 35 dB            |

## FO Cables

|           |                |
|-----------|----------------|
| Standards | EN 50173-5     |
|           | IEC 60794-2-20 |
|           | ISO/IEC 24764  |

### Construction

|       |  |
|-------|--|
| Type  | IVH24G50-OM4   |
| Fiber | 24 primary coated fibres nominally 242 $\mu$ m, arranged in 2 groups of 12 fibres,<br>Group 1: Red id tread<br>Group 2: Green id tread |

tML<sup>®</sup> 24 - FO Micro Distribution Trunk Cable both sides 1x 24F MPO w. Pins 24G50/125 $\mu$  OM4 LSHF,  
Type A, Length: xx in m

|                 |   |
|-----------------|---|
| Fiber colors    | According to TIA/EIA 598-C also in agreement with IEC 60304:<br>1-12: Blue, orange, green, brown, grey, white, red, black, yellow, violet, pink and aqua<br>13-24: Blue, orange, green, brown, grey, white, red, transparent, yellow, violet, pink and aqua (with add. ring mark) |
| Strength member | Ultra high modulus Aramid yarns   |
| Sheath          | Halogen free, flame resistant thermoplastic sheathing compound acc. to EN 50290-2-27, UV stabilised   |
| Sheath colors   | Magenta, RAL 4003   |

## Fire rating

|               |                 |
|---------------|-----------------|
| IEC 60332-1-2 | Pass            |
| IEC 60332-2-2 | Pass            |
| IEC 60754-1   | No halogens     |
| IEC 60754-2   | No acid matters |
| IEC 61034-2   | No dense smoke  |

## Heat of combustion

|           |           |
|-----------|-----------|
| 200 MJ/km | 0.5 KWh/m |
|-----------|-----------|

## Physical properties IEC60974-1-2

|                              |   |
|------------------------------|---|
| Outer diameter cable         | $\varnothing$ 3.6 mm +0.1 mm -0.3 mm                                |
| Diameter PVC-core tube       | 2.0 $\pm$ 0.1 mm  |
| Wall thickness PVC-core tube | 0.35 mm – 0.40 mm   |
| Weight                       | 11 kg/km  |
| Tensile strength (dynamic)   | 220 N   |
| Tensile strength (permanent) | 110 N   |
| Compressive strength (crush) | 400 N   |
| Impact                       | 4 Nm, R= 12.5 mm  |
| Kink                         | No Kink   |
| Min. Bending radius          | R = 20 mm   |
| Temperature range            | Operation and installation: -0°C to 50°C.<br>Storage: -20°C to 50°C |

## FO Fiber

|                                   |  |
|-----------------------------------|--|
| Type                              | Corning ClearCurve <sup>®</sup> 50/125 $\mu$ OM4 multimode fiber   |
| Optimized Data Rate over Distance | 40/100 Gb over 170 m*<br>10 Gb/s over 550 m<br>1 Gb/s over 1100 m  |
| Standard Compliance               | ISO/IEC 11801: type OM4 fiber**<br>IEC 60793-2-10: type A1a.3 fiber**<br>TIA/EIA: 492AAAD<br>ITU: ITU G651.1 |

tML<sup>®</sup> 24 - FO Micro Distribution Trunk Cable both sides 1x 24F MPO w. Pins 24G50/125 $\mu$  OM4 LSHF,  
Type A, Length: xx in m

|    |  |
|----|--|
| *  | Distances specified in the 40G/100G per IEEE 802.3ba standard are 150m on OM4 and 100m on OM3; Corning fibers are manufactured to tighter dispersion specifications and thereby support the extended distances shown in the table (assuming cable attenuation $\leq$ 3.0 dB/km and same 1.0 dB of connector loss for OM3 that the standard requires for OM4) |
| ** | Assumes IEC draft standard is harmonized with 492AAAD which was approved by TIA  |

## Optical Specifications

|                    |  |
|--------------------|--|
| Bandwidth          | High Performance EMB* (MHz.km): 4700 at 850 nm only<br>Legacy Performance EMB** (MHz.km): 3500 at 850 nm / 500 at 1300 nm  |
| Attenuation        | At 850 nm max. $\leq$ 2.3 dB/km<br>At 1300 nm max. $\leq$ 0.6 dB/km  |
| Macrobend Loss     | Mandrel Radius (mm): 37.2 / 15 / 7.5<br>Number of Turns: 100 / 2 / 2<br>Induced Attenuation (dB) at 850 nm: $\leq$ 0.05 / $\leq$ 0.1 / 0.2<br>Induced Attenuation (dB) at 1300 nm: $\leq$ 0.15 / $\leq$ 0.3 / $\leq$ 0.5 |
| Numerical Aperture | 0.200 $\pm$ 0.015  |
| *                  | Ensured via miniEMBc, per TIA/EIA 455-220A and IEC 60793-1-49, for high performance laser-based systems (up to 10Gb/s)   |
| **                 | OFL BW, per TIA/EIA 455-204 and IEC 60793-1-41, for legacy and LED-based systems (typically up to 100 Mb/s)  |

## Dimensional Specifications

|                                |                         |
|--------------------------------|-------------------------|
| Core Diameter                  | 50.0 $\pm$ 2.5 $\mu$ m  |
| Cladding Diameter              | 125.0 $\pm$ 1.0 $\mu$ m |
| Core-Clad Concentricity        | $\leq$ 1.5 $\mu$ m      |
| Cladding Non-Circularity       | $\leq$ 1.0%             |
| Core Non-Circularity           | $\leq$ 5.0%             |
| Coating Diameter               | 242 $\pm$ 5 $\mu$ m     |
| Coating-Cladding Concentricity | $<$ 12 $\mu$ m          |

## Environmental

| Environmental Test           | Test Condition                  | Induced Attenuation 850 nm & 1300 nm (dB/km) |
|------------------------------|---------------------------------|--|
| Temperature Dependence       | -60°C to +85°C                  | $\leq$ 0.10                                  |
| Temperature Humidity Cycling | -10°C to +85°C and 4% to 98% RH | $\leq$ 0.10                                  |
| Water Immersion              | 23°C $\pm$ 2°C                  | $\leq$ 0.20                                  |
| Heat Aging                   | 85°C $\pm$ 2°C                  | $\leq$ 0.20                                  |
| Damp Heat                    | 85°C at 85% RH                  | $\leq$ 0.20                                  |
| Operating Temperature Range  | -60°C to +85°C                  |  |

## Mechanical Specifications

|            |  |
|------------|--|
| Proof Test | The entire fiber length is subjected to a tensile stress $\geq$ 100 kpsi (0.7 GN/m <sup>2</sup> ). |
|------------|--|

tML<sup>®</sup> 24 - FO Micro Distribution Trunk Cable both sides 1x 24F MPO w. Pins 24G50/125 $\mu$  OM4 LSHF, Type A, Length: xx in m

|        |  |
|--------|--|
| Length | Fiber lengths available up to 17.6 km/spool. |
|--------|--|

## Performance Characterizations

|                                     |   |
|-------------------------------------|---|
| Refractive Index Difference         | 1%  |
| Effective Group Index of Refraction | 850 nm: 1.480<br>1300 nm: 1.479   |
| Fatigue Resistance Parameter (nd)   | 20  |
| Coating Strip Force                 | Dry: 0.6 lbs (2.7N)<br>Wet: 14 days in 23°C water soak: 0.6 lbs (2.7N)  |
| Chromatic Dispersion                | Zero Dispersion Wavelength ( $\lambda_0$ ): 1295 nm $\leq \lambda_0 \leq$ 1315 nm<br>Zero Dispersion Slope ( $S_0$ ): $\leq 0.101$ ps/(nm <sup>2</sup> *km) |

## Product variants & accessories

| Art.-No.              | Description   |
|-----------------------|---|
| TML-M2P/M2P09I24E-Axx | tML <sup>®</sup> 24 - FO Micro Distribution Trunk Cable both sides 1x 24F MPO w. Pins 24E9/125 $\mu$ OS2 LSHF, Type A, Length: xx in m  |
| TML-M2P/M2P50I24G3Axx | tML <sup>®</sup> 24 - FO Micro Distribution Trunk Cable both sides 1x 24F MPO w. Pins 24G50/125 $\mu$ OM3 LSHF, Type A, Length: xx in m |
| TML-M2P/M2P50I24G4Axx | tML <sup>®</sup> 24 - FO Micro Distribution Trunk Cable both sides 1x 24F MPO w. Pins 24G50/125 $\mu$ OM4 LSHF, Type A, Length: xx in m |
| TML-M2P/M2P50I24G5Axx | tML <sup>®</sup> 24 - FO Micro Distribution Trunk Cable both sides 1x 24F MPO w. Pins 24G50/125 $\mu$ OM5 LSHF, Type A, Length: xx in m |