

## FO Loopback Connector 24F MPO/MTP<sup>®</sup> without pins 50/125 $\mu$ OM4



### FO Components

Loopbacks are used primarily as a means to test optical links in networks or devices by "looping back" the connections from the TX (transmit) pairs to the RX (receive) pairs. By doing this, a complete optical link is formed, allowing the optical performance evaluation of a discrete component or a complete link in a network path covering one or more interfaces.

QSFP optical loopbacks offer a female MPO/MTP<sup>®</sup> connector end that mates to any MPO or MTP<sup>®</sup> adapter or device port. The QSFP loopback also can be mated directly to a parallel optical device such as a Quad Small Form-factor Pluggable (QSFP) transceiver with a 4-lane configuration. For multimode applications, an attenuated version of the MPO loopback is available to simulate longer links in a network, with up to 5dB attenuation. With standard or custom pinouts available for 8- to 12-fiber MT ferrules, the QSFP loopback can accommodate specific optical-routing needs. The small and compact housing design allows side-by-side mounting in dense board applications and tight spaces. This design makes it ideal for blades with multiple optical components on a face plate.

MPO/MTP<sup>®</sup> optical loopbacks can be used to test such devices as CXP, QSFP, CFP and other links that use MPO as a form of interconnect in the network. Available in both 12- and 24-fiber configurations, the optical loopbacks offer



**tde<sup>®</sup> trans data elektronik GmbH**

**Headquarter address:**

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

**Sales office address:**

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 914 36 99  
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

## FO Loopback Connector 24F MPO/MTP<sup>®</sup> without pins 50/125 $\mu$ OM4

standard and custom mapping.

### Technical Data

- Compact in size
- Ease of use with Plug-in technology
- Network diagnosing & testing
- Optional for 12 or 24 fibers MPO with or without Pins

### FO Connectors

The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP<sup>®</sup> plug has a defined fiber height of 1 - 3.5 $\mu$ . The max. adjacent fiber height difference is 0.2 $\mu$ m and for all fibers 0.3 $\mu$ m.

#### Connector

Type	MPO/MTP <sup>®</sup> Female Push Pull Locking (magenta)
Ferrule	24 Fiber MM Elite <sup>®</sup> ferrule, PPS
Boot colour	Red
Temperature range	-40°C to +75°C
Manufacturer	tde/US Conec

#### Optical Performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
50/125 $\mu$ OM4	MPO/MTP <sup>®</sup>	850 nm	≤ 0.12 dB	0.25 dB	35 dB

### Product variants & accessories

Art.-No.	Description
L-M2-50-3-LOOP	FO Loopback Connector 24F MPO/MTP <sup>®</sup> without pins 50/125 $\mu$ OM3
L-M2-50-4-LOOP	FO Loopback Connector 24F MPO/MTP <sup>®</sup> without pins 50/125 $\mu$ OM4