

FO Loopback Connector 24F MPO/MTP[®] with pins 50/125 μ OM4



FO Components

Loopbacks are used primarily as a means to test optical links in networks or devices by "looping back" the connections from the TX (transmit) pairs to the RX (receive) pairs. By doing this, a complete optical link is formed, allowing the optical performance evaluation of a discrete component or a complete link in a network path covering one or more interfaces.

QSFP optical loopbacks offer a female MPO/MTP[®] connector end that mates to any MPO or MTP[®] adapter or device port. The QSFP loopback also can be mated directly to a parallel optical device such as a Quad Small Form-factor Pluggable (QSFP) transceiver with a 4-lane configuration. For multimode applications, an attenuated version of the MPO loopback is available to simulate longer links in a network, with up to 5dB attenuation. With standard or custom pinouts available for 8- to 12-fiber MT ferrules, the QSFP loopback can accommodate specific optical-routing needs. The small and compact housing design allows side-by-side mounting in dense board applications and tight spaces. This design makes it ideal for blades with multiple optical components on a face plate.

MPO/MTP[®] optical loopbacks can be used to test such devices as CXP, QSFP, CFP and other links that use MPO as a form of interconnect in the network. Available in both 12- and 24-fiber configurations, the optical loopbacks offer



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 914 36 99
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

FO Loopback Connector 24F MPO/MTP[®] with pins 50/125 μ OM4

standard and custom mapping.

Technical Data

- Compact in size
- Ease of use with Plug-in technology
- Network diagnosing & testing
- Optional for 12 or 24 fibers MPO with or without Pins

FO Connectors

The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP[®] plug has a defined fiber height of 1 - 3.5 μ . The max. adjacent fiber height difference is 0.2 μ m and for all fibers 0.3 μ m.

Connector

Type	MPO/MTP [®] Male Push Pull Locking with Elite Pins (magenta)
Ferrule	24 Fiber MM Elite [®] ferrule, PPS
Boot colour	Red
Temperature range	-40°C to +75°C
Manufacturer	tde/US Conec

Optical Performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
50/125 μ OM4	MPO/MTP [®]	850 nm	≤ 0.12 dB	0.25 dB	35 dB

Product variants & accessories

Art.-No.	Description
L-M2P50-3-LOOP	FO Loopback Connector 24F MPO/MTP [®] with pins 50/125 μ OM3
L-M2P50-4-LOOP	FO Loopback Connector 24F MPO/MTP [®] with pins 50/125 μ OM4