

tML<sup>®</sup> - FO Micro Distribution Trunk Cable both sides 4x MPO/MTP<sup>®</sup> Female 48E9/125µ OS2 LSHF, Type C, Length: xxxxx



## tML<sup>®</sup> - tde Modular Link

tML<sup>®</sup> is a patented, modular cabling system consisting of the three key components module, trunk cable and rack mount enclosure. The system components are 100 percent manufactured, pre-assembled and tested in Germany. They enable plug-and-play installation on site – especially in data centres, but also in industrial environments – within the shortest possible time. Heart of the system are the rear MPO/MTP<sup>®</sup> and Telco connectors, which can be used to connect at least six or twelve ports at a time. Depending on the module configuration, transfer rates of up to 200G are currently possible with SR4. The fibre optic and TP modules can be used together in a module carrier with a very high port density. The tde offers its tML<sup>®</sup> cabling system as a proven tML<sup>®</sup> standard system and in the highly innovative variants tML<sup>®</sup> Xtended, tML<sup>®</sup> 24 System and now tML<sup>®</sup> 32 System for extreme scalability and very easy migration to higher transmission rates such as 40G, 100G, 200G and 400G.



**tde<sup>®</sup> trans data elektronik GmbH**

### Headquarter address:

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

### Sales office address:

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 8805 61 13  
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

tML<sup>®</sup> - FO Micro Distribution Trunk Cable both sides 4x MPO/MTP<sup>®</sup> Female 48E9/125μ OS2 LSHF, Type C, Length: xxxxx

## Technical Data

The tML<sup>®</sup>- FO Micro Distribution Trunk Cable is preterminated with MPO/MTP<sup>®</sup>connectors on both ends. The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP<sup>®</sup>plug has a defined fiber height of 1 - 3.5μ. The max. adjacent fiber height difference is 0.2μm and for all fibers 0.3μm. All system components (modules, trunk cables and patch cords) are co-ordinated for the reaching of the performance particularly. The fan-out unit is optimized for tML<sup>®</sup> - Cable Mounting Bracket for Fan-out Units. The module is marked with sequential serial number and article number.

## FO Connectors

The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP<sup>®</sup> plug has a defined fiber height of 1 - 3.5μ. The max. adjacent fiber height difference is 0.2μm and for all fibers 0.3μm.

### Connector

Type	MPO/MTP <sup>®</sup> Female Push Pull Locking (Green)
Ferrule	12 Fiber SM Elite <sup>®</sup> ferrule, PPS
Boot colour	Black
Temperature range	-40°C bis +75°C
Manufacturer	tde/US Conec

### Optical Performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
9/125μ OS2	MPO/MTP <sup>®</sup> APC	1310 / 1550 nm	≤ 0.10 dB	0.20 dB	75 dB

## FO Cables

Standards	Environmental and mechanical tests according to EN 187000 and IEC 60794-1-2.
Flame retardant	IEC 60332-3
Halogen free	IEC 60754-1
Low smoke emission	IEC 61034-1/2
Reaction to fire (Euroclasses)	D <sub>ca</sub>

Type	Micro Distribution Indoor Cable
Fibers	48 (4 x 12)
Strength members	Aramid Yarns
Outer jacket	LSZH
Color	Gelb (RAL1021)
Weight	62 kg/km
Outer Ø	7.5 ± 0.2 mm
Tensile Load	1000 N

tML® - FO Micro Distribution Trunk Cable both sides 4x MPO/MTP® Female 48E9/125µ OS2 LSHF, Type C, Length: xxxxx

Crush	700 N
Temperature range	-20°C to +70°C
Min. bending radius	10 x Ø Outer

## FO Fiber

Type	Corning Ultra SMF-28® 09/125µ OS2 singlemode fiber
Maximum Attenuation	At 1310 nm max. 0.32 dB/km At 1383 nm max. 0.32 dB/km At 1490 nm max. 0.21 dB/km At 1550 nm max. 0.18 dB/km At 1625 nm max. 0.20 dB/km
Attenuation vs. Wavelength	Range: 1285 - 1330 nm; Ref. λ: 1310 nm; Max. Difference: 0.03 dB/km Range: 1525 - 1575 nm; Ref. λ: 1550 nm; Max. Difference: 0.02 dB/km
Macrobend Loss	Mandrel Radius: 10mm; Number of Turns: 1; Wavelength: 1550nm; Induced Attenuation: ≤ 0.50 dB Mandrel Radius: 10mm; Number of Turns: 1; Wavelength: 1625nm; Induced Attenuation: ≤ 1.5 dB Mandrel Radius: 15mm; Number of Turns: 10; Wavelength: 1550nm; Induced Attenuation: ≤ 0.05 dB Mandrel Radius: 15mm; Number of Turns: 10; Wavelength: 1625nm; Induced Attenuation: ≤ 0.30 dB Mandrel Radius: 25mm; Number of Turns: 100; Wavelength: 1310nm, 1550nm, 1625nm; Induced Attenuation: ≤ 0.01 dB
Point Discontinuity	Wavelength: 1310 nm; Point Discontinuity: ≤ 0.05 dB Wavelength: 1550 nm; Point Discontinuity: ≤ 0.05 dB
Cable Cutoff Wavelength (λ <sub>ccf</sub> )	λ <sub>ccf</sub> ≤ 1260 nm
Mode-Field Diameter	At 1310 nm = 9.2 ± 0.4 µm At 1550 nm = 10.4 ± 0.5 µm
Dispersion	At 1550 nm = ≤ 18.0 [ps/(nm*km)] At 1625 nm = ≤ 22.0 [ps/(nm*km)]
	Zero Dispersion Wavelength (λ <sub>0</sub> ): 1304 nm ≤ λ <sub>0</sub> ≤ 1324 nm Zero Dispersion Slope (S <sub>0</sub> ): ≤ 0.092 ps/(nm² *km)
Polarization Mode Dispersion (PMD)	PMD Link Design Value = ≤ 0.04 ps/√km Maximum Individual Fiber = ≤ 0.1 ps/√km

## Dimensional Specifications

Fiber Curl	≥ 4.0 m radius of curvature
Cladding Diameter	125.0 ± 0.7 µm
Core-Clad Concentricity	≤ 0.5 µm
Cladding Non-Circularity	≤ 0.7%
Coating Diameter	242 ± 5 µm
Coating-Cladding Concentricity	< 12 µm

## Environmental Specifications

Environmental Test	Test Condition	Induced Attenuation 1310 nm, 1550 nm & 1625 nm
Temperature Dependence	-60°C to +85°C	≤ 0.05
Temperature Humidity Cycling	-10°C to +85°C up to 98% RH	≤ 0.05
Water Immersion	23°C ± 2°C	≤ 0.05

tML<sup>®</sup> - FO Micro Distribution Trunk Cable both sides 4x MPO/MTP<sup>®</sup> Female 48E9/125 $\mu$  OS2 LSHF, Type C, Length: xxxxx

Heat Aging	85°C $\pm$ 2°C	$\leq$ 0.05
Operating Temperature Range	-60°C to +85°C	

## Mechanical Specifications

Proof Test	The entire fiber length is subjected to a tensile stress $\geq$ 100 kpsi (0.69 GPa).
Length	Fiber lengths available up to 63.0 km/spool.

## Performance Characterizations

Core Diameter	8.2 $\mu$ m
Numerical Aperture	0.14
Effective Group Index of Refraction	1310 nm: 1.4676 1550 nm: 1.4682
Fatigue Resistance Parameter (nd)	20
Coating Strip Force	Dry: 0.6 lbs (3N) Wet: 14 days room temperature: 0.6 lbs (3N)
Rayleigh Backscatter Coefficient (for 1 ns Pulse Width)	1310 nm: -77 dB 1550 nm: -82 dB

## FO Fan-Out

Length Fan-Out	50 mm
Max. $\varnothing$ Fan-Out	16.4 mm
Parallel connectors	4

## Product variants & accessories

Art.-No.	Description
TML-MP/MP09I48Exxxxx	tML <sup>®</sup> - FO Micro Distribution Trunk Cable both sides 4x MPO/MTP <sup>®</sup> Female 48E9/125 $\mu$ OS2 LSHF, Type C, Length: xxxxx