

tDF[®] - FO Premium splice module 6x LC APC duplex SM 3U/7HP with pigtails 9/125 μ

tDF[®] - tde Distribution Frame (ODF)

tDF[®] is a modular Central Office solution with the highest packing density. At 46U, up to 4032 fibers can be terminated with LC. In developing the tde has taken primarily attention on the user-friendly installation. So the patented modules are fully be fitted from the front. A 19-inch sub rack occupies three height units and is equipped with twelve splice modules. Per sub rack, up to 288 fibers can be terminated with LC. The splices will be stored in standard splice cassettes. A unique feature of the splice module is the built-in loose tube over length management, which compared to conventional solutions saves an additional rack unit for the over length tray. The trunk cables are brought to the sub rack side and splitted there. This results in very short stripping lengths for the trunk cables. Due to the tML[®] compatibility also MPO/MTP[®] modules can be equipped in the same sub rack. The modular design of the tDF rack system offers maximum flexibility. The racks can be ordered customized completely preconfigured.



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 914 36 99
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

tDF[®] - FO Premium splice module 6x LC APC duplex SM 3U/7HP with pigtails 9/125 μ

Technical Data

Pre-mounted	6 LC duplex adapters 12 LC APC Fiber pigtails 9/125 μ OS2 12 Crimp Splice protectors 1 Splice cassettes 1 Splice holder 1 Splice cover 1,6m Flex tube
Alternative pre-mounted	TDF-M06-xxLCAD9APS
xx	(01 - 06) quantity of adapters

Type	Front panel for 6 x LC Duplex
Color	Anodized E6 EV1
Inscription	1 - 12 Screen printing by label strips
Material	Alu- AIMG3 G22
Dimensions	3U/7HP

Type	Module slot for rack 3U/84HP
Dimensions	app. 230 x 129 x 32mm

FO Adapters

Type	LC Duplex
Application	Singlemode OS2 APC
Design	One-Piece with flange
Connector style	SC Simplex
Color	Green
Material	Plastic
Sleeve	Zirconia Straight Split
Shutter	-
Manufacturer	tde

FO Pigtails Premium

FO Connectors

Connector Type	LC APC Unibody Simplex
Housing	Plastic, Green
Ferrule	Zirconia Straight Split, Spring-loaded Axially
Ferrule Hole	125.5 μ
Ferrule Concentricity	$\leq 0.6 \mu$
Mating Cycles	500
Operating Temperature	-40°C up to +75°C
Strain Relief to	100 N

tDF[®] - FO Premium splice module 6x LC APC duplex SM 3U/7HP with pigtails 9/125 μ

Manufacturer	tde
--------------	-----

Optical performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
9/125 μ	LC APC	1310 / 1550 nm	\leq 0.10 dB	0.25 dB	75 dB

FO Cables

Tight Buffer	Low smoke (IEC 61034 and EN 50268) and free of halogens (LSOH)
	Non corrosive after IEC 60754-2 and EN 50267
	Flame resistant after IEC 60332-3C and EN 50266-2-4
	Completely dry design
	Free from metal, no grounding problems and potential differences
	Tight Buffer for simple and direct connector mounting

Characteristics

Fiber Count	1 (Tight Buffer)
Core- \varnothing	0.9 mm
Coreweight	1 kg/km
Min. Bending radius - Installation	30 mm
Min. Bending radius - Operation	30 mm
Removal	1500 mm
Fire load	0.15 MJ/m
Temperature range - Installation	-5 to +50°C
Temperature range - Operation	-20 to +60°C
Temperature range - Transport / Lagerung	-25 to +70°C

FO Fiber

Type	Corning Ultra SMF-28 [®] 09/125 μ OS2 singlemode fiber
Maximum Attenuation	At 1310 nm max. 0.32 dB/km At 1383 nm max. 0.32 dB/km At 1490 nm max. 0.21 dB/km At 1550 nm max. 0.18 dB/km At 1625 nm max. 0.20 dB/km
Attenuation vs. Wavelength	Range: 1285 - 1330 nm; Ref. λ : 1310 nm; Max. Difference: 0.03 dB/km Range: 1525 - 1575 nm; Ref. λ : 1550 nm; Max. Difference: 0.02 dB/km
Macrobend Loss	Mandrel Radius: 10mm; Number of Turns: 1; Wavelength: 1550nm; Induced Attenuation: \leq 0.50 dB Mandrel Radius: 10mm; Number of Turns: 1; Wavelength: 1625nm; Induced Attenuation: \leq 1.5 dB Mandrel Radius: 15mm; Number of Turns: 10; Wavelength: 1550nm; Induced Attenuation: \leq 0.05 dB Mandrel Radius: 15mm; Number of Turns: 10; Wavelength: 1625nm; Induced Attenuation: \leq 0.30 dB Mandrel Radius: 25mm; Number of Turns: 100; Wavelength: 1310nm, 1550nm, 1625nm; Induced Attenuation: \leq 0.01 dB

tDF[®] - FO Premium splice module 6x LC APC duplex SM 3U/7HP with pigtails 9/125 μ

Point Discontinuity	Wavelength: 1310 nm; Point Discontinuity: ≤ 0.05 dB Wavelength: 1550 nm; Point Discontinuity: ≤ 0.05 dB
Cable Cutoff Wavelength (λ_{ccf})	$\lambda_{ccf} \leq 1260$ nm
Mode-Field Diameter	At 1310 nm = 9.2 ± 0.4 μ m At 1550 nm = 10.4 ± 0.5 μ m
Dispersion	At 1550 nm = ≤ 18.0 [ps/(nm*km)] At 1625 nm = ≤ 22.0 [ps/(nm*km)]
	Zero Dispersion Wavelength (λ_0): 1304 nm $\leq \lambda_0 \leq 1324$ nm Zero Dispersion Slope (S_0): ≤ 0.092 ps/(nm ² *km)
Polarization Mode Dispersion (PMD)	PMD Link Design Value = ≤ 0.04 ps/ \sqrt km Maximum Individual Fiber = ≤ 0.1 ps/ \sqrt km

Dimensional Specifications

Fiber Curl	≥ 4.0 m radius of curvature
Cladding Diameter	125.0 ± 0.7 μ m
Core-Clad Concentricity	≤ 0.5 μ m
Cladding Non-Circularity	$\leq 0.7\%$
Coating Diameter	242 ± 5 μ m
Coating-Cladding Concentricity	< 12 μ m

Environmental Specifications

Environmental Test	Test Condition	Induced Attenuation 1310 nm, 1550 nm & 1625 nm
Temperature Dependence	-60°C to +85°C	≤ 0.05
Temperature Humidity Cycling	-10°C to +85°C up to 98% RH	≤ 0.05
Water Immersion	23°C \pm 2°C	≤ 0.05
Heat Aging	85°C \pm 2°C	≤ 0.05
Operating Temperature Range	-60°C to +85°C	

Mechanical Specifications

Proof Test	The entire fiber length is subjected to a tensile stress ≥ 100 kpsi (0.69 GPa).
Length	Fiber lengths available up to 63.0 km/spool.

Performance Characterizations

Core Diameter	8.2 μ m
Numerical Aperture	0.14
Effective Group Index of Refraction	1310 nm: 1.4676 1550 nm: 1.4682
Fatigue Resistance Parameter (nd)	20
Coating Strip Force	Dry: 0.6 lbs (3N) Wet: 14 days room temperature: 0.6 lbs (3N)
Rayleigh Backscatter Coefficient (for 1 ns Pulse Width)	1310 nm: -77 dB 1550 nm: -82 dB

tDF[®] - FO Premium splice module 6x LC APC duplex SM 3U/7HP with pigtails 9/125 μ

Product variants & accessories

Art.-No.	Description
TDF-M06-06LCAD9APS	tDF [®] - FO Premium splice module 6x LC APC duplex SM 3U/7HP with pigtails 9/125 μ
TDF-M06-06LCD50-3PS	tDF [®] - FO Premium splice module 6x LC duplex MM 3U/7HP with pigtails 50/125 μ OM3
TDF-M06-06LCD50-4PS	tDF [®] - FO Premium splice module 6x LC duplex MM 3U/7HP with pigtails 50/125 μ OM4
TDF-M06-06LCD9PS	tDF [®] - FO Premium splice module 6x LC PC duplex SM 3U/7HP with pigtails 9/125 μ