

tML[®] Xtended - FO Dark Fiber Module 5HP black 4x MPO/MTP[®] w/o Pins/6x MPO/MTP[®] w. Pins
50/125 μ OM3, SR4



tML[®] Xtended

tML[®] Xtended is a patented, modular cabling system consisting of the three key components module, trunk cable and rack mount enclosure. The system components are 100 percent manufactured, pre-assembled and tested in Germany. They enable plug-and-play installation on site – especially in data centres, but also in industrial environments – within the shortest possible time. Heart of the system are the rear MPO/MTP[®] 12 fiber and Telco connectors, which can be used to connect at least six or twelve ports at a time. Depending on the module configuration, transfer rates of up to 200G are currently possible with SR4. The fibre optic and TP modules can be used together in a module carrier with a very high port density. The tde offers its tML[®] cabling system as a proven tML[®] standard system and in the highly innovative variants tML[®] 24 system and now tML[®] 32 system for extreme scalability and very easy migration to higher transmission rates such as 40G, 100G, 200G and 400G.



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 914 36 99
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

tML[®] Xtended - FO Dark Fiber Module 5HP black 4x MPO/MTP[®] w/o Pins/6x MPO/MTP[®] w. Pins
50/125 μ OM3, SR4

Technical Data

The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP[®]plug has a defined fiber height of 1 - 3.5 μ . The max. adjacent fiber height difference is 0.2 μ m and for all fibers 0.3 μ m. All system components (modules, trunk cables and patch cords) are co-ordinated for the reaching of the performance particularly. The module is marked with sequential serial number and article number. The modules are ROHS compliant.

Entry	2 x MPO/MTP [®] Female Adapter (aqua) back
Exit	6 x MPO/MTP [®] Male Adapter (aqua) front
Tests	Interferometer, Insertion Loss, Return Loss and Visual Final Inspection; all measured values are electronically archived
	QS-Managementsystem ISO 9001, ISO 14001 and TL 9000

Box	Galvanized steel sheet
Front Panel	black

FO Connectors

Connector

Type	MPO/MTP [®] Female Push Pull Locking (aqua)
Ferrule	12 Fiber MM Elite [®] ferrule, PPS
Boot colour	Black
Manufacturer	tde/US Conec

Optical Performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
50/125 μ OM3	MPO/MTP [®]	850 nm	\leq 0.14 dB	0.25 dB	35 dB

FO Connectors

Connector

Type	MPO/MTP [®] Male Push Pull Locking (aqua)
Ferrule	12 Fiber MM Elite [®] ferrule, PPS
Boot colour	Black
Manufacturer	tde/US Conec

tML[®] Xtended - FO Dark Fiber Module 5HP black 4x MPO/MTP[®] w/o Pins/6x MPO/MTP[®] w. Pins
50/125 μ OM3, SR4

Optical Performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
50/125 μ OM3	MPO/MTP [®]	850 nm	≤ 0.14 dB	0.25 dB	35 dB

FO Adapters

Type	MPO/MTP [®]
Application	Multimode OM3
Design	without Flange
Connector style	SC Simplex
Key Orientation	Type A, Key up/down
Color	Aqua
Material	Plastic
Sleeve	--
Shutter	--
Standards	IEC 61754-7 TIA 604-5
Manufacturer	US Conec

FO Fiber

Type	Draka OM3 50/125 μ m multimode fiber (C12)	
Standards and Norms	IEC 60793-2-10 Category A1a.2;	EN 50 173:2002 category OM3
	EN 60793-2-10: type A1a.2	ISO/IEC 11801:2002 category OM3
	ITU Recommendation G.651	IEEE 802.3 - 2002 incl. amendment 802.3ae - 2002.
	TIA/EIA-492 AAAB	

Attenuation according to IEC 60793-1-40

Maximum value of cable at 850 nm	≤ 3.0 dB/km
Maximum value of cable at 1300 nm	≤ 1.0 dB/km
Maximum value of fiber (for reference only) at 850 nm	≤ 2.5 dB/km
Maximum value of fiber (for reference only) at 1300 nm	≤ 0.8 dB/km
Inhomogeneity of OTDR trace for any two 1000 metre fiber lengths	Max. 0.1 dB/km

tML[®] Xtended - FO Dark Fiber Module 5HP black 4x MPO/MTP[®] w/o Pins/6x MPO/MTP[®] w. Pins
50/125 μ OM3, SR4

Bandwidth according to IEC 60793-1-41

OFL value at 850 nm	1500 MHz*km
OFL value at 1300 nm	500 MHz*km
Effective Modal Bandwidth (EMB) Effective Modal Bandwidth I assured by means of differential mode delay (DMD) measurement as specified in IEC 60793-1-49	2000 MHz*km

Group index of refraction according to IEC 60793-1-22

Group index of refraction at 850 nm	1.482
Group index of refraction at 1300 nm	1.477

Other properties according to IEC 60793-1-xx

Attribute	Measurement method	Limits
Core diameter	IEC/EN 60793-1-20	50 \pm 2.5 μ m
Cladding diameter	IEC/EN 60793-1-20	125.0 \pm 1.0 μ m
Cladding non-circularity	IEC/EN 60793-1-20	\leq 1.0%
Core non-circularity	IEC/EN 60793-1-20	\leq 5%
Core -cladding concentricity error	IEC/EN 60793-1-20	\leq 1.5 μ m
Primary coating diameter - uncoloured	IEC/EN 60793-1-21	242 \pm 7 μ m
Primary coating diameter - coloured	IEC/EN 60793-1-21	250 \pm 15 μ m
Primary coating non-circularity	IEC/EN 60793-1-21	\leq 5%
Primary coating-cladding concentricity error	IEC/EN 60793-1-21	\leq 10 μ m
Proof stress level	IEC/EN 60793-1-30	\geq 0.7 (\approx 1 %)
Typical average strip force	IEC/EN 60793-1-32	1.7 N
Strip force (peak)	IEC/EN 60793-1-32	1.3 N \leq F _{peak.strip} \leq 8.9 N
Numerical aperture	IEC/EN 60793-1-43	0.200 \pm 0.015

Product variants & accessories

Art.-No.	Description
TML-T06MPP/4MP50G3XS	tML [®] Xtended - FO Dark Fiber Module 5HP black 4x MPO/MTP [®] w/o Pins/6x MPO/MTP [®] w. Pins 50/125 μ OM3, SR4
TML-T06MPP/4MP50G4XS	tML [®] Xtended - FO Dark Fiber Module 5HP black 4x MPO/MTP [®] w/o Pins/6x MPO/MTP [®] w. Pins 50/125 μ OM4, SR4
TML-T06MPP/4MP50G5XS	tML [®] Xtended - FO Dark Fiber Module 5HP black 4x MPO/MTP [®] w/o Pins/6x MPO/MTP [®] w. Pins 50/125 μ OM5, SR4