

tML[®] - FO patch cord both sides 1x MPO/MTP[®] Female 12E9/125 μ OS2 LSOH, Type B, Length: xxx



tML[®] - tde Modular Link

tML[®] is a patented, modular cabling system consisting of the three key components module, trunk cable and rack mount enclosure. The system components are 100 percent manufactured, pre-assembled and tested in Germany. They enable plug-and-play installation on site - especially in data centres, but also in industrial environments - within the shortest possible time. The system is characterized by highest packing density and highest flexibility during migration to higher transmission rates. Fibre optic and TP modules can be combined in one rack mount enclosure. 96x fibre optics LC Duplex or 96x MPO connectors can be used modularly on a 19-inch height unit. Thanks to its patented polarity and dark fibre modules, the tML system offers the simplest migration options to 100G and more.

The tML[®] - FO patch cord is intended for the connection of two tML[®]- FO Modules.



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 914 36 99
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

tML[®] - FO patch cord both sides 1x MPO/MTP[®] Female 12E9/125 μ OS2 LSOH, Type B, Length: xxx

Technical Data

The tML[®]- FO trunk cable is preterminated with MPO/MTP[®]connectors on both ends. The Cable is very slim and flexible. The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP[®]plug has a defined fiber height of 1 - 3.5 μ . The max. adjacent fiber height difference is 0.2 μ m and for all fibers 0.3 μ m. All system components (modules, trunk cables and patch cords) are co-ordinated for the reaching of the performance particularly. The module is marked with sequential serial number and article number.

Cable	Round cable, loose tube, LSOH, yellow
Nominal diameter	3.0 mm
Connectors	MPO/MTP [®] APC Female Push Pull (green)
Pin out	Type B
Tests	Interferometer, Insertion Loss, Return Loss and Visual Final Inspection; all measured values are electronically archived
	QS-Managementsystem ISO 9001, ISO 14001 and TL 9000

xxx - stands for the cable length in meters (every length available)

FO Connectors

The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP[®] plug has a defined fiber height of 1 - 3.5 μ . The max. adjacent fiber height difference is 0.2 μ m and for all fibers 0.3 μ m.

Connector

Type	MPO/MTP [®] Female Push Pull Locking (Green)
Ferrule	12 Fiber SM Elite [®] ferrule, PPS
Boot colour	Black
Temperature range	-40°C bis +75°C
Manufacturer	tde/US Conec

Optical Performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
9/125 μ OS2	MPO/MTP [®] APC	1310 / 1550 nm	≤ 0.10 dB	0.20 dB	75 dB

FO Cables

Standards	EN 50173-5
	IEC 60794-2-20
	ISO/IEC 24764
Flame resistance	IEC 60332-1-2
	IEC 60332-2-2

tML[®] - FO patch cord both sides 1x MPO/MTP[®] Female 12E9/125 μ OS2 LSOH, Type B, Length: xxx

	IEC 60754-1
	IEC 60754-2
	IEC 61034

Cable construction

Type	IVH12E09
Loose tube	12 coated fibers within PVC-core tube
Fiber type	SM-G652D, 9/125 μ , Corning SMF-28e+, OS2
Strength members	Aramid yarn
Outer jacket	LSZH (Halogen free, low smoke, flame retardant thermoplastic compound)
Jacket color	Yellow, RAL 1021
Identification	"t d e – IVH12E09–MPO LSZH" and sequential meter marking + Lot number

Physical properties

Outer diameter cable	3.0 \pm 0.1 mm
Diameter PVC-core tube	1.8 \pm 0.1 mm
Wall thickness PVC-core tube	0.35 mm – 0.40 mm
Max. tensile load	300 N
Min. bending radius	30 mm
Temperature range (storage, installation, operation)	-20°C to +70°C

FO Fiber

Type	Corning SMF-28e+ [®] 09/125 μ OS2 G.652.D singlemode fiber
Maximum Attenuation	At 1310 nm max. 0.33 - 0.35 dB/km At 1383 \pm 3 nm max. 0.31 - 0.35 dB/km At 1490 nm max. 0.21 - 0.24 dB/km At 1550 nm max. 0.19 - 0.20 dB/km At 1625 nm max. 0.20 - 0.23 dB/km
Attenuation vs. Wavelength	Range: 1285 - 1330 nm; Ref. λ : 1310 nm; Max. Difference: 0.03 dB/km Range: 1525 - 1575 nm; Ref. λ : 1550 nm; Max. Difference: 0.02 dB/km
Macrobend Loss	Mandrel Diameter:32mm; Number of Turns: 1; Wavelength: 1550nm; Induced Attenuation: \leq 0.03 dB Mandrel Diameter:50mm; Number of Turns: 100; Wavelength: 1310nm; Induced Attenuation: \leq 0.03 dB Mandrel Diameter:50mm; Number of Turns: 100; Wavelength: 1550nm; Induced Attenuation: \leq 0.03 dB Mandrel Diameter:60mm; Number of Turns: 100; Wavelength: 1625nm; Induced Attenuation: \leq 0.03 dB
Point Discontinuity	Wavelength: 1310 nm; Point Discontinuity: \leq 0.05 dB Wavelength: 1550 nm; Point Discontinuity: \leq 0.05 dB
Cable Cutoff Wavelength (λ_{ccf})	$\lambda_{ccf} \leq$ 1260 nm
Mode-Field Diameter	At 1310 nm = 9.2 \pm 0.4 μ m At 1550 nm = 10.4 \pm 0.5 μ m
Dispersion	At 1550 nm = \leq 18.0 [ps/(nm*km)] At 1625 nm = \leq 22.0 [ps/(nm*km)]
	Zero Dispersion Wavelength (λ_0): 1310 nm $\leq \lambda_0 \leq$ 1324 nm Zero Dispersion Slope (S_0): \leq 0.092 ps/(nm ² *km)
Polarization Mode Dispersion (PMD)	PMD Link Design Value = \leq 0.06 ps/ \sqrt km Maximum Individual Fiber = \leq 0.1 ps/ \sqrt km

tML[®] - FO patch cord both sides 1x MPO/MTP[®] Female 12E9/125 μ OS2 LSOH, Type B, Length: xxx

Norm	ITU-T Recommendation G.652 (Tables A, B, C, and D) IEC Specifications 60793-2-50 Type B1.3 TIA/EIA 492-CAAB Telcordia Generic Requirements GR-20-CORE ISO 11801 OS2
------	---

Dimensional Specifications

Fiber Curl	≥ 4.0 m radius of curvature
Cladding Diameter	125.0 ± 0.7 μ m
Core-Clad Concentricity	≤ 0.5 μ m
Cladding Non-Circularity	$\leq 0.7\%$
Coating Diameter	242 ± 5 μ m
Coating-Cladding Concentricity	< 12 μ m

Environmental Specifications

Environmental Test	Test Condition	Induced Attenuation 1310 nm, 1550 nm & 1625 nm
Temperature Dependence	-60°C to +85°C	≤ 0.05
Temperature Humidity Cycling	-10°C to +85°C up to 98% RH	≤ 0.05
Water Immersion	23°C \pm 2°C	≤ 0.05
Heat Aging	85°C \pm 2°C	≤ 0.05
Operating Temperature Range	-60°C to +85°C	

Mechanical Specifications

Proof Test	The entire fiber length is subjected to a tensile stress ≥ 100 kpsi (0.7 GPa).
Length	Fiber lengths available up to 63.0 km/spool.

Performance Characterizations

Core Diameter	8.2 μ m
Numerical Aperture	0.14
Zero Dispersion Wavelength (λ_0)	1317 nm
Zero Dispersion Slope (S_0)	0.088 ps/(nm ² *km)
Effective Group Index of Refraction	1310 nm: 1.4676 1550 nm: 1.4682
Fatigue Resistance Parameter (nd)	20
Coating Strip Force	Dry: 0.6 lbs (3N) Wet: 14 days room temperature: 0.6 lbs (3N)
Rayleigh Backscatter Coefficient (for 1 ns Pulse Width)	1310 nm: -77 dB 1550 nm: -82 dB

Product variants & accessories

tML[®] - FO patch cord both sides 1x MPO/MTP[®] Female 12E9/125 μ OS2 LSOH, Type B, Length: xxx

Art.-No.	Description
TML-MP/MP09I12E-Bxxx	tML [®] - FO patch cord both sides 1x MPO/MTP [®] Female 12E9/125 μ OS2 LSOH, Type B, Length: xxx
TML-MP/MP50I12G3Bxxx	tML [®] - FO patch cord both sides 1x MPO/MTP [®] Female 12G50/125 μ OM3 LSOH, Type B, Length: xxx
TML-MP/MP50I12G4Bxxx	tML [®] - FO Micro Distribution Trunk Cable both sides 1x MPO/MTP [®] Female 12G50/125 μ OM4 LSOH, Type B, Length: xxx
TML-MP/MP50I12G5Bxxx	tML [®] - FO Micro Distribution Trunk Cable both sides 1x MPO/MTP [®] Female 12G50/125 μ OM5 LSOH, Type B, Length: xxx