


FO attenuator MU/UPC plug/jack, xdB, 1310/1550nm



## tde - FO Attenuators

A fiber optic attenuator is a passive device used to reduce the amplitude of a light signal without significantly changing the wave form itself. This is often a requirement in DWDM and EDFA applications where the receiver cannot accept the signal generated from a high-power light source.

tde attenuators feature a proprietary type of metal-ion doped fiber which reduces the light signal as it passes through. This method of attenuation allows for higher performance than fiber splices or fiber offsets, which function by misdirecting rather than absorbing the light signal. tde attenuators are capable of performing in the 1310, C and L Bands. tde attenuators are capable of withstanding over 1W of high power light exposure for extended periods of time, making them well-suited to EDFA and other high-power applications. Low Polarization Dependent Loss (PDL) and a stable and independent wavelength distribution makes them ideal for DWDM.

### Applications

- Erbium Doped Fiber Amplifiers (EDFA)



**tde<sup>®</sup>** trans data elektronik GmbH

#### Headquarter address:

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

#### Sales office address:

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 914 36 99  
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

## FO attenuator MU/UPC plug/jack, xxdB, 1310/1550nm

- Dense Wave Division Multiplexers (DWDM)
- Overpowered fiber optic systems

### Features

- Metal ion doped fiber
- High-power light source durability
- Wavelength independence
- Attenuation levels ranging from 1dB to 30dB
- 1310nm, 1550nm, 1250-1625nm and 1350/1550nm dual wave lengths

### Technical Data

|                         |   |
|-------------------------|---|
| Return Loss             | ≥ 55 dB (UPC)                             |
| Attenuation Tolerance   | 01dB bis 10dB: ± 0.5% 11dB bis 30dB: ± 5% |
| Operational Wavelengths | 1310, 1490, and 1550 nm                   |
| Operating Temperature   | -40 to +75°C                              |
| Maximum Power           | 500mw                                     |

### Product variants & accessories

| Art.-No.           | Description                                       |
|--------------------|---|
| L-ATT-MU/UPC-MF-xx | FO attenuator MU/UPC plug/jack, xxdB, 1310/1550nm |