

tML® Xtended - FO Dark Fiber Module 5HP 4x MPO/MTP® w/o Pins/6x MPO/MTP® w. Pins 50/125µ  
OM4, SR4



## tML® Xtended

tML® Xtended is a patented, modular cabling system consisting of the three key components module, trunk cable and rack mount enclosure. The system components are 100 percent manufactured, pre-assembled and tested in Germany. They enable plug-and-play installation on site – especially in data centres, but also in industrial environments – within the shortest possible time. Heart of the system are the rear MPO/MTP® 12 fiber and Telco connectors, which can be used to connect at least six or twelve ports at a time. Depending on the module configuration, transfer rates of up to 200G are currently possible with SR4. The fibre optic and TP modules can be used together in a module carrier with a very high port density. The tde offers its tML® cabling system as a proven tML® standard system and in the highly innovative variants tML® 24 system and now tML® 32 system for extreme scalability and very easy migration to higher transmission rates such as 40G, 100G, 200G and 400G.



**tde® trans data elektronik GmbH**

**Headquarter address:**

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

**Sales office address:**

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 8805 61 13  
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

tML<sup>®</sup> Xtended - FO Dark Fiber Module 5HP 4x MPO/MTP<sup>®</sup> w/o Pins/6x MPO/MTP<sup>®</sup> w. Pins 50/125μ OM4, SR4

## Technical Data

The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP<sup>®</sup> plug has a defined fiber height of 1 - 3.5μ. The max. adjacent fiber height difference is 0.2μm and for all fibers 0.3μm. All system components (modules, trunk cables and patch cords) are co-ordinated for the reaching of the performance particularly. The module is marked with sequential serial number and article number. The modules are ROHS compliant.

Entry	2 x MPO/MTP <sup>®</sup> Female Adapter (magenta) back
Exit	6 x MPO/MTP <sup>®</sup> Male Adapter (magenta) front
Tests	Interferometer, Insertion Loss, Return Loss and Visual Final Inspection; all measured values are electronically archived
	QS-Managementsystem ISO 9001, ISO 14001 and TL 9000

Box	Galvanized steel sheet
Front Panel	Stainless steel

## FO Connectors

The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP<sup>®</sup> plug has a defined fiber height of 1 - 3.5μ. The max. adjacent fiber height difference is 0.2μm and for all fibers 0.3μm.

### Connector

Type	MPO/MTP <sup>®</sup> Female Push Pull Locking (Magenta)
Ferrule	12 Fiber MM Elite <sup>®</sup> ferrule, PPS
Boot colour	Black
Manufacturer	tde/US Conec

### Optical Performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
50/125μ OM4	MPO/MTP <sup>®</sup>	850 /1300 nm	≤ 0.12 dB	0.25 dB	35 dB

## FO Connectors

The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP<sup>®</sup> plug has a defined fiber height of 1 - 3.5μ. The max. adjacent fiber height difference is 0.2μm and for all fibers 0.3μm.

### Connector

Type	MPO/MTP <sup>®</sup> Male Push Pull Locking with Elite Pins (magenta)
------	---

## tML<sup>®</sup> Xtended - FO Dark Fiber Module 5HP 4x MPO/MTP<sup>®</sup> w/o Pins/6x MPO/MTP<sup>®</sup> w. Pins 50/125μ OM4, SR4

Ferrule	12 Fiber MM Elite <sup>®</sup> ferrule, PPS
Boot colour	Black
Manufacturer	tde/US Conec

### Optical Performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
50/125μ OM4	MPO/MTP <sup>®</sup>	850 /1300 nm	≤ 0.12 dB	0.25 dB	35 dB

### FO Adapters

Type	MPO/MTP <sup>®</sup>
Application	Multimode OM4
Design	without Flange
Connector style	SC Simplex
Key Orientation	Type A, Key up/down
Color	Magenta
Material	Plastic
Sleeve	--
Shutter	--
Standards	IEC 61754-7 TIA 604-5
Manufacturer	US Conec

### FO Fiber

Type	Corning ClearCurve <sup>®</sup> 50/125μ OM4 multimode fiber
Optimized Data Rate over Distance	40/100 Gb over 170 m* 10 Gb/s over 550 m 1 Gb/s over 1100 m
Standard Compliance	ISO/IEC 11801: type OM4 fiber** IEC 60793-2-10: type A1a.3 fiber** TIA/EIA: 492AAAD ITU: ITU G651.1
*	Distances specified in the 40G/100G per IEEE 802.3ba standard are 150m on OM4 and 100m on OM3; Corning fibers are manufactured to tighter dispersion specifications and thereby support the extended distances shown in the table (assuming cable attenuation ≤3.0 dB/km and same 1.0 dB of connector loss for OM3 that the standard requires for OM4)
**	Assumes IEC draft standard is harmonized with 492AAAD which was approved by TIA

### Optical Specifications

Bandwidth	High Performance EMB* (MHz.km): 4700 at 850 nm only Legacy Performance EMB** (MHz.km): 3500 at 850 nm / 500 at 1300 nm
-----------	---

## tML<sup>®</sup> Xtended - FO Dark Fiber Module 5HP 4x MPO/MTP<sup>®</sup> w/o Pins/6x MPO/MTP<sup>®</sup> w. Pins 50/125μ OM4, SR4

Attenuation	At 850 nm max. ≤ 2.3 dB/km At 1300 nm max. ≤ 0.6 dB/km
Macrobend Loss	Mandrel Radius (mm): 37.2 / 15 / 7.5 Number of Turns: 100 / 2 / 2 Induced Attenuation (dB) at 850 nm: ≤ 0.05 / ≤ 0.1 / 0.2 Induced Attenuation (dB) at 1300 nm: ≤ 0.15 / ≤ 0.3 / ≤ 0.5
Numerical Aperture	0.200 ± 0.015
*	Ensured via miniEMBc, per TIA/EIA 455-220A and IEC 60793-1-49, for high performance laser-based systems (up to 10Gb/s)
**	OFL BW, per TIA/EIA 455-204 and IEC 60793-1-41, for legacy and LED-based systems (typically up to 100 Mb/s)

### Dimensional Specifications

Core Diameter	50.0 ± 2.5 μm
Cladding Diameter	125.0 ± 1.0 μm
Core-Clad Concentricity	≤ 1.5 μm
Cladding Non-Circularity	≤ 1.0%
Core Non-Circularity	≤ 5.0%
Coating Diameter	242 ± 5 μm
Coating-Cladding Concentricity	< 12 μm

### Environmental

Enviromental Test	Test Condition	Induced Attenuation 850 nm & 1300 nm (dB/km)
Temperature Dependence	-60°C to +85°C	≤ 0.10
Temperature Humidity Cycling	-10°C to +85°C and 4% to 98% RH	≤ 0.10
Water Immersion	23°C ± 2°C	≤ 0.20
Heat Aging	85°C ± 2°C	≤ 0.20
Damp Heat	85°C at 85% RH	≤ 0.20
Operating Temperature Range	-60°C to +85°C	

### Mechanical Specifications

Proof Test	The entire fiber length is subjected to a tensile stress ≥ 100 kpsi (0.7 GN/m²).
Length	Fiber lengths available up to 17.6 km/spool.

### Performance Characterizations

Refractive Index Difference	1%
Effective Group Index of Refraction	850 nm: 1.480 1300 nm: 1.479
Fatigue Resistance Parameter (nd)	20
Coating Strip Force	Dry: 0.6 lbs (2.7N) Wet: 14 days in 23°C water soak: 0.6 lbs (2.7N)

tML<sup>®</sup> Xtended - FO Dark Fiber Module 5HP 4x MPO/MTP<sup>®</sup> w/o Pins/6x MPO/MTP<sup>®</sup> w. Pins 50/125μ OM4, SR4

Cromatic Dispersion	Zero Dispersion Wavelength ( $\lambda_0$ ): 1295 nm $\leq \lambda_0 \leq$ 1315 nm Zero Dispersion Slope ( $S_0$ ): $\leq 0.101$ ps/(nm <sup>2</sup> *km)
---------------------	---

## Product variants & accessories

Art.-No.	Description
TML-T06MPP/04MP50G3X	tML <sup>®</sup> Xtended - FO Dark Fiber Module 5HP 4x MPO/MTP <sup>®</sup> w/o Pins/6x MPO/MTP <sup>®</sup> w. Pins 50/125μ OM3, SR4
TML-T06MPP/04MP50G4X	tML <sup>®</sup> Xtended - FO Dark Fiber Module 5HP 4x MPO/MTP <sup>®</sup> w/o Pins/6x MPO/MTP <sup>®</sup> w. Pins 50/125μ OM4, SR4
TML-T06MPP/04MP50G5X	tML <sup>®</sup> Xtended - FO Dark Fiber Module 5HP 4x MPO/MTP <sup>®</sup> w/o Pins/6x MPO/MTP <sup>®</sup> w. Pins 50/125μ OM5, SR4