

tML[®] Xtended - FO Module 2x MPO/MTP[®] without Pins/12x LC Duplex w. shutter 9/125µ OS2



tML[®] - tde Modular Link

tML[®] is a patented, modular cabling system consisting of the three key components module, trunk cable and rack mount enclosure. The system components are 100 percent manufactured, pre-assembled and tested in Germany. They enable plug-and-play installation on site - especially in data centres, but also in industrial environments - within the shortest possible time. The system is characterized by highest packing density and highest flexibility during migration to higher transmission rates. Fibre optic and TP modules can be combined in one rack mount enclosure. 96x fibre optics LC Duplex or 96x MPO connectors can be used modularly on a 19-inch height unit. Thanks to its patented polarity and dark fibre modules, the tML system offers the simplest migration options to 100G and more.

The utility patent protected tML[®] Xtended - module will be installed in the link on one side rotated 180 degrees. The associated tML[®] Xtended trunk cable has a type B pin out. The complete link corresponds to EIA / TIA "Method B". The advantage is that before and after migration uniformly configured patch cables and modules are used.

The tML[®] Xtended - FO Module MPO/MTP[®] is intended for the installation in the tML[®] Rack Mount Enclosure 1U (for 8 x Modules).



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 914 36 99
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

tML[®] Xtended - FO Module 2x MPO/MTP[®] without Pins/12x LC Duplex w. shutter 9/125 μ OS2

Technical Data

The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP[®]plug has a defined fiber height of 1 - 3.5 μ . The max. adjacent fiber height difference is 0.2 μ m and for all fibers 0.3 μ m. All system components (modules, trunk cables and patch cords) are co-ordinated for the reaching of the performance particularly. The module is marked with sequential serial number and article number. The modules are ROHS compliant.

Entry	2 x MPO/MTP [®] Female Adapter (green) back
Exit	12 x LC Duplex Adapter with self-closing shutter (blue) front
Tests	Interferometer, Insertion Loss, Return Loss and Visual Final Inspection; all measured values are electronically archived
	QS-Managementsystem ISO 9001, ISO 14001 and TL 9000

Box	Galvanized steel sheet
Front Panel	Stainless steel
Dimensions	110 x 108 x 20 mm

FO Adapters

Type	MPO/MTP [®]
Application	Singlemode OS2 APC
Design	without Flange
Connector style	SC Simplex
Key Orientation	Type A, Key up/down
Color	Green
Material	Plastic
Sleeve	--
Shutter	--
Standards	IEC 61754-7 TIA 604-5
Manufacturer	US Conec

FO Adapters

When the connector is inserted into the adapter it compress the springs, opening the internal shutter. The internal shutter opens, and due to the special design of the shutter, it will not touch the ferrule end face. As the connector is removed from the adapter, the shutter spring automatically returns the internal shutter to the closed position.

Type	LC Duplex
Application	Singlemode PC
Design	One-Piece without flange
Connector style	SC simplex
Color	Blue

tML[®] Xtended - FO Module 2x MPO/MTP[®] without Pins/12x LC Duplex w. shutter 9/125 μ OS2

Housing material	Plastic
Sleeve	Zirkonia Staight Split
Self-closing shutter material	Metal
Self-closing shutter protection	Dust an laser light
Manufacturer	tde

FO Connectors

The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP[®] plug has a defined fiber height of 1 - 3.5 μ . The max. adjacent fiber height difference is 0.2 μ m and for all fibers 0.3 μ m.

Connector

Type	MPO/MTP [®] Female Push Pull Locking (Green)
Ferrule	12 Fiber SM Elite [®] ferrule, PPS
Boot colour	Black
Temperature range	-40°C bis +75°C
Manufacturer	tde/US Conec

Optical Performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
9/125 μ OS2	MPO/MTP [®] APC	1310 / 1550 nm	≤ 0.10 dB	0.25 dB	75 dB

FO Connectors

Connector Type	LC UPC Unibody Simplex
Housing	Plastic, Blue
Ferrule	Zirconia Straight Split, Spring-loaded Axially
Ferrul Hole	125.5 μ
Ferrule Concentricity	≤ 0.6 μ
Mating Cycles	500
Operating temperature	-40°C up to +75°C
Strain Relief to	100 N
Manufacturer	tde

Optical performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
9/125 μ	LC UPC	1310 / 1550 nm	≤ 0.10 dB	0.25 dB	55 dB

FO Fiber

tML[®] Xtended - FO Module 2x MPO/MTP[®] without Pins/12x LC Duplex w. shutter 9/125 μ m OS2

Type	Draka OS2 9/125 μ m singlemode fiber (C03e)	
Standards and Norms	IEC 60793-2-50 Category B.1.3	ISO/IEC 11801:2002, cat. OS1
	EN 60793-2-50: Class B1.3	ISO/IEC 24702: 2006, cat. OS2; also OS1 requirements are fulfilled
	ITU Recommendation G.652.D – the older ITU designations A, B and C are also fulfilled	IEEE 802.3 – 2002 incl. 802.3ae
	EN 50173-1:2007, cat. OS2; also OS1 requirements are fulfilled	

Attenuation (of cable with fibers) according to IEC 60793-1-40

1310 nm – 1625 nm	≤ 0.39 dB/km
1550 nm	≤ 0.25 dB/km
Inhomogeneity of OTDR trace for any two 1000 metre fiber lengths	Max. 0.1 dB/km

Group index of refraction according to IEC 60793-1-22

Group index of refraction at 1310 nm	1.467
Group index of refraction at 1550 nm	1.468
Group index of refraction at 1625 nm	1.468

Other properties according to IEC 60793-1-xx

Attribute	Measurement method	Limits
Cladding diameter	IEC/EN 60793-1-20	125.0 \pm 0.7 μ m
Cladding non-circularity	IEC/EN 60793-1-20	$\leq 0.7\%$
Core (MFD) non-circularity	IEC/EN 60793-1-20	$\leq 6\%$
Core (MDF) -cladding concentricity error	IEC/EN 60793-1-20	≤ 0.5 μ m
Primary coating diameter - uncoloured	IEC/EN 60793-1-21	242 \pm 7 μ m
Primary coating diameter - coloured	IEC/EN 60793-1-21	250 \pm 15 μ m
Primary coating non-circularity	IEC/EN 60793-1-21	$\leq 5\%$
Primary coating-cladding concentricity error	IEC/EN 60793-1-21	≤ 12.0 μ m
Proof stress level	IEC/EN 60793-1-30	≥ 0.7 GPa ($\approx 1\%$)
Strip force (peak)	IEC/EN 60793-1-32	1.0 N \leq F _{peak.strip} \leq 8.9 N
Chromatic dispersion coefficient In the interval 1285 nm – 1330 nm At 1550 nm At 1625 nm	IEC/EN 60793-1-42	≤ 3 ps/km*nm ≤ 18.0 ps/km*nm ≤ 22.0 ps/km*nm
Zero dispersion wavelength, λ_0		1311 \pm 11 nm
Zero dispersion slope		≤ 0.090 ps/(nm ² *km)
Cut-off wavelength	IEC/EN 60793-1-44	1034 - 1330 λ_c nm ≤ 1260 λ_c nm

tML[®] Xtended - FO Module 2x MPO/MTP[®] without Pins/12x LC Duplex w. shutter 9/125 μ OS2

Mode field diameter at 1310 nm	IEC/EN 60793-1-45	9.0 \pm 0.4 μ m
Mode field diameter at 1550 nm		10.1 \pm 0.5 μ m
Macrobending loss at 1550 nm, 100 turns on a \varnothing 60 mm mandrel.	IEC/EN 60793-1-47	\leq 0.05 dB
Polarisation mode dispersion (PMD) coefficient, cabled	IEC/EN 60793-1-48	\leq 0.5 ps/ \sqrt km
PMDQ Link Design Value:	IEC/EN 60794-3	\leq 0.2 ps/ \sqrt km

Product variants & accessories

Art.-No.	Description
TML-M12LCADS/MP09E-X	tML [®] Xtended - FO Module 2x MPO/MTP [®] without Pins/12x LC APC Duplex w. shutter 9/125 μ OS2
TML-M12LCDS/MP09E-X	tML [®] Xtended - FO Module 2x MPO/MTP [®] without Pins/12x LC Duplex w. shutter 9/125 μ OS2
TML-M12LCDS/MP50G4X	tML [®] Xtended - FO Module 2x MPO/MTP [®] without Pins/12x LC Duplex w. shutter 50/125 μ OM4
TML-M12LCDS/MP50G5X	tML [®] Xtended - FO Module 2x MPO/MTP [®] without Pins/12x LC Duplex w. shutter 50/125 μ OM5