


## 10/100Base-TX (RJ-45) [100 m/328 ft.] to 100Base-X SFP Slot (empty)



The ION C2210 is a media converter module that provides an interface between 10/100Base-TX ports and 100Base-FX ports, allowing users to integrate fiber optic cabling into 10/100 copper environments. Operating at Layer 2, the data link layer, this converter not only converts copper to fiber, it also provides rate conversion allowing legacy 10Base-T copper devices to connect to 100Base-FX fiber. The ION C2210 is a manageable device when installed in a managed ION chassis.

## Features

- Auto-Negotiation of speed and duplex on TP port
- Auto-MDI/MDIX on TP port
- Link Pass Through (LPT)
- Far-End-Fault (FEF) detection
- Pause (Software Controlled)
- Automatic Link Restoration
- Field Upgradeable Firmware
- Can be used in any ION Platform Chassis
- Standards based, will link with any Standard 10/100Base-TX and any Standard 100Base-FX ports



### tde<sup>®</sup> trans data elektronik GmbH

#### Hausanschrift:

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

#### Vertriebsbüro:

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 914 36 99  
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

10/100Base-TX (RJ-45) [100 m/328 ft.] to 100Base-X SFP Slot (empty)

## Manageable Features

- Report converter status to chassis management software:
  - TP and Fiber Link Status
  - Hardware switch settings
  - Copper Port Speed
  - TP and Fiber Port Duplex
  - Fault condition
- Write operation includes:
  - Power on/off device
  - Auto-Negotiation enable/disable
  - Force 10 Mbps or 100 Mbps
  - Force half or full-duplex
  - Select advertising modes when
  - Auto-Negotiation is enabled
  - LPT enable/disable
  - FEF enable/disable
  - Pause enable/disable
  - Auto-MDI/MDIX enable/disable

Note: Manageable Features are available when used in an ION Platform chassis along with an ION Management Module.

## Technische Daten

### Standards

- IEEE 802.3u
- IEEE 802.3x

### Data Rate

- 10 Mbps; 100 Mbps Layer 2

10/100Base-TX (RJ-45) [100 m/328 ft.] to 100Base-X SFP Slot (empty)

## MAC Address Table

- 1K

## Frame Buffer Memory

- 512 Kbits

## Max Frame Size

- 2048 bytes

## Switch

- SW1: Auto-Negotiation (UP = enabled)
- SW2: Forced 100 Mbps/10 Mbps with Auto-Neg. off (UP = 100 Mbps)
- SW3: Forced Full/Half-Duplex with Auto-Neg. off (UP = Full)
- SW4: Full/Half-Duplex on fiber port (UP = Full)
- SW5: Auto-MDI/MDIX on UTP (UP = enabled)
- SW6: Link Pass Through (UP = enabled)

## Internal Jumper

- Auto-MDI/MDIX: Enable/Disable

## Jumper

- Hardware: Mode of operation is determined by the settings on the 4-position switch
- Software: Mode of operation is determined by the most recently saved on-board microprocessor settings

## Status LEDs

- FD (Fiber Duplex): ON= Full-duplex on fiber
- LACT (Fiber Link/Activity): ON = Fiber Link
- PWR (Power): ON=Connection to powered backplane
- (TP. Duplex/Link): Yellow = Half duplex, Green = Full-Duplex
- (TP. Speed): Yellow = 10Mbps, Green = 100 Mbps

## Dimensions

## 10/100Base-TX (RJ-45) [100 m/328 ft.] to 100Base-X SFP Slot (empty)

- Width: 0.86" [22 mm]
- Depth: 6.5" [165 mm]
- Height: 3.4"[86 mm]

### Power Consumption

- 2.5 Watts, 200 mA @ 13.9 VDC

### Environment

- Environment specs are dependent on the chassis chosen
- Operating: 0°C to 50°C
- Humidity: 5% to 95% (non-condensing)
- Altitude: 0 – 10,000 ft.

### Weight

- 1 lb. [0.45 kg]

### MTBF

- Greater than 250,000 hours (MIL-HDBK-217F)
- Greater than 667,500 hours (Bellcore)

### Certifications

- CISPR/EN55022 Class A, FCC Class A, CE Mark, EN55024

### Warranty

- Lifetime

## Artikelvarianten & Zubehör

Art.-Nr.	Beschreibung
C2210-1040	10/100Base-TX (RJ-45) [100 m/328 ft.] to 100Base-X SFP Slot (empty)