


- ION Fast Ethernet Remotely Managed NID Module, 10/100/1000Base-T to 100Base-FX with OAM/IP-Based Management



10/100/1000Base-T (RJ-45) [100 m]

to 100Base-FX 1300nm multimode (SC)

[2 km/1.2 mi.] Link Budget: 11.0 dB

Description

The ION C2220 is a managed Network Interface Device (NID) module that provides an interface between 10/100/1000Base-T ports and 100Base-FX ports, allowing users to manage their links while integrating fiber optic cabling into 10/100/1000 copper environments. As a remotely managed device, the C2220 can be managed individually via an IP address or it can be managed by the ION Management Module when installed in a managed ION chassis. With advanced features like IEEE 802.3ah Link OAM, VLAN, QoS, SSH/SSL, jumbo frame support, and bandwidth allocation, the C2220 providing various methods for secure delivery of Ethernet services in business and mobile backhaul applications.

Features



tde[®] trans data elektronik GmbH

Hausanschrift:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Vertriebsbüro:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 914 36 99
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

- ION Fast Ethernet Remotely Managed NID Module, 10/100/1000Base-T to 100Base-FX with OAM/IP-Based Management

- MEF 9, 14 + 21 certified
- 802.3ah Link OAM
- 10K Jumbo Frame Support
- Two selectable Remote management modes:
 - IP-Based Remote Management
 - In-Band (remote device managed by local peer)
- Auto-MDI/MDIX
- Auto-Negotiation
- Pause
- Link Pass Through
- Far-End-Fault (FEF)
- Remote Loopback
- Field Upgradeable Firmware
- IEEE 802.1p q VLAN and double VLAN tagging with 4096 VIDs
- DHCP client
- SNTP
- TFTP
- RADIUS client
- RMON counters for each port
- Bandwidth profiling
- DMI Optical Management
- Cable diagnostic function for copper ports
- SSH
- Telnet
- Command Line Interface (CLI)
- Web management
- Focal Point management
- SNMP v1, v2c, and v3
- USB port for basic setup
- Management VLAN

Show product on manufacturers website: <https://www.transition.com/products/media-converters/c2220-series/>

Technische Daten

Specifications

- ION Fast Ethernet Remotely Managed NID Module, 10/100/1000Base-T to 100Base-FX with OAM/IP-Based Management

Artikelvarianten & Zubehör

Art.-Nr.	Beschreibung
C2220-1013	- ION Fast Ethernet Remotely Managed NID Module, 10/100/1000Base-T to 100Base-FX with OAM/IP-Based Management