


10/100/1000Base-T (RJ-45) [100 m] to 100Base-FX 1310nm single mode (SC) [20 km/12.4 mi.] Link

Budget: 16.0 dB



Direct Attach Cables / Active Optical Cables

A simple to install, cost-effective and interoperable solution

Often used for data center short-reach interconnects, Direct Attach, Active Copper and Active Optical Cables are an indispensable part of any network.

Terminated with transceiver-style connectors, they are designed to be used in the same ports as a typical SFP+ or QSFP transceiver, with no need for adapters or converters. Our DAC and AOC cables offer compatibility with a huge range of vendors, enabling the connectivity you need within the Top of Rack and End of Row environments.

- 10G, 25G, 40G & 100G product solutions
- Seamless interoperability with network equipment
- Multi-code options enabling different OEM vendors at each end of the cable
- 4x breakout cables, 40G QSFP+ to 4x 10G SFP and 100G QSFP28 to 4x 25G SFP28
- Fast Delivery, Custom solutions
- Compatible with Over 90 Systems
- Savings of up to 70%



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

10/100/1000Base-T (RJ-45) [100 m] to 100Base-FX 1310nm single mode (SC) [20 km/12.4 mi.] Link

Budget: 16.0 dB

The ION C2220 is a managed Network Interface Device (NID) module that provides an interface between 10/100/1000Base-T ports and 100Base-FX ports, allowing users to manage their links while integrating fiber optic cabling into 10/100/1000 copper environments. As a remotely managed device, the C2220 can be managed individually via an IP address or it can be managed by the ION Management Module when installed in a managed ION chassis. With advanced features like IEEE 802.3ah Link OAM, VLAN, QoS, SSH/SSL, jumbo frame support, and bandwidth allocation, the C2220 provides various methods for secure delivery of Ethernet services in business and mobile backhaul applications.

Features

- MEF 9, 14 + 21 certified
- IEEE 802.3ah Link OAM
- 10K Jumbo Frame Support
- Two selectable Remote management modes:
 - IP-Based Remote Management
 - In-Band (remote device managed by local peer)
- Auto-MDI/MDIX
- Auto-Negotiation
- Pause
- Link Pass Through
- Far-End-Fault (FEF)
- Remote Loopback
- Field Upgradeable Firmware
- IEEE 802.1p QoS Packet Classification
- IEEE 802.1q VLAN and double VLAN tagging with 4096 VIDs
- DHCP client
- SNTP
- TFTP
- RADIUS client
- RMON counters for each port
- Bandwidth profiling
- DMI Optical Management
- Cable diagnostic function for copper ports
- SSH
- Telnet
- Command Line Interface (CLI)
- Web management

10/100/1000Base-T (RJ-45) [100 m] to 100Base-FX 1310nm single mode (SC) [20 km/12.4 mi.] Link

Budget: 16.0 dB

- Focal Point management
- SNMP v1, v2c, and v3
- USB port for basic setup
- Management VLAN

Technical Data

Standards

- IEEE 802.3
- IEEE 802.3ah
- IEEE 802.1p
- IEEE 802.1Q

Data Rate

- Copper: 10/100/1000 Mbps
- Fiber: 100 Mbps

Filtering Addresses

- 8K MAC Addresses

Max Frame Size

- 10,240 bytes

Dimensions

- Width: 0.86" [22 mm]
- Depth: 6.5" [165 mm]
- Height: 3.4" [86 mm]

Power Consumption

- 4.5 Watts

Environment

10/100/1000Base-T (RJ-45) [100 m] to 100Base-FX 1310nm single mode (SC) [20 km/12.4 mi.] Link

Budget: 16.0 dB

- Environment specs are dependent on the chassis chosen
- Operating: 0°C to 50°C
- Humidity: 5% to 95% (non-condensing)
- Altitude: 0 – 10,000 ft.

Weight

- 1 lb. [0.45 kg]

Certifications

- EN55022 Class A, EN55024, CE Mark

Warranty

- Lifetime

Product variants & accessories

Art.-No.	Description
C2220-1014	10/100/1000Base-T (RJ-45) [100 m] to 100Base-FX 1310nm single mode (SC) [20 km/12.4 mi.] Link Budget: 16.0 dB