


(2) Coax (BNC) to \*SFP slot (empty)



## Direct Attach Cables / Active Optical Cables

A simple to install, cost-effective and interoperable solution

Often used for data center short-reach interconnects, Direct Attach, Active Copper and Active Optical Cables are an indispensable part of any network.

Terminated with transceiver-style connectors, they are designed to be used in the same ports as a typical SFP+ or QSFP transceiver, with no need for adapters or converters. Our DAC and AOC cables offer compatibility with a huge range of vendors, enabling the connectivity you need within the Top of Rack and End of Row environments.

- 10G, 25G, 40G & 100G product solutions
- Seamless interoperability with network equipment
- Multi-code options enabling different OEM vendors at each end of the cable
- 4x breakout cables, 40G QSFP+ to 4x 10G SFP and 100G QSFP28 to 4x 25G SFP28
- Fast Delivery, Custom solutions
- Compatible with Over 90 Systems
- Savings of up to 70%



**tde<sup>®</sup>** trans data elektronik GmbH

### Headquarter address:

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

### Sales office address:

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 8805 61 13  
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

## (2) Coax (BNC) to \*SFP slot (empty)

The ION C6210 is a managed media converter module that provides a solution for those users that need to extend DS3-T3/E3 connections over fiber. The C6210 is available in versions that support fixed fiber connectors as well as SFP fiber modules offering support for a variety of fiber types, distances, and wavelengths to provide maximum flexibility across a variety of network topologies. CWDM SFPs can also be utilized to further increase the bandwidth capacity of the fiber infrastructure.

The C6210 DS3-T3/E3 converters must be used in pairs. A typical installation will include a modular card installed in a managed ION chassis linked over fiber to a stand-alone S6210 in a remote location.

## Features

- AIS (Alarm Indication Signal)
- Coax Line Build Out
- Switch selectable for DS3/T3 or E3
- Remote firmware upgrade
- Loopback – Coax and Fiber
- LEDs for immediate visual status
- Supports dual or single fiber
- Supports multimode and single mode fiber at a variety of distances
- Supports CWDM SFPs
- SNMP management when used with ION chassis and management module
- Remote stand-alone can be managed by local peer
- Must be used in pairs

## Technical Data

### Standards

- ANSI
- ITU-TS
- ETSI
- G.823 for jitter tolerance
- G.755 for loss of signal

### Connectors

- Coax Connectors 75 ohm coax
- Fiber Connectors SFP: LC connector Uses standard 100Base-X/OC-3
- SFP Fixed Optics: ST or SC connector

## (2) Coax (BNC) to \*SFP slot (empty)

### Data Rate

- DS3/T3 = 44.7 Mbps; E3 = 34.4 Mbps

### Status LEDs

- Power, Coax link status, coax loopback status, AIS on coax link; Fiber link status, fiber loopback status, AIS on fiber link

### Dimensions

- Width: 0.86" [22 mm]
- Depth: 6.5" [165 mm]
- Height: 3.4" [86 mm]

### Power Consumption

- 2.5 Watts

### Environment

- Environment specs are dependent on the chassis chosen
- Operating: 0°C to 50°C
- Humidity: 5% to 95% (non-condensing)
- Altitude: 0 – 10,000 ft.

### Weight

- 1 lb. [0.45 kg]

### MTBF

- Greater than 250,000 hours (MIL-HDBD-217F)
- Greater than 687,000 hours (Bellcore)

### Certifications

- CISPR/EN55022 Class A, FCC Class A, CE Mark

### Warranty

## (2) Coax (BNC) to \*SFP slot (empty)

- Lifetime

## Product variants & accessories

Art.-No.	Description
C6210-3040	(2) Coax (BNC) to *SFP slot (empty)