

TRANSCEIVER- SFP, CC, 1.25G, 1530nm, SM LC, 40km, 3.3V, DMI

## Lantronix / Transition Networks

1000Base-LX/ZX Fiber Channel single mode (LC) with DMI 1530nm [40 km/24.9 mi.] Link Budget: 19.0 dB

## Product Description

1000Base-LX/ZX Fiber Channel single mode (LC) with DMI [40 km/24.9 mi.] Link Budget: 19.0 dB

## Features

- Coarse Wavelength Division Multiplexing (CWDM) ITU Grid Compliant Wavelengths
- Hot-Pluggable SFP Optical Transceiver With Duplex LC Connector
- Digital Diagnostic Function (DMI)
- Class 1 Laser International Safety Standard IEC-60825 Compliant
- Compatible with SFP Multi-Sourcing Agreement (MSA)
- Single +3.3V Power Supply
- RoHS Compliant
- Compliant with IEEE 802.3z 1000Base-LX/ZX
- Compliant with Fiber Channel 1x SM-LC-L FC-PI
- Compliant with IEEE 802.3z 1000Base-LX/ZX
- Compliant with Fiber Channel
- 1x SM-LC-L FC-PI

Show product on manufacturers website: <https://www.lantronix.com/products/>



**tde<sup>®</sup>** trans data elektronik GmbH

**Headquarter address:**

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

**Sales office address:**

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 8805 61 13  
Fax.: +49 231 8805 61 15

[info@tde.de](mailto:info@tde.de) | [www.tde.de](http://www.tde.de)

TRANSCEIVER- SFP, CC, 1.25G, 1530nm, SM LC, 40km, 3.3V, DMI

## Technical Data

## Specifications

## Product variants & accessories

Art.-No.	Description
TN-CWDM-SFP-1530-40	TRANSCEIVER- SFP, CC, 1.25G, 1530nm, SM LC, 40km, 3.3V, DMI