


CWDM-M1631LCR - 16 Channel Mux/Demux CWDM



16 Ch. ,1310-1610nm, Duplex LC

Product Description

Transition Networks CWDM products uses a passive technology that allows for any protocol to be transported over the fiber link, as long as it is at a specific wavelength. Transition Networksâ CWDM Mux/Demux and Add/Drop Mux can provide a simple and affordable method to maximize existing fiber capacity with little or no increased cost.

16 Channel,1310-1610nm, Duplex LC

Features

- Increase bandwidth on existing fiber infrastructure
- Alleviate fiber exhaustion
- Transmit multiple protocols over an existing duplex fiber link by combining the fiber outputs of multiple media converters
- Provide scalable bandwidth of up to 10 Gbps per channel over existing fiberlinks
- Plug-and-Play, no configuration of CWDM components



tde[®] trans data elektronik GmbH

Hausanschrift:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Vertriebsburo:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 914 36 99
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

CWDM-M1631LCR - 16 Channel Mux/Demux CWDM

- Use existing standard optical ports on switches and routers
- Utilize Optical Line Converter as transponder

Show product on manufacturers website: <https://www.transition.com/products/optical-devices/cwdm-m1631lcr/>

Technische Daten

Specifications

Artikelvarianten & Zubehör

Art.-Nr.	Beschreibung
CWDM-M1631LCR	CWDM-M1631LCR - 16 Channel Mux/Demux CWDM