

CWDM-M947LCR - 8 Channel Mux/Demux CWDM

8 Ch. + OSC, 1470-1610 + 1310nm, Duplex LC

Product Description

Transition Networks CWDM products use a passive technology that allows for any protocol to be transported over the fiber link, as long as it is at a specific wavelength. Transition Networks' CWDM Mux/Demux and Add/Drop Mux can provide a simple and affordable method to maximize existing fiber capacity with little or no increased cost.

8 Channel and OSC, 1470-1610 + 1310nm, Duplex LC

Features

- Increase bandwidth on existing fiber infrastructure
- Alleviate fiber exhaustion
- Transmit multiple protocols over an existing duplex fiber link by combining the fiber outputs of multiple media converters
- Provide scalable bandwidth of up to 10 Gbps per channel over existing fiber links
- Plug-and-Play, no configuration of CWDM components
- Use existing standard optical ports on switches and routers

- Utilize Optical Line Converter as transponder

Show product on manufacturer's website: <https://www.transition.com/products/optical-devices/cwdm-m947lcr/>



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 914 36 99
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

CWDM-M947LCR - 8 Channel Mux/Demux CWDM

Technical Data

Specifications

Product variants & accessories

Art.-No.	Description
CWDM-M947LCR	CWDM-M947LCR - 8 Channel Mux/Demux CWDM