

TRANSCEIVER- SFP+, HP Compatible, 10GBASE-SR, 10.3G, MM LC, 850nm, 3.3V DMI

Lantronix / Transition Networks

10Gbase-SR, SFP+ with DMI, multimode 850nm (Duplex LC) [300/82/33 m; 985/269/108 ft.] Link Budget: 4.0 dB

Product Description

10Gbase-SR, SFP+ with DMI, multimode 850nm (Duplex LC) [300/82/33 m; 985/269/108 ft.] Link Budget: 4.0 dB

Features

- SFP+ Optical Transceiver with LC connector
- 10G Small Form-Factor Pluggable (SFP+) MSA compatible
- Compliant with IEEE 802.3ae 10GBase-SR/LR/LW
- SFF-8472 Digital Diagnostic Function (DMI)
- Maximum Link Length of 80KM
- Single +3.3V Power Supply
- RoHS Compliant
- Class 1 Laser International Safety Standard IEC 60825 Compliant

Show product on manufacturers website: <https://www.lantronix.com/products/>



tde[®] trans data elektronik GmbH

Hausanschrift:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Vertriebsbüro:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

TRANSCEIVER- SFP+, HP Compatible, 10GBASE-SR, 10.3G, MM LC, 850nm, 3.3V DMI

Technische Daten

Specifications

Artikelvarianten & Zubehör

Art.-Nr.	Beschreibung
TN-JD092B	TRANSCEIVER- SFP+, HP Compatible, 10GBASE-SR, 10.3G, MM LC, 850nm, 3.3V DMI