


10GBase-LR/LW/10G Fiber Channel, SFP+ with DMI single mode (LC) 1290nm [40 km/24.9 mi.] Link

Budget: 14.1 dB



Lantronix / Transition Networks

Applications include: 10G Ethernet Switches and Routers, xDSL Applications, and Metro Edge Switching.

Features

- Compliant with 10GBase-ER/EW
- SFF-8472 Digital Diagnostic Function (DMI)
- Maximum Link Length of 40 km
- RoHS Compliant
- SFP+ Optical Transceiver with duplex LC connector
- Single +3.3 V Power Supply



tde[®] trans data elektronik GmbH

Hausanschrift:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Vertriebsbüro:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

10GBase-LR/LW/10G Fiber Channel, SFP+ with DMI single mode (LC) 1290nm [40 km/24.9 mi.] Link

Budget: 14.1 dB

Technische Daten

Standards

- IEEE 802.3ae

Output Wavelength

- $-5.5\text{nm} < \lambda_c < +7.5\text{nm}$

Dimensions

- Width: 0.52" [13 mm]
- Depth: 2.18" [55 mm]
- Height: 0.33" [8 mm]

Power Input

- +5V, 3.3V

Environment

- Operating: 0°C to 70°C
- Storage: -40°C to 85°C

Certifications

- IEC-60825, FDA 21, CFR 1040.10 and 1040.11

Warranty

- Lifetime

Artikelvarianten & Zubehör

Art.-Nr.	Beschreibung
TN-CWDM-10G-1290-40	10GBase-LR/LW/10G Fiber Channel, SFP+ with DMI single mode (LC) 1290nm [40 km/24.9 mi.] Link Budget: 14.1 dB