

10GBase-LR/LW/10G Fiber Channel, SFP+ with DMI single mode (LC) 1470nm [80 km/49.8 mi.] Link

Budget: 24.0 dB



Applications include: 10G Ethernet Switches and Routers, xDSL Applications, and Metro Edge Switching.

## Features

- Compliant with 10GBase-ER/EW
- SFF-8472 Digital Diagnostic Function (DMI)
- Maximum Link Length of 80 km
- RoHS Compliant
- SFP+ Optical Transceiver with duplex LC connector
- Single +3.3 V Power Supply



**tde<sup>®</sup>** trans data elektronik GmbH

### Headquarter address:

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

### Sales office address:

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 914 36 99  
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

10GBase-LR/LW/10G Fiber Channel, SFP+ with DMI single mode (LC) 1470nm [80 km/49.8 mi.] Link

Budget: 24.0 dB

## Technical Data

### Standards

- IEEE 802.3ae

### Output Wavelength

- $-5.5\text{nm} < \lambda_c < +7.5\text{nm}$

### Dimensions

- Width: 0.52" [13 mm]
- Depth: 2.18" [55 mm]
- Height: 0.33" [8 mm]

### Power Input

- +5V, 3.3V

### Environment

- Operating: 0°C to 70°C
- Storage: -40°C to 85°C

### Certifications

- IEC-60825, FDA 21, CFR 1040.10 and 1040.11

### Warranty

- Lifetime

## Product variants & accessories

Art.-No.	Description
TN-CWDM-10G-1470-80	10GBase-LR/LW/10G Fiber Channel, SFP+ with DMI single mode (LC) 1470nm [80 km/49.8 mi.] Link Budget: 24.0 dB