

1000Base-LX/Fiber Channel 1x single mode (LC) with DMI 1390nm [80 km/49.7 mi.] Link Budget: 24.0 dB



## Direct Attach Cables / Active Optical Cables

A simple to install, cost-effective and interoperable solution

Often used for data center short-reach interconnects, Direct Attach, Active Copper and Active Optical Cables are an indispensable part of any network.

Terminated with transceiver-style connectors, they are designed to be used in the same ports as a typical SFP+ or QSFP transceiver, with no need for adapters or converters. Our DAC and AOC cables offer compatibility with a huge range of vendors, enabling the connectivity you need within the Top of Rack and End of Row environments.

- 10G, 25G, 40G & 100G product solutions
- Seamless interoperability with network equipment
- Multi-code options enabling different OEM vendors at each end of the cable
- 4x breakout cables, 40G QSFP+ to 4x 10G SFP and 100G QSFP28 to 4x 25G SFP28
- Fast Delivery, Custom solutions
- Compatible with Over 90 Systems
- Savings of up to 70%



**tde®** trans data elektronik GmbH

### Headquarter address:

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

### Sales office address:

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 8805 61 13  
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

1000Base-LX/Fiber Channel 1x single mode (LC) with DMI 1390nm [80 km/49.7 mi.] Link Budget: 24.0 dB

Applications include: Gigabit Ethernet Switches and Routers, Fiber Channel Switch Infrastructure, xDSL Applications, and Metro Edge Switching.

## Features

- Coarse Wavelength Division Multiplexing (CWDM) ITU Grid Compliant Wavelengths
- Hot-Pluggable SFP Footprint Duplex LC Optical Transceiver
- Digital Diagnostic Function (DDF)
- Compatible with SFP Multi-Sourcing Agreement (MSA)
- Compliant with Fiber Channel 1X SM-LC-L FC-PH

## Technical Data

### Standards

- IEEE 802.3 2003
- IEEE 802.3z
- ANSI X3.297-1997

### Output Wavelength

- $-5.5\text{nm} < \lambda_c < +7.5\text{nm}$

### Typical Data Rate

- 1250Mbps

### Minimum Data Rate

- 100Mbps

### Dimensions

- Width: 0.52" [13 mm]
- Depth: 2.18" [55 mm]
- Height: 0.33" [8 mm]

1000Base-LX/Fiber Channel 1x single mode (LC) with DMI 1390nm [80 km/49.7 mi.] Link Budget: 24.0 dB

## Power Consumption

- 0.66 Watts

## Power Input

- 3.3V

## Environment

- Operating: 0°C to 70°C

## Certifications

- IEC-60825, FDA 21, CFR 1040.10 and 1040.11

## Warranty

- Lifetime

## Product variants & accessories

Art.-No.	Description
TN-SFP-LX8-C39	1000Base-LX/Fiber Channel 1x single mode (LC) with DMI 1390nm [80 km/49.7 mi.] Link Budget: 24.0 dB