

## TRANSCEIVER- SFP,GIG E,LX,CWDM,1410NM,SM LC,80KM,3.3V,W/DMI

1000Base-LX/Fiber Channel 1x single mode (LC) with DMI 1410nm [80 km/49.7 mi.] Link Budget: 24.0 dB

### Product Description

1000Base-LX/Fiber Channel 1x single mode (LC) with DMI [80 km/49.7 mi.] Link Budget: 24.0 dB

### Features

- Coarse Wavelength Division Multiplexing (CWDM) ITU Grid Compliant Wavelengths
- Hot-Pluggable SFP Footprint Duplex LC Optical Transceiver
- Digital Diagnostic Function (DMI)
- Class 1 Laser International Safety Standard IEC-60825 Compliant
- Compatible with SFP Multi-Sourcing Agreement (MSA)
- Compliant with Fiber Channel 1X SM-LC-L FC-PI (Can be used on Optical Line Converter xFMFF4040-100)

Show product on manufacturers website: <https://www.transition.com/products/optical-devices/tn-sfp-lx8-cxx/>



**tde<sup>®</sup> trans data elektronik GmbH**

**Headquarter address:**

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

**Sales office address:**

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 914 36 99  
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

TRANSCEIVER- SFP,GIG E,LX,CWDM,1410NM,SM LC,80KM,3.3V,W/DMI

## Technical Data

## Specifications

## Product variants & accessories

Art.-No.	Description
TN-SFP-LX8-C41	TRANSCEIVER- SFP,GIG E,LX,CWDM,1410NM,SM LC,80KM,3.3V,W/DMI