

TRANSCEIVER- SFP,GIG E,LX,CWDM,1550NM,SM LC,80KM,3.3V,W/DMI

Direct Attach Cables / Active Optical Cables

A simple to install, cost-effective and interoperable solution

Often used for data center short-reach interconnects, Direct Attach, Active Copper and Active Optical Cables are an indispensable part of any network.

Terminated with transceiver-style connectors, they are designed to be used in the same ports as a typical SFP+ or QSFP transceiver, with no need for adapters or converters. Our DAC and AOC cables offer compatibility with a huge range of vendors, enabling the connectivity you need within the Top of Rack and End of Row environments.

- 10G, 25G, 40G & 100G product solutions
- Seamless interoperability with network equipment
- Multi-code options enabling different OEM vendors at each end of the cable
- 4x breakout cables, 40G QSFP+ to 4x 10G SFP and 100G QSFP28 to 4x 25G SFP28
- Fast Delivery, Custom solutions
- Compatible with Over 90 Systems
- Savings of up to 70%

1000Base-LX/Fiber Channel 1x single mode (LC) with DMI 1550nm [80 km/49.7 mi.] Link Budget: 24.0 dB

Product Description

1000Base-LX/Fiber Channel 1x single mode (LC) with DMI [80 km/49.7 mi.]

Link Budget: 24.0 dB

Features

- Coarse Wavelength Division Multiplexing (CWDM) ITU Grid Compliant Wavelengths
- Hot-Pluggable SFP Footprint Duplex LC Optical Transceiver
- Digital Diagnostic Function (DMI)
- Class 1 Laser International Safety Standard IEC-60825 Compliant
- Compatible with SFP Multi-Sourcing Agreement (MSA)
- Compliant with Fiber Channel 1X SM-LC-L FC-PI (Can be used on Optical Line Converter xFMFF4040-100)

Show product on manufacturers website: <https://www.lantronix.com/products/>



tde[®] trans data elektronik GmbH

Hausanschrift:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Vertriebsbüro:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

TRANSCEIVER- SFP,GIG E,LX,CWDM,1550NM,SM LC,80KM,3.3V,W/DMI

Technische Daten

Specifications

Artikelvarianten & Zubehör

Art.-Nr.	Beschreibung
TN-SFP-LX8-C55	TRANSCEIVER- SFP,GIG E,LX,CWDM,1550NM,SM LC,80KM,3.3V,W/DMI