


100Base-FX 1310nm single mode (LC) [10 km/6.2 mi.] Link Budget: 19.0 dB; UL Listed



Direct Attach Cables / Active Optical Cables

A simple to install, cost-effective and interoperable solution

Often used for data center short-reach interconnects, Direct Attach, Active Copper and Active Optical Cables are an indispensable part of any network.

Terminated with transceiver-style connectors, they are designed to be used in the same ports as a typical SFP+ or QSFP transceiver, with no need for adapters or converters. Our DAC and AOC cables offer compatibility with a huge range of vendors, enabling the connectivity you need within the Top of Rack and End of Row environments.

- 10G, 25G, 40G & 100G product solutions
- Seamless interoperability with network equipment
- Multi-code options enabling different OEM vendors at each end of the cable
- 4x breakout cables, 40G QSFP+ to 4x 10G SFP and 100G QSFP28 to 4x 25G SFP28
- Fast Delivery, Custom solutions
- Compatible with Over 90 Systems
- Savings of up to 70%



tde® trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

100Base-FX 1310nm single mode (LC) [10 km/6.2 mi.] Link Budget: 19.0 dB; UL Listed

Applications include: Fast Ethernet Switches & Routers, Fiber Channel Switch Infrastructure, xDSL Applications, and Metro Edge Switching.

Features

- Hot-Pluggable SFP Footprint Duplex LC Optical Transceiver
- Compliant with SFP Multi-Sourcing Agreement (MSA)
- Compliant with 100Base-FX
- Compliant with Intermediate-Reach SONET OC-3/SDH STM-1 (S-1.1)
- Can be used on Optical Line Converter xFMFF4040-100

Technical Data

Standards

- IEEE 802.3
- IEEE 802.3ah

Dimensions

- Width: 0.52" [13 mm]
- Depth: 2.18" [55 mm]
- Height: 0.33" [8 mm]

Power Consumption

- 1.0 Watts

Power Input

- 3.3V

Environment

- Operating: 0°C to 70°C
- Storage: -40°C to 85°C
- TN-GLC-xxx-RGD

- Operating: -40°C to 85°C
- Storage: -40°C to 100°C

100Base-FX 1310nm single mode (LC) [10 km/6.2 mi.] Link Budget: 19.0 dB; UL Listed

Certifications

- IEC-60825, FDA 21, CFR 1040.10 and 1040.11; UL Listed (specific SKUs only)

Warranty

- Lifetime

Product variants & accessories

Art.-No.	Description
TN-GLC-FE-100LX	100Base-FX 1310nm single mode (LC) [10 km/6.2 mi.] Link Budget: 19.0 dB; UL Listed