


Gigabit Ethernet PCIe NIC with a 100/1000Base-X Open SFP fiber slot + 10/100/1000Base-T PoE+ port
(includes optional low-profile bracket)



The N-GXE-POE-xx-01 Series is a Fiber Gigabit Ethernet PCIe Network Interface Card (NIC) which provides connectivity to a secure fiber network while also delivering power to a PoE powered device (PD), such as a VoIP phone, with a copper UTP interface. It fully complies with all IEEE 802.3z and 1000Base-X standards, providing up to 2000 Mbps full-duplex bandwidth capacity.

Developed to support high-end users, this (2) port NIC has (1) 1000Base-X fiber network interface port (SFP version is 100/1000Base-X) and (1) switched 10/100/1000Base-T port supporting IEEE 802.3at PoE+ power. It is designed to allow a PC to power a VoIP phone, or any other traditional copper powered device, over a secure fiber network. Additionally, the NIC also has the ability to provide traffic switching functions between the copper and fiber ports, even when the PC is in a sleep mode.

Combining the functions of PC connectivity and VoIP phone connectivity into one device saves installation time, expense, and the space of having two devices at the desktop. When the VoIP traffic is filtered and prioritized by third-party devices like an Ethernet switch and the IP phone, this PoE NIC will pass all tagged traffic ensuring users experience a high level of Quality of Service (QoS). VLANs and Prioritization can also be configured at the NIC via Lantronix' PoE NIC utility software.

Features



tde[®] trans data elektronik GmbH

Hausanschrift:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Vertriebsbüro:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 914 36 99
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

Gigabit Ethernet PCIe NIC with a 100/1000Base-X Open SFP fiber slot + 10/100/1000Base-T PoE+ port
(includes optional low-profile bracket)

- High bandwidth 1000Mbps
 - Supports Full-duplex Mode
 - Supports IEEE 802.3x Full-Duplex Flow Control
 - Supports PCIe x1 bus
 - Compliant with PCIe Rev 2.1 Interface
 - Supports Jumbo Frames
 - Supports High Level VLAN Filtering Function
 - IPv6 capable
 - Supports IP headers and TCP/UDP checksum offload
 - Wake-on-LAN (WoL) power management
 - PXE 2.1 Boot ROM Supported
 - ACPI 2.0 Link Status LED for each port
 - Driver Support
-
- Windows 7
 - Windows 8, 8.1
 - Windows 10
 - Windows Server 2008
 - Windows Server 2012
 - Vista
 - Linux
-
- Available with a fixed LC port or an open SFP port

Technische Daten

Standards

- IEEE 802.3-2000
- IEEE 802.3z
- IEEE 802.3x
- IEEE 802.1Q
- IEEE 802.1P
- IEEE 802.3ab
- IEEE 802.3af
- IEEE 802.3at

MAC Address

Gigabit Ethernet PCIe NIC with a 100/1000Base-X Open SFP fiber slot + 10/100/1000Base-T PoE+ port
(includes optional low-profile bracket)

- 8k MAC address table

Max Packet Size

- Jumbo Frames, 10k bytes

Jumper Switches

- Legacy PoE
- Energy Efficient Ethernet (EEE) enable/disable

Status LEDs

- L/A Fiber Link/Activity
- PoE Power-over-Ethernet
- RJ-45 Upper Lf TP Link/Activity/Speed
- RJ-45 Upper Rt TP Duplex

Dimensions

- Width: 4.8" [121.9 mm]
- Depth: 6.5" [165.1 mm]
- Height: 0.9" [22.86 mm]

Power Consumption

- 1.6 Watts (typical without PoE)
- 43.6 Watts (typical with PoE)

Voltage Input

- PCIe 3.3V
- 12V Peripheral connection for PoE

PoE

- Mode A Power

Environment

Gigabit Ethernet PCIe NIC with a 100/1000Base-X Open SFP fiber slot + 10/100/1000Base-T PoE+ port
(includes optional low-profile bracket)

- Operating: 0°C to 50°C
- Storage: -15°C to 65°C
- Humidity: 5% to 95% (non-condensing)
- Altitude: 0 – 10,000 ft.

Weight

- 2 lbs. [0.90 kg]

MTBF

- Greater than 260,500 MIL-HDBK-217F Hours
- Greater than 716,375 Bellcore Hours

Certifications

- Emission: EN55022 Class B, CE, UL Listed
- Immunity: EN55024

Warranty

- Lifetime

Artikelvarianten & Zubehör

Art.-Nr.	Beschreibung
N-GXE-POE-SFP-01	Gigabit Ethernet PCIe NIC with a 100/1000Base-X Open SFP fiber slot + 10/100/1000Base-T PoE+ port (includes optional low-profile bracket)