

Industrial DIN Rail Mounted Power Supply: 48VDC, 39.8Watts



Industrial DIN Rail Mounted Power Supply

48VDC, 39.8Watts

Features

- Variable AC input range
- Protected against:
 - Overload
 - Over Voltage
- Convection air cooling
- DIN rail mountable
- UL 508 approved
- Full load burn in test
- RoHS Compliant



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 914 36 99
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

Industrial DIN Rail Mounted Power Supply: 48VDC, 39.8Watts

Technical Data

Power Output

- Output Voltage 48VDC
- Current Rating: 0.83A
- Power Rating: 39.8 Watts
- Ripple & Noise Max 120mVp-p
- Voltage Range: 48~56VDC
- Voltage Tolerance $\pm 1.0\%$
- Line Regulation: $\pm 1.0\%$
- Load Regulation $\pm 1.0\%$
- Setup, Rise Time 300ms, 30ms
- Hold Up Time: 20ms/115VAC

Power Input

- Voltage Range Switch Selectable: 88~264VAC, 120~370VDC
- Frequency Range: 47~63Hz
- Efficiency: 88%
- AC Current (Typical): ,
- Inrush Current (Cold): ,
- Leakage Current: <

Protection

- Overload 105~160%
- Overvoltage: 57.6~64.8V

Dimensions

- Width: 1.57" [40 mm]
- Depth: 3.94" [100 mm]
- Height: 3.54" [90 mm]

Environment

- Operating: -20°C to +70°C
- Storage: -40°C to +85°C
- Humidity: 20% to 90% (non-condensing)

Weight

Industrial DIN Rail Mounted Power Supply: 48VDC, 39.8Watts

- 0.66 lbs. [0.3 kg]

MTBF

- 301.7Khrs

Certifications

- Safety: UL508, TUV EN60950-1, NEC Class 2, LPS Compliant, UL60950-1, EN55011, EN55022, CISPR22, EN61204-3 Class B, EN61000-3-2, EN61000-3-3, EN61000-4-2, EN61000-4-3, EN61000-4-4, EN61000-4-5, EN61000-4-6, EN61000-4-8, EN61000-4-11, EN55024, EN61000-6-2, EN50082-2, EN61204-3 A, IEC60068-2-6 (Vibration)

Warranty

- Lifetime

Product variants & accessories

Art.-No.	Description
25130	Industrial DIN Rail Mounted Power Supply: 48VDC, 39.8Watts