

Dry Contact Relay Module for DC Power Supply



Direct Attach Cables / Active Optical Cables

A simple to install, cost-effective and interoperable solution

Often used for data center short-reach interconnects, Direct Attach, Active Copper and Active Optical Cables are an indispensable part of any network.

Terminated with transceiver-style connectors, they are designed to be used in the same ports as a typical SFP+ or QSFP transceiver, with no need for adapters or converters. Our DAC and AOC cables offer compatibility with a huge range of vendors, enabling the connectivity you need within the Top of Rack and End of Row environments.

- 10G, 25G, 40G & 100G product solutions
- Seamless interoperability with network equipment
- Multi-code options enabling different OEM vendors at each end of the cable
- 4x breakout cables, 40G QSFP+ to 4x 10G SFP and 100G QSFP28 to 4x 25G SFP28
- Fast Delivery, Custom solutions
- Compatible with Over 90 Systems
- Savings of up to 70%



tde® trans data elektronik GmbH

Hausanschrift:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Vertriebsbüro:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

Dry Contact Relay Module for DC Power Supply

The IONDCR-R1 is a field installable dry contact relay module for the IONPS-D-R1 power supply. This module mounts in the lower right-hand corner of the IONPS-D-R1 face-plate, allowing the power supply to be tied into a separate alarm circuit. Contacts will be activated by various configurable conditions, enabling an external visual or audible alarm.

Technische Daten

MTBF

- Greater than 250,000 Hours (MIL-HDBK-217F)
- Greater than 687,500 Hours (Bellcore)

Artikelvarianten & Zubehör

Art.-Nr.	Beschreibung
IONDCR-R1	Dry Contact Relay Module for DC Power Supply