

TRANSCEIVER- SFP, 1300nm, Extended SX, 1.25GIG, 50UM FIBER, LC

Lantronix / Transition Networks

1000Base-SX 1300nm extended multimode (Duplex LC) [50/125 $\hat{1}$ / $\frac{1}{4}$ m fiber only: up to 2 km/1.2 mi.] with DMI, Link Budget: 8.0 dB

Product Description

1000Base-SX 1300nm extended multimode (Duplex LC) [50/125 $\hat{1}$ / $\frac{1}{4}$ m fiber only: up to 2 km/1.2 mi.] with DMI, Link Budget: 8.0 dB

Features

- Hot-Pluggable SFP Footprint Optical Transceiver
- Digital Diagnostic Function
- Class 1 Laser International Safety Standard IEC-60825 Compliant
- Compatible with SFP Multi-Sourcing Agreement (MSA)

Show product on manufacturers website: <https://www.lantronix.com/products/>



tde[®] trans data elektronik GmbH

Hausanschrift:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Vertriebsbüro:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

TRANSCEIVER- SFP, 1300nm, Extended SX, 1.25GIG, 50UM FIBER, LC

Technische Daten

Specifications

Artikelvarianten & Zubehör

Art.-Nr.	Beschreibung
TN-SFP-ESX5	TRANSCEIVER- SFP, 1300nm, Extended SX, 1.25GIG, 50UM FIBER, LC