

tML[®] 24 - FO Patch cord both sides MPO24 Female 24G50/125 μ OM5 100GbE, Type A, Length: xxx in

m



tML[®] - tde Modular Link

tML[®] is a patented, modular cabling system consisting of the three key components module, trunk cable and rack mount enclosure. The system components are 100 percent manufactured, pre-assembled and tested in Germany. They enable plug-and-play installation on site - especially in data centres, but also in industrial environments - within the shortest possible time. The system is characterized by highest packing density and highest flexibility during migration to higher transmission rates. Fibre optic and TP modules can be combined in one rack mount enclosure. 96x fibre optics LC Duplex or 96x MPO connectors can be used modularly on a 19-inch height unit. Thanks to its patented polarity and dark fibre modules, the tML system offers the simplest migration options to 100G and more.



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 914 36 99
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

tML[®] 24 - FO Patch cord both sides MPO24 Female 24G50/125 μ OM5 100GbE, Type A, Length: xxx in
m

Technical Data

The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP[®] plug has a defined fiber height of 1 - 3.5 μ . The max. adjacent fiber height difference is 0.2 μ m and for all fibers 0.3 μ m.

Cable	Round cable 3.6 mm, loose tube, LSOH, limegreen
Connectors	MPO/MTP [®] Push Pull (limegreen)
Pin out	Type A
Tests	Interferometer, Insertion Loss, Return Loss and Visual Final Inspection; all measured values are electronically archived
	QS-Managementsystem ISO 9001, ISO 14001 and TL 9000

FO Connectors

The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP[®] plug has a defined fiber height of 1 - 3.5 μ . The max. adjacent fiber height difference is 0.2 μ m and for all fibers 0.3 μ m.

Connector

Type	MPO/MTP [®] Female Push Pull Locking
Ferrule	24 Fiber MM Elite [®] ferrule, PPS
Boot colour	Red
Temperature range	-40°C to +75°C
Manufacturer	tde/US Conec

Optical Performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
50/125 μ OM5	MPO/MTP [®]	850 nm	≤ 0.16 dB	0.30 dB	30 dB

FO Cables

Loose tube

Loose tube	unfilled (FRNC)
Wall thickness PVC-tube	0.35 mm – 0.40 mm
Outer diameter	2.6 mm with 24 optical fibres
Tube colour	green
Colour code fibres (1-12)	red, green, blue, yellow, white, grey, brown, violet, turquoise, black, orange, pink
Colour code fibres (13-24)	red, green, blue, yellow, white, grey, brown, violet, turquoise, transparent, orange, pink (always with black ring marking, except transparent)

tML[®] 24 - FO Patch cord both sides MPO24 Female 24G50/125 μ OM5 100GbE, Type A, Length: xxx in
m

Strain relief elements

Strain relief elements	Aramid
Strength members	Fiberglass-reinforced plastic (FRP)

Outer jacket

Outer jacket	Halogen-free and flame-retardant material (FRNC)
Wall thickness	approx. 0.4 mm
Outer diameter	approx. 3.8 mm
Colour	lime green
Inkjet - marking (black)	t d e – IVH24G50–MPO-OM5 LSZH (F.RoHS)

Mechanical characteristics

Min. bending radius fixed (static) acc. IEC 60794-1-2 E11A	10 x outside diameter
Min. bending radius during assembly (dynamic), with additional tensile strain acc. IEC 60794-1-2 E6	15 x outside diameter
Max. tensile force acc. IEC 60794-1-2 E1, short term	300 N
Max. crush resistance acc. IEC 60794-1-2 E3, long term	150 N/dm
Max. crush resistance acc. IEC 60794-1-2 E3, short term	1500 N/dm
Cable weight	20.0 kg/km

Thermal characteristics

Transport and storage	-40°C to +80°C
Verlegung	-20°C to +50°C
In use acc. IEC 60794-1-2 F1	-40°C to +80°C

Fire performance

Cable is flame-retardant	acc. to IEC 60332-1-2
Smoke density	acc. to IEC 61034
Halogen-free	acc. to IEC 60754-1
Acidity of the combustion gases	acc. to IEC 60754-2
Fire load	0.26 MJ/m

Chemical characteristics	No resistance to oil, petrol, acid and leach
Standardisation	IEC 60794-2

tML[®] 24 - FO Patch cord both sides MPO24 Female 24G50/125 μ OM5 100GbE, Type A, Length: xxx in
m

FO Fiber

Type	Corning ClearCurve [®] 50/125 μ OM5 multimode fiber
Design	Optical fibre G50/125 μ m (conform to IEC 60793-2-10 type A1a.4b) with optical core 50 μ m +/- 2.5 μ m diameter and optical cladding 125 μ m +/- 1 μ m diameter

Geometrical properties

Core concentricity error	< 5 %
Coating concentricity error	< 1 %
Core coating eccentricity	< 1.5 μ m
Eccentricity of coating	< 12 μ m
Screen test	\geq 0.7 GPa (100 kpsi)

Transmission characteristics

Attenuation, maximum values 850 nm (cabled fibre)	2.5 dB/km
Attenuation, maximum values 953 nm (cabled fibre)	1.8 dB/km
Attenuation, maximum values 1300 nm (cabled fibre)	0.7 dB/km
Attenuation, maximum values 850 nm (uncabled fibre)	2.34 dB/km
Attenuation, maximum values 953 nm (uncabled fibre)	1.7 dB/km
Attenuation, maximum values 1300 nm (uncabled fibre)	0.64 dB/km
Macrobending, induced attenuation 100 turns, 37.5 mm	\leq 0.5 dB (at 850 nm)
Macrobending, induced attenuation 100 turns, 37.5 mm	\leq 0.5 dB (at 1300 nm)
Macrobending, induced attenuation 2 turns, 15 mm	\leq 0.1 dB (at 850 nm)
Macrobending, induced attenuation 2 turns, 15 mm	\leq 0.3 dB (at 1300 nm)
Macrobending, induced attenuation 2 turns, 7.5 mm	\leq 0.3 dB (at 850 nm)
Macrobending, induced attenuation 2 turns, 7.5 mm	\leq 0.5 dB (at 1300 nm)
Bandwidth (OFL), minimum values 850 nm	3500 MHz x km
Bandwidth (OFL), minimum values 953 nm	1850 MHz x km
Bandwidth (OFL), minimum values 1300 nm	500 MHz x km
Effective modal Bandwidth-length product min. 850 nm	4700 MHz x km

tML[®] 24 - FO Patch cord both sides MPO24 Female 24G50/125 μ OM5 100GbE, Type A, Length: xxx in m

Effective modal Bandwidth-length product min. 953 nm	2470 MHz x km
Numerical aperture	0.200 +/- 0.015
Effective group of refraction 850 nm	1.482
Effective group of refraction 1300 nm	1.477

Product variants & accessories

Art.-No.	Description
TMLM2/M2-09I24E-Axxx	tML [®] 24 - FO Patch cord both sides MPO24 Female 24E9/125 μ OS2 100GbE, Type A, Length: xx in m
TMLM2/M2-50I24G3Axxx	tML [®] 24 - FO Patch cord both sides MPO24 Female 24G50/125 μ OM3 100GbE, Type A, Length: xxx in m
TMLM2/M2-50I24G4Axxx	tML [®] 24 - FO Patch cord both sides MPO24 Female 24G50/125 μ OM4 100GbE, Type A, Length: xxx in m
TMLM2/M2-50I24G5Axxx	tML [®] 24 - FO Patch cord both sides MPO24 Female 24G50/125 μ OM5 100GbE, Type A, Length: xxx in m