

tML<sup>®</sup> 24 - FO Module 5HP black 1x 24F MPO/MTP<sup>®</sup>/12x LC Duplex w. shutter 50/125μ OM5



## tML<sup>®</sup> - tde Modular Link

tML<sup>®</sup> is a patented, modular cabling system consisting of the three key components module, trunk cable and rack mount enclosure. The system components are 100 percent manufactured, pre-assembled and tested in Germany. They enable plug-and-play installation on site – especially in data centres, but also in industrial environments – within the shortest possible time. Heart of the system are the rear MPO/MTP<sup>®</sup> and Telco connectors, which can be used to connect at least six or twelve ports at a time. Depending on the module configuration, transfer rates of up to 200G are currently possible with SR4. The fibre optic and TP modules can be used together in a module carrier with a very high port density. The tde offers its tML<sup>®</sup> cabling system as a proven tML<sup>®</sup> standard system and in the highly innovative variants tML<sup>®</sup> Xtended, tML<sup>®</sup> 24 System and now tML<sup>®</sup> 32 System for extreme scalability and very easy migration to higher transmission rates such as 40G, 100G, 200G and 400G.

The utility patent protected tML<sup>®</sup> 24 - FO Module MPO/MTP<sup>®</sup> is intended for the installation in the tML<sup>®</sup> Rack Mount Enclosure 3U (for 8 x Modules). The module configuration guarantees an extremely easy migration from 1GbE to 100GbE because there can always be worked on both sides with uniformly configured modules and patch cables. The tML<sup>®</sup> 24 module can be used only in conjunction with the tML<sup>®</sup>HD patch cord. A special cleaning tool is required



**tde<sup>®</sup> trans data elektronik GmbH**

**Headquarter address:**

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

**Sales office address:**

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 8805 61 13  
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

tML® 24 - FO Module 5HP black 1x 24F MPO/MTP®/12x LC Duplex w. shutter 50/125µ OM5

to clean the adapters with shutter.

## Technical Data

The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP®plug has a defined fiber height of 1 - 3.5µ. The max. adjacent fiber height difference is 0.2µm and for all fibers 0.3µm. All system components (modules, trunk cables and patch cords) are co-ordinated for the reaching of the performance particularly. The module is marked with sequential serial number and article number. The modules are ROHS compliant.

Entry	1 x MPO/MTP®Female Adapter (red) back
Exit	6 x LC Quad Adapter (limegreen) front
Tests	Interferometer, Insertion Loss, Return Loss and Visual Final Inspection; all measured values are electronically archived
	QS-Managementsystem ISO 9001, ISO 14001 and TL 9000

Box	Galvanized steel sheet
Front Panel	black

## FO Adapters

Type	MPO/MTP®
Application	Singlemode / Multimode
Design	without Flange
Connector style	SC Simplex
Key Orientation	Type A, Key up/down
Color	Red
Material	Plastic
Sleeve	--
Shutter	--
Standards	IEC 61754-7 TIA 604-5
Manufacturer	US Conec

## FO Adapters

When the connector is inserted into the adapter it compress the springs, opening the internal shutter. The internal shutter opens, and due to the special design of the shutter, it will not touch the ferrule end face. As the connector is removed from the adapter, the shutter spring automatically returns the internal shutter to the closed position.

Type	LC Duplex
Application	Multimode OM5
Design	One-Piece without flange

## tML® 24 - FO Module 5HP black 1x 24F MPO/MTP®/12x LC Duplex w. shutter 50/125µ OM5

Connector style	SC simplex
Color	Limegreen
Housing material	Plastic
Sleeve	Zirkonia Staight Split
Self-closing shutter material	Metal
Self-closing shutter protection	Dust an laser light
Manufacturer	tde

### FO Connectors

The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP® plug has a defined fiber height of 1 - 3.5µ. The max. adjacent fiber height difference is 0.2µm and for all fibers 0.3µm.

#### Connector

Type	MPO/MTP® Female Push Pull Locking
Ferrule	24 Fiber MM Elite® ferrule, PPS
Boot colour	Red
Temperature range	-40°C to +75°C
Manufacturer	tde/US Conec

#### Optical Performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
50/125µ OM5	MPO/MTP®	850 nm	≤ 0.11 dB	0.25 dB	35 dB

### FO Connectors

Connector Type	LC Unibody Simplex
Housing	Plastic, Limegreen
Ferrule	Zirkonia Staight Split, Spring-loaded Axially
Ferrule Hole	126 µ
Mating Cycles	1.000
Operating Temperature	-40°C up to +75°C
Strain Relief to	100 N
Manufacturer	tde

#### Optical performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
50/125µ OM5	LC	850 nm	≤ 0.10 dB	0.30 dB	35 dB

tML® 24 - FO Module 5HP black 1x 24F MPO/MTP®/12x LC Duplex w. shutter 50/125µ OM5

## FO Fiber

Type	Corning ClearCurve® 50/125µ OM5 multimode fiber
Design	Optical fibre G50/125 µm (conform to IEC 60793-2-10 type A1a.4b) with optical core 50 µm +/- 2.5 µm diameter and optical cladding 125 µm +/- 1 µm diameter

## Geometrical properties

Core concentricity error	< 5 %
Coating concentricity error	< 1 %
Core coating eccentricity	< 1.5 µm
Eccentricity of coating	< 12 µm
Screen test	≥ 0.7 GPa (100 kpsi)

## Transmission characteristics

Attenuation, maximum values 850 nm (cabled fibre)	2.5 dB/km
Attenuation, maximum values 953 nm (cabled fibre)	1.8 dB/km
Attenuation, maximum values 1300 nm (cabled fibre)	0.7 dB/km
Attenuation, maximum values 850 nm (uncabled fibre)	2.34 dB/km
Attenuation, maximum values 953 nm (uncabled fibre)	1.7 dB/km
Attenuation, maximum values 1300 nm (uncabled fibre)	0.64 dB/km
Macrobending, induced attenuation 100 turns, 37.5 mm	≤ 0.5 dB (at 850 nm)
Macrobending, induced attenuation 100 turns, 37.5 mm	≤ 0.5 dB (at 1300 nm)
Macrobending, induced attenuation 2 turns, 15 mm	≤ 0.1 dB (at 850 nm)
Macrobending, induced attenuation 2 turns, 15 mm	≤ 0.3 dB (at 1300 nm)
Macrobending, induced attenuation 2 turns, 7.5 mm	≤ 0.3 dB (at 850 nm)
Macrobending, induced attenuation 2 turns, 7.5 mm	≤ 0.5 dB (at 1300 nm)
Bandwidth (OFL), minimum values 850 nm	3500 MHz x km
Bandwidth (OFL), minimum values 953 nm	1850 MHz x km
Bandwidth (OFL), minimum values 1300 nm	500 MHz x km
Effective modal Bandwidth-length product min. 850 nm	4700 MHz x km
Effective modal Bandwidth-length product min. 953 nm	2470 MHz x km
Numerical aperture	0.200 +/- 0.015

tML® 24 - FO Module 5HP black 1x 24F MPO/MTP®/12x LC Duplex w. shutter 50/125µ OM5

Effective group of refraction 850 nm	1.482
Effective group of refraction 1300 nm	1.477

## Product variants & accessories

Art.-No.	Description
L-CLEAN-SMART1.25-R	FO Replacement Cartridges for Cleaning Tool 1,25mm for LC Duplex Adapter with self-closing shutter
L-CLEAN-SMART-CS1.25	FO Cleaning Tool 1,25mm for CS and LC Duplex Adapter with self-closing shutter
TML-T12LCADK/M2-09ES	tML® 24 - FO Module 5HP black 1x 24F MPO/MTP®/12x LC APC Duplex 9/125µ OS2
TML-T12LCDK/M2-09ES	tML® 24 - FO Module 5HP black 1x 24F MPO/MTP®/12x LC Duplex 9/125µ OS2
TML-T12LCDK/M2-50G3S	tML® 24 - FO Module 5HP black 1x 24F MPO/MTP® /12x LC Duplex 50/125µ OM3
TML-T12LCDK/M2-50G4S	tML® 24 - FO Module 5HP black 1x 24F MPO/MTP®/12x LC Duplex 50/125µ OM4
TML-T12LCDS/M2-50G5S	tML® 24 - FO Module 5HP black 1x 24F MPO/MTP®/12x LC Duplex w. shutter 50/125µ OM5