

tML[®] Xtended - FO Micro Distribution trunk cable both sides 2xMPO/MTP[®] w. Pins 24G50/125 μ OM5
LSHF, Type B, Length: xx in m



tML[®] - tde Modular Link

tML[®] is a patented, modular cabling system consisting of the three key components module, trunk cable and rack mount enclosure. The system components are 100 percent manufactured, pre-assembled and tested in Germany. They enable plug-and-play installation on site – especially in data centres, but also in industrial environments – within the shortest possible time. Heart of the system are the rear MPO/MTP[®] and Telco connectors, which can be used to connect at least six or twelve ports at a time. Depending on the module configuration, transfer rates of up to 200G are currently possible with SR4. The fibre optic and TP modules can be used together in a module carrier with a very high port density. The tde offers its tML[®] cabling system as a proven tML[®] standard system and in the highly innovative variants tML[®] Xtended, tML[®] 24 System and now tML[®] 32 System for extreme scalability and very easy migration to higher transmission rates such as 40G, 100G, 200G and 400G.



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

tML[®] Xtended - FO Micro Distribution trunk cable both sides 2xMPO/MTP[®] w. Pins 24G50/125 μ OM5
LSHF, Type B, Length: xx in m

Technical Data

The tML[®]- FO Micro Distribution trunk cable is preterminated with MPO/MTP[®]connectors on both ends. The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP[®]plug has a defined fiber height of 1 - 3.5 μ . The max. adjacent fiber height difference is 0.2 μ m and for all fibers 0.3 μ m. All system components (modules, trunk cables and patch cords) are co-ordinated for the reaching of the performance particularly. The fan-out unit is optimized for tML[®] - Cable Mounting Bracket for Fan-out Units. The module is marked with sequential serial number and article number.

FO Connectors

The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP[®] plug has a defined fiber height of 1 - 3.5 μ . The max. adjacent fiber height difference is 0.2 μ m and for all fibers 0.3 μ m.

Connector

Type	MPO/MTP [®] Male Push Pull Locking with Elite Pins
Ferrule	12 Fiber MM Elite [®] ferrule, PPS
Boot colour	Black
Manufacturer	tde/US Conec

Optical Performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
50/125 μ OM5	MPO/MTP [®]	850 nm	≤ 0.11 dB	0.25 dB	35 dB

FO Fan-Out

Length Fan-Out	40 mm
Max. \varnothing Fan-Out	10 mm
Parallel connectors	2

FO Cables

Loose tube

Loose tube	unfilled (FRNC)
Wall thickness PVC-tube	0.35 mm – 0.40 mm
Outer diameter	2.6 mm with 24 optical fibres
Tube colour	green
Colour code fibres (1-12)	red, green, blue, yellow, white, grey, brown, violet, turquoise, black, orange, pink
Colour code fibres (13-24)	red, green, blue, yellow, white, grey, brown, violet, turquoise, transparent, orange, pink (always with black ring marking, except transparent)

tML[®] Xtended - FO Micro Distribution trunk cable both sides 2xMPO/MTP[®] w. Pins 24G50/125 μ OM5
LSHF, Type B, Length: xx in m

Strain relief elements

Strain relief elements	Aramid
Strength members	Fiberglass-reinforced plastic (FRP)

Outer jacket

Outer jacket	Halogen-free and flame-retardant material (FRNC)
Wall thickness	approx. 0.4 mm
Outer diameter	approx. 3.8 mm
Colour	lime green
Inkjet - marking (black)	t d e – IVH24G50–MPO-OM5 LSZH (F.RoHS)

Mechanical characteristics

Min. bending radius fixed (static) acc. IEC 60794-1-2 E11A	10 x outside diameter
Min. bending radius during assembly (dynamic), with additional tensile strain acc. IEC 60794-1-2 E6	15 x outside diameter
Max. tensile force acc. IEC 60794-1-2 E1, short term	300 N
Max. crush resistance acc. IEC 60794-1-2 E3, long term	150 N/dm
Max. crush resistance acc. IEC 60794-1-2 E3, short term	1500 N/dm
Cable weight	20.0 kg/km

Thermal characteristics

Transport and storage	-40°C to +80°C
Verlegung	-20°C to +50°C
In use acc. IEC 60794-1-2 F1	-40°C to +80°C

Fire performance

Cable is flame-retardant	acc. to IEC 60332-1-2
Smoke density	acc. to IEC 61034
Halogen-free	acc. to IEC 60754-1
Acidity of the combustion gases	acc. to IEC 60754-2
Fire load	0.26 MJ/m

Chemical characteristics	No resistance to oil, petrol, acid and leach
Standardisation	IEC 60794-2

tML[®] Xtended - FO Micro Distribution trunk cable both sides 2xMPO/MTP[®] w. Pins 24G50/125 μ OM5
LSHF, Type B, Length: xx in m

FO Fiber

Type	Corning ClearCurve [®] 50/125 μ OM5 multimode fiber
Design	Optical fibre G50/125 μ m (conform to IEC 60793-2-10 type A1a.4b) with optical core 50 μ m +/- 2.5 μ m diameter and optical cladding 125 μ m +/- 1 μ m diameter

Geometrical properties

Core concentricity error	< 5 %
Coating concentricity error	< 1 %
Core coating eccentricity	< 1.5 μ m
Eccentricity of coating	< 12 μ m
Screen test	\geq 0.7 GPa (100 kpsi)

Transmission characteristics

Attenuation, maximum values 850 nm (cabled fibre)	2.5 dB/km
Attenuation, maximum values 953 nm (cabled fibre)	1.8 dB/km
Attenuation, maximum values 1300 nm (cabled fibre)	0.7 dB/km
Attenuation, maximum values 850 nm (uncabled fibre)	2.34 dB/km
Attenuation, maximum values 953 nm (uncabled fibre)	1.7 dB/km
Attenuation, maximum values 1300 nm (uncabled fibre)	0.64 dB/km
Macrobending, induced attenuation 100 turns, 37.5 mm	\leq 0.5 dB (at 850 nm)
Macrobending, induced attenuation 100 turns, 37.5 mm	\leq 0.5 dB (at 1300 nm)
Macrobending, induced attenuation 2 turns, 15 mm	\leq 0.1 dB (at 850 nm)
Macrobending, induced attenuation 2 turns, 15 mm	\leq 0.3 dB (at 1300 nm)
Macrobending, induced attenuation 2 turns, 7.5 mm	\leq 0.3 dB (at 850 nm)
Macrobending, induced attenuation 2 turns, 7.5 mm	\leq 0.5 dB (at 1300 nm)
Bandwidth (OFL), minimum values 850 nm	3500 MHz x km
Bandwidth (OFL), minimum values 953 nm	1850 MHz x km
Bandwidth (OFL), minimum values 1300 nm	500 MHz x km
Effective modal Bandwidth-length product min. 850 nm	4700 MHz x km

tML[®] Xtended - FO Micro Distribution trunk cable both sides 2xMPO/MTP[®] w. Pins 24G50/125 μ OM5
LSHF, Type B, Length: xx in m

Effective modal Bandwidth-length product min. 953 nm	2470 MHz x km
Numerical aperture	0.200 +/- 0.015
Effective group of refraction 850 nm	1.482
Effective group of refraction 1300 nm	1.477

Product variants & accessories

Art.-No.	Description
TML-MPP/MPP09I24E-Bxx	tML [®] Xtended - FO Micro Distribution trunk cable both sides 2xMPO/MTP [®] with Pins 24E9/125 μ OS2 LSHF, Type B, Length: xx in m
TML-MPP/MPP50I24G4Bxx	tML [®] Xtended - FO Micro Distribution trunk cable both sides 2xMPO/MTP [®] w. Pins 24G50/125 μ OM4 LSHF, Type B, Length: xx in m
TML-MPP/MPP50I24G5Bxx	tML [®] Xtended - FO Micro Distribution trunk cable both sides 2xMPO/MTP [®] w. Pins 24G50/125 μ OM5 LSHF, Type B, Length: xx in m