

1000Base-BX 1550nm TX/1310nm RX single fiber single mode (LC) with DMI [10 km/6.2 mi.] Link

Budget: 11.0 dB; UL Listed



Lantronix / Transition Networks

Applications include: Gigabit Ethernet Switches and Routers, Fiber Channel Switch Infrastructure, xDSL Applications, and Metro Edge Switching.

Features

- Hot-Pluggable SFP Footprint Optical Transceiver
- Digital Diagnostic Function
- Compliant with SFP Multi-Sourcing Agreement (MSA)



tde[®] trans data elektronik GmbH

Hausanschrift:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Vertriebsbüro:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

1000Base-BX 1550nm TX/1310nm RX single fiber single mode (LC) with DMI [10 km/6.2 mi.] Link

Budget: 11.0 dB; UL Listed

Technische Daten

Standards

- IEEE 802.3

Dimensions

- Width: 0.52" [13 mm]
- Depth: 2.18" [55 mm]
- Height: 0.33" [8 mm]

Power Consumption

- 0.66 Watts

Power Input

- 3.3V

Environment

- Operating: 0°C to 70°C
- Operating: -40°C to 85°C (TN-SFP-LXBxxT)

Certifications

- IEC-60825, FDA 21, CFR 1040.10 and 1040.11; UL Listed (specific SKUs only)

Warranty

- Lifetime

Artikelvarianten & Zubehör

Art.-Nr.	Beschreibung
TN-SFP-LXB12	1000Base-BX 1550nm TX/1310nm RX single fiber single mode (LC) with DMI [10 km/6.2 mi.] Link Budget: 11.0 dB; UL Listed