

1000Base-SX 1310nm TX/1550nm RX multimode (LC) with DMI [500 m/1640 ft.] Link Budget: 7.0 dB

## Direct Attach Cables / Active Optical Cables

A simple to install, cost-effective and interoperable solution

Often used for data center short-reach interconnects, Direct Attach, Active Copper and Active Optical Cables are an indispensable part of any network.

Terminated with transceiver-style connectors, they are designed to be used in the same ports as a typical SFP+ or QSFP transceiver, with no need for adapters or converters. Our DAC and AOC cables offer compatibility with a huge range of vendors, enabling the connectivity you need within the Top of Rack and End of Row environments.

- 10G, 25G, 40G & 100G product solutions
- Seamless interoperability with network equipment
- Multi-code options enabling different OEM vendors at each end of the cable
- 4x breakout cables, 40G QSFP+ to 4x 10G SFP and 100G QSFP28 to 4x 25G SFP28
- Fast Delivery, Custom solutions
- Compatible with Over 90 Systems
- Savings of up to 70%

Applications include: Gigabit Ethernet Switches and Routers, Fiber Channel Switch Infrastructure, xDSL Applications, and Metro Edge Switching.

### Features

- Hot-Pluggable SFP Footprint Optical Transceiver
- Digital Diagnostic Function
- Compliant with SFP Multi-Sourcing Agreement (MSA)



**tde<sup>®</sup>** trans data elektronik GmbH

**Headquarter address:**

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

**Sales office address:**

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 8805 61 13  
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

1000Base-SX 1310nm TX/1550nm RX multimode (LC) with DMI [500 m/1640 ft.] Link Budget: 7.0 dB

## Technical Data

### Standards

- IEEE 802.3

### Dimensions

- Width: 0.52" [13 mm]
- Depth: 2.18" [55 mm]
- Height: 0.33" [8 mm]

### Power Consumption

- 0.66 Watts

### Power Input

- 3.3V

### Environment

- Operating: 0°C to 70°C

### Certifications

- IEC-60825, FDA 21, CFR 1040.10 and 1040.11

### Warranty

- Lifetime

## Product variants & accessories

Art.-No.	Description
TN-SFP-SXB1	1000Base-SX 1310nm TX/1550nm RX multimode (LC) with DMI [500 m/1640 ft.] Link Budget: 7.0 dB