

Managed Hardened PoE+ Switch, (4) GE PoE+, (2) GE with (4) 100/1000Base-X SFP



(4) 10/100/1000Base-T PoE+ with (2) 10/100/1000Base-T RJ-45 + (2) 100/1000Base-X SFP ports

## Description

The SISPM1040-362-LRT is a full managed PoE+ switch suitable for connecting and powering devices in hardened environments. The switch can supply up to 30 Watts per port on all four PoE ports simultaneously. The switch also includes the embedded Device Management System (DMS) software that provides the advanced tools necessary for total management of all IP addressable devices. The unique DMS provides security integrators with lower overall cost, less downtime and easier management of the entire PoE+ network.

Transition Networks' hardened switches are certified to operate reliably in harsh environments such as those found on factory floors, outdoor enclosures or other challenging environments.

## Features

- Store-and-Forward Architecture with 16 Gbps Switching Bandwidth
- Supports Jumbo frames up to 9.6K Bytes
- Ring Protections



**tde® trans data elektronik GmbH**

### Hausanschrift:

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

### Vertriebsbüro:

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 914 36 99  
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

## Managed Hardened PoE+ Switch, (4) GE PoE+, (2) GE with (4) 100/1000Base-X SFP

- Industry standard G.8032 Ethernet Ring Protection Switching (ERPS)
- Support G.8031 Ethernet Linear Protection Switching (EPS)
- Rapid Ring with recovery time less than 20ms
  
- Radius, TACACS+, User Authentication
- Supports LLDP Protocol
- HTTPS/SSH v1/v2 Network Security
- Temperature Detection and Alarm
- Support HW Watchdog to resume operation from CPU hang up
- IEEE 1588 v2 PTP
- Port Mirroring
- Power-over-Ethernet
  
- Port Configuration
- Auto Power Reset (APR)
- DHCP per Port
- PoE Scheduling
- Complies to IEEE 802.3at, IEEE802.3af
- 120 Watts PoE budget
- 30 Watts output on all 4 PoE+ ports
  
- IEEE 802.3ad LACP, up to 6 groups and up to 4 ports per group
- Up to 4K VLAN groups, Port based, 802.1Q tag, Q-in-Q, MAC based VLAN, Management VLAN, Private VLAN Edge, Voice VLAN, GVRP
- ACL – up to 256 entries, Drop or Rate limiting based on: Source and Destinations MAC, VLAN ID and IP address, protocol, port, DSCP/ IP precedence, TCP/UDP source and destination ports, 802.1p priority, Ethernet type, ICMP packets and TCP flag
- Loop Protection
- Quality of Service
  
- Supports 8 hardware queues
- Scheduling: strict priority and WRR, Queue assignment based on DSCP and class of service
- Classification: Port based, 802.1p VLAN priority based, IPV4/IPV6 precedence / DSCP based, DiffServ, Classification and re-marking ACLs
- Rate limiting: Ingress policer, Egress shaping and rate control, per port

## Managed Hardened PoE+ Switch, (4) GE PoE+, (2) GE with (4) 100/1000Base-X SFP

- IPv4/IPv6 dual stacks and static routing
- Port Security, IP Source Guard
- System Alarms via SYSLOG / SNMP Trap
- DHCP Client/Server, DHCP relay, Option 82
- Port based network access control (802.1x)
- Web / SNMP v1,v2c,v3 / Telnet / CLI management
- Device Management System (DMS)
  - Graphical Monitoring – Topology View, Floor view, Map view
  - Find my Switch
  - Traffic Monitoring
  - Trouble shooting – Network diagnostic, protection mechanism, performance and Link Management

Show product on manufacturers website: <https://www.transition.com/products/switch/sispm1040-362-lrt/>

## Technische Daten

## Specifications

## Artikelvarianten & Zubehör

Art.-Nr.	Beschreibung
SISPM1040-362-LRT	Managed Hardened PoE+ Switch, (4) GE PoE+, (2) GE with (4) 100/1000Base-X SFP