

LAN SWITCH, Managed Hardened PoE+ Switch, (8) 10/100/1000Base-T PoE+, (4) 100/1000Base-X SFP



(8) 10/100/1000Base-T PoE+ [100 m/328 ft.] with (4) 100/1000Base-X SFP ports

Description

The SISPM1040-384-LRT-C is a full managed PoE+ switch suitable for connecting and powering devices in hardened environments. The switch can supply up to 30 Watts per port on all eight ports simultaneously. The switch also includes the embedded Device Management System (DMS) software that provides the advanced tools necessary for total management of all IP addressable devices. The unique DMS provides security integrators with lower overall cost, less downtime and easier management of the entire PoE+ network.

Transition Networks's hardened switches are certified to operate reliably in harsh environments such as those found on factory floors, outdoor enclosures or other challenging environments.

Features

- Store-and-Forward Architecture with 24 Gbps Switching Bandwidth
- Supports Jumbo frames up to 9.6K Bytes
- Ring Protections



tde® trans data elektronik GmbH

Hausanschrift:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Vertriebsbüro:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 914 36 99
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

LAN SWITCH, Managed Hardened PoE+ Switch, (8) 10/100/1000Base-T PoE+, (4) 100/1000Base-X SFP

- Industry standard G.8032 Ethernet Ring Protection Switching (ERPS)
- Support G.8031 Ethernet Linear Protection Switching (EPS)
- Rapid Ring with recovery time less than 20ms

- Radius, TACACS+, User Authentication
- Supports LLDP Protocol
- HTTPS/SSH v1/v2 Network Security
- Temperature Detection and Alarm
- Support HW Watchdog to resume operation from CPU hang up
- IEEE 1588 v2 PTP
- Port Mirroring
- Power-over-Ethernet

- Port Configuration
- Auto Power Reset (APR)
- DHCP per Port
- PoE Scheduling
- Complies to IEEE 802.3at, IEEE802.3af
- 240Watts PoE budget
- 30Watts output on all 8 ports

- IEEE 802.3ad LACP, up to 6 groups and up to 4 ports per group
- Up to 4K VLAN groups, Port based, 802.1Q tag, Q-in-Q, MAC based VLAN, Management VLAN, Private VLAN Edge, Voice VLAN, GVRP
- ACL – up to 256 entries, Drop or Rate limiting based on: Source and Destinations MAC, VLAN ID and IP address, protocol, port, DSCP/ IP precedence, TCP/UDP source and destination ports, 802.1p priority, Ethernet type, ICMP packets and TCP flag
- Loop Protection
- Quality of Service

- Supports 8 hardware queues
- Scheduling: strict priority and WRR, Queue assignment based on DSCP and class of service
- Classification: Port based, 802.1p VLAN priority based, IPV4/IPV6 precedence / DSCP based, DiffServ, Classification and re-marking ACLs
- Rate limiting: Ingress policer, Egress shaping and rate control, per port

LAN SWITCH, Managed Hardened PoE+ Switch, (8) 10/100/1000Base-T PoE+, (4) 100/1000Base-X SFP

- IPv4/IPv6 dual stacks and static routing
- Port Security, IP Source Guard
- System Alarms via SYSLOG / SNMP Trap
- DHCP Client/Server, DHCP relay, Option 82
- Port based network access control (802.1x)
- Web / SNMP v1,v2c,v3 / Telnet / CLI management
- Device Management System (DMS)
 - Graphical Monitoring – Topology View, Floor view, Map view
 - Find my Switch
 - Traffic Monitoring
 - Trouble shooting – Network diagnostic, protection mechanism, performance and Link Management

Show product on manufacturers website: <https://www.transition.com/products/switch/sispm1040-384-lrt-c/>

Technische Daten

Specifications

Artikelvarianten & Zubehör

| Art.-Nr. | Beschreibung |
|---------------------|----------------------------------------------------------------------------------------------|
| SISPM1040-384-LRT-C | LAN SWITCH, Managed Hardened PoE+ Switch, (8) 10/100/1000Base-T PoE+, (4) 100/1000Base-X SFP |