

(8) 10/100/1000Base-T PoE+ ports [100 m/328 ft.] + (4) 100/1000Base-X SFP slots (Din Rail Bracket included)



The SISPM1040-384-LRT-C is a managed PoE+ switch suitable for connecting and powering devices in hardened environments. The switch can supply up to 30 Watts per port on all (8) ports simultaneously. The switch also includes the embedded Device Management System software that provides the advanced tools necessary for total management of all IP addressable devices. The unique DMS provides security integrators with lower overall cost, less downtime and easier management of the entire PoE+ network.

Lantronix' hardened switches are certified to operate reliably in harsh environments such as those found on factory floors, outdoor enclosures or other challenging environments.

Features

- Store-and-Forward Architecture with 24 Gbps Switching Bandwidth
- Supports Jumbo frames up to 9.6K Bytes
- Ring Protections
- Industry standard G.8032 Ethernet Ring Protection Switching (ERPS)
- Support G.8031 Ethernet Linear Protection Switching (EPS)
- Rapid Ring with recovery time less than 20ms



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 914 36 99
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

(8) 10/100/1000Base-T PoE+ ports [100 m/328 ft.] + (4) 100/1000Base-X SFP slots (Din Rail Bracket included)

- Supports LLDP Protocol
- Temperature Detection and Alarm
- Support HW Watchdog to resume operation from CPU hang up
- IEEE 1588 v2 PTP
- Port Mirroring
- Power-over-Ethernet

- Port Configuration
- Auto Power Reset (APR)
- DHCP per Port
- Always on PoE
- PoE Scheduling
- Complies to IEEE 802.3at, IEEE 802.3af

- IEEE 802.3ad LACP, up to 6 groups and up to 4 ports per group
- Up to 4K VLAN groups, Port based, IEEE 802.1Q tag, Q-in-Q, MAC based VLAN, Management VLAN, Private VLAN Edge, Voice VLAN, GVRP
- ACL – up to 256 entries, Drop or Rate limiting based on: Source and Destinations MAC, VLAN ID and IP address, protocol, port, DSCP/ IP precedence, TCP/UDP source and destination ports, IEEE 802.1p priority, Ethernet type, ICMP packets and TCP flag
- Loop Protection
- Quality of Service

- Supports 8 hardware queues
- Scheduling: strict priority and WRR, Queue assignment based on DSCP and class of service
- Classification: Port based, IEEE 802.1p VLAN priority based, IPV4/ IPV6 precedence / DSCP based, DiffServ, Classification and re-marking
- Rate limiting: Ingress policer, Egress shaping and rate control, per port

- IPv4/IPv6 dual stacks and static routing
- Port Security, IP Source Guard
- System Alarms via SYSLOG / SNMP Trap
- DHCP Client/Server, DHCP relay, Option 82
- Port based network access control (IEEE 802.1X)
- Web / SNMP v1,v2c,v3 / Telnet / CLI management
- Media Redundancy Protocol (MRP)

(8) 10/100/1000Base-T PoE+ ports [100 m/328 ft.] + (4) 100/1000Base-X SFP slots (Din Rail Bracket included)

Device Management System (DMS)

- Graphical Monitoring – Topology view, Floor view, Map view
- Traffic Monitoring
- Troubleshooting – Network diagnostic, protection mechanism, performance and link management

Technical Data

Standards

- IEEE 802.3
- IEEE 802.3u
- IEEE 802.3z
- IEEE 802.3ab
- IEEE 802.3x
- IEEE 802.3ad
- IEEE 802.1p
- IEEE 802.1Q
- IEEE 802.1w
- IEEE 802.1s
- IEEE 802.1X
- IEEE 802.1AB
- IEEE 802.1ad
- IEEE 802.3af
- IEEE 802.3at
- IEEE 802.3ah
- IEEE 802.1ag
- IEEE 802.1D
- IEEE 1588 v2
- ITU-T Y.1731
- ITU-T G.8031
- ITU-T G.8032
- IEC62439-2

(8) 10/100/1000Base-T PoE+ ports [100 m/328 ft.] + (4) 100/1000Base-X SFP slots (Din Rail Bracket included)

MAC Address

- 8K

Backplane

- 24Gbps

Serial Console

- RJ-45

Status LEDs

- System, Power1, Ring Master, Coupling, Power2, Alarm, Port Status

Dimensions

- Width: 2.4" [62 mm]
- Depth: 5.3" [135 mm]
- Height: 5.4" [130 mm]

DIP Switch (2-pin)

- Rapid Ring setting

Reset button

- Reset the switch, Restore Factory default

Digital output (relay)

- 24VDC/1A

Digital input

- Level 0 (Low): 0V to 6V
- Level 1 (High): 10V to 24V

(8) 10/100/1000Base-T PoE+ ports [100 m/328 ft.] + (4) 100/1000Base-X SFP slots (Din Rail Bracket included)

Power Input

- 44 – 57VDC (>52V for 802.3at PoE+ recommended, >48V for IEEE 802.3af PoE recommended); Dual inputs Terminal Block

Power Consumption Without PoE

- 11.1 Watts

Power-over-Ethernet

- 240 Watts PoE Budget
- 30 Watts output on all 8 ports

Ingress Protection

- IP30

Environment

- Operating: -40°C to +75°C
- Storage: -40°C to 85°C
- Humidity: 5% to 95% (non-condensing)
- Altitude: 0 – 10,000 ft.

Weight

- 2.2 lbs. [1 kg]

MTBF

- 92,110 hours

Certifications

- EMI: CE, FCC Part 15, EN61000-4-2, EN61000-4-3, EN-61000-4-4, EN61000- 4-5, EN61000-4-6, EN61000-4-8, IEC60068-2-32 (Free fall), IEC60068-2-27 (Shock), IEC60068-2-6 (Vibration), NEMA TS-2
- Safety: IEC62368-1/EN62368-1, UL Class 1/Div 2

Compliant*

(8) 10/100/1000Base-T PoE+ ports [100 m/328 ft.] + (4) 100/1000Base-X SFP slots (Din Rail Bracket included)

(Designed to Meet) *Please contact sales with certification needs

- EN50155, EN50121-4, DNV, IEC61850-3, IEEE1613

Warranty

- 5 Years

Product variants & accessories

Art.-No.	Description
SISPM1040-384-LRT-C	(8) 10/100/1000Base-T PoE+ ports [100 m/328 ft.] + (4) 100/1000Base-X SFP slots (Din Rail Bracket included)