

tML<sup>®</sup> - partial front plate with 6x MPO/MTP<sup>®</sup> Type B (Key Up/Up) for the Rack Mount Enclosure 1U extendable



## tML<sup>®</sup> Xtended

tML<sup>®</sup> Xtended is a patented, modular cabling system consisting of the three key components module, trunk cable and rack mount enclosure. The system components are 100 percent manufactured, pre-assembled and tested in Germany. They enable plug-and-play installation on site – especially in data centres, but also in industrial environments – within the shortest possible time. Heart of the system are the rear MPO/MTP<sup>®</sup> 12 fiber and Telco connectors, which can be used to connect at least six or twelve ports at a time. Depending on the module configuration, transfer rates of up to 200G are currently possible with SR4. The fibre optic and TP modules can be used together in a module carrier with a very high port density. The tde offers its tML<sup>®</sup> cabling system as a proven tML<sup>®</sup> standard system and in the highly innovative variants tML<sup>®</sup> 24 system and now tML<sup>®</sup> 32 system for extreme scalability and very easy migration to higher transmission rates such as 40G, 100G, 200G and 400G.

The tML<sup>®</sup> - FO partial front panel is intended for the installation in the tML<sup>®</sup> Rack Mount Enclosure 1U extendable (for 8 x Modules). The tML<sup>®</sup> HD partial front panel can be used only in combination with the tML<sup>®</sup> HD patch cord.



**tde<sup>®</sup> trans data elektronik GmbH**

**Headquarter address:**

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

**Sales office address:**

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 914 36 99  
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

tML<sup>®</sup> - partial front plate with 6x MPO/MTP<sup>®</sup> Type B (Key Up/Up) for the Rack Mount Enclosure 1U extendable

## Technical Data

Pre-mounted	6 x MPO/MTP <sup>®</sup> Adapter (grey)
	QS-Managementsystem ISO 9001, ISO 14001 and TL 9000

## tML<sup>®</sup> - partial front panels

Front Panel	Stainless steel
Dimensions	108 x 20 mm

## FO Adapters

Type	MPO/MTP <sup>®</sup>
Application	Multimode OM1/OM2
Design	without Flange
Connector style	SC Simplex
Key Orientation	Type B, Key up/up
Color	Grey
Material	Plastic
Sleeve	--
Shutter	--
Standards	IEC 61754-7 TIA 604-5
Manufacturer	US Conec

## Product variants & accessories

Art.-No.	Description
TML-M06MP-GN-A8	tML <sup>®</sup> - partial front plate with 6x MPO/MTP <sup>®</sup> Type A (Key Up/Down) OS2 green for the Rack Mount Enclosure 1U extendable
TML-M06MP-GR-A8	tML <sup>®</sup> - partial front plate with 6x MPO/MTP <sup>®</sup> Type B (Key Up/Up) for the Rack Mount Enclosure 1U extendable
TML-M06MP-LG-A8	tML <sup>®</sup> - partial front plate with 6x MPO/MTP <sup>®</sup> Type A (Key Up/Down) OM5 limegreen for the Rack Mount Enclosure 1U extendable
TML-M06MP-TK-A8	tML <sup>®</sup> - partial front plate with 6x MPO/MTP <sup>®</sup> Type A (Key Up/Down) OM3 aqua for the Rack Mount Enclosure 1U extendable
TML-M06MP-VI-A8	tML <sup>®</sup> - partial front plate with 6x MPO/MTP <sup>®</sup> Type A (Key Up/Down) OM4 magenta for the Rack Mount Enclosure 1U extendable