

HD - FO Patch cord switchable LC HD / LC HD Duplex Mini 50/125 μ , FRNC, OM4, Crossover, Length:
xxxxx in cm



tde - Fiber Optic Assemblies

The tde patch and trunk cables are manufactured completely at the German facility in Ohrte. Production processes at tde meet the latest standards, and the company has one of the most up-to-date fiber optic assembly houses in Europe. Fiber optic patch cables and trunk cables are manufactured in many different configurations using highly automated processes on two independent mass production lines. The range of products on offer encompasses the entire spectrum of connector types available on the market. Production capacity is around 100,000 fiber optic connectors per month, and this can be ramped up easily whenever required. To guarantee consistently top quality, only the best components from renowned vendors are used. All tde production staff have the necessary qualifications and education, and have been well trained in using specialist technical equipment such as laser cleavers and glue-dispensing robots.

Each cable application is subjected to a full test procedure comprising interferometer measurements, insertion loss and return loss measurements and a final visual inspection to ensure that only 100% error-free products are shipped to the customer.

Products made by tde perform at least internationally accepted quality standards and norms. The quality management system is ISO 9001, ISO 14001 and TL9000 certified.



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

HD - FO Patch cord switchable LC HD / LC HD Duplex Mini 50/125 μ , FRNC, OM4, Crossover, Length:
xxxxx in cm

Technical Data

FO Connectors

Connector type	LC HD Duplex Uniboot
Housing	Plastic, integrated locking of unlocking aid
Polarity	Tool-less
Ferrule	Zirkonia Straight Split, Spring-loaded Axially
Ferrule hole	126 μ m
Mating cycles	1000
Operating temperature	-40°C to 75°C
Strain relief to	100 N
Manufacturer	tde
Simplex/Duplex clip	Uniboot Duplex Housing

Optical performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
50/125 μ OM4	LC Uniboot HD	850 nm	< 0.25 dB	0.45 dB	30 dB

FO Cables

Flame resistance	IEC 60332-3
	IEC 60754
	IEC 61034-1
	IEC 61034-2

Cable construction

Type	DVH02G50-OM4-2.0
Tight buffer	2x 600 μ coated fibers (free movable in the compound)
Fiber type	MM-OM4, 50/125 μ , Corning ClearCurve OM4
Strength members	Aramid yarn (free movable in the compound)
Outer jacket	LSZH (Halogen free, low smoke, flame retardant thermoplastic compound)
Jacket color	Magenta, RAL 4003
Identification	"t d e – DVH02G50-OM4-2.0mm LSZH" and sequential meter marking + Lot number

Physical properties

Outer diameter cable	2.0 \pm 0.1 mm
Maximum tensile load, short term	500 N
Maximum tensile load, long term	300 N
Min. Bending radius, unloaded	20 mm

HD - FO Patch cord switchable LC HD / LC HD Duplex Mini 50/125μ, FRNC, OM4, Crossover, Length:
xxxxx in cm

Min. Bending radius, loaded	40 mm
Temperature range (operation)	-5°C to +60°C

FO Fiber

Type	Corning ClearCurve [®] 50/125μ OM4 multimode fiber
Optimized Data Rate over Distance	40/100 Gb over 170 m* 10 Gb/s over 550 m 1 Gb/s over 1100 m
Standard Compliance	ISO/IEC 11801: type OM4 fiber** IEC 60793-2-10: type A1a.3 fiber** TIA/EIA: 492AAAD ITU: ITU G651.1
*	Distances specified in the 40G/100G per IEEE 802.3ba standard are 150m on OM4 and 100m on OM3; Corning fibers are manufactured to tighter dispersion specifications and thereby support the extended distances shown in the table (assuming cable attenuation ≤3.0 dB/km and same 1.0 dB of connector loss for OM3 that the standard requires for OM4)
**	Assumes IEC draft standard is harmonized with 492AAAD which was approved by TIA

Optical Specifications

Bandwidth	High Performance EMB* (MHz.km): 4700 at 850 nm only Legacy Performance EMB** (MHz.km): 3500 at 850 nm / 500 at 1300 nm
Attenuation	At 850 nm max. ≤ 2.3 dB/km At 1300 nm max. ≤ 0.6 dB/km
Macrobend Loss	Mandrel Radius (mm): 37.2 / 15 / 7.5 Number of Turns: 100 / 2 / 2 Induced Attenuation (dB) at 850 nm: ≤ 0.05 / ≤ 0.1 / 0.2 Induced Attenuation (dB) at 1300 nm: ≤ 0.15 / ≤ 0.3 / ≤ 0.5
Numerical Aperture	0.200 ± 0.015
*	Ensured via miniEMBc, per TIA/EIA 455-220A and IEC 60793-1-49, for high performance laser-based systems (up to 10Gb/s)
**	OFL BW, per TIA/EIA 455-204 and IEC 60793-1-41, for legacy and LED-based systems (typically up to 100 Mb/s)

Dimensional Specifications

Core Diameter	50.0 ± 2.5 μm
Cladding Diameter	125.0 ± 1.0 μm
Core-Clad Concentricity	≤ 1.5 μm
Cladding Non-Circularity	≤ 1.0%
Core Non-Circularity	≤ 5.0%
Coating Diameter	242 ± 5 μm
Coating-Cladding Concentricity	< 12 μm

HD - FO Patch cord switchable LC HD / LC HD Duplex Mini 50/125 μ , FRNC, OM4, Crossover, Length: xxxxx in cm

Environmental

Environmental Test	Test Condition	Induced Attenuation 850 nm & 1300 nm (dB/km)
Temperature Dependence	-60°C to +85°C	≤ 0.10
Temperature Humidity Cycling	-10°C to +85°C and 4% to 98% RH	≤ 0.10
Water Immersion	23°C \pm 2°C	≤ 0.20
Heat Aging	85°C \pm 2°C	≤ 0.20
Damp Heat	85°C at 85% RH	≤ 0.20
Operating Temperature Range	-60°C to +85°C	

Mechanical Specifications

Proof Test	The entire fiber length is subjected to a tensile stress ≥ 100 kpsi (0.7 GN/m ²).
Length	Fiber lengths available up to 17.6 km/spool.

Performance Characterizations

Refractive Index Difference	1%
Effective Group Index of Refraction	850 nm: 1.480 1300 nm: 1.479
Fatigue Resistance Parameter (nd)	20
Coating Strip Force	Dry: 0.6 lbs (2.7N) Wet: 14 days in 23°C water soak: 0.6 lbs (2.7N)
Chromatic Dispersion	Zero Dispersion Wavelength (λ_0): 1295 nm $\leq \lambda_0 \leq$ 1315 nm Zero Dispersion Slope (S_0): ≤ 0.101 ps/(nm ² *km)

Product variants & accessories

Art.-No.	Description
L-HLCA/HLCA9DRMxxxxx	HD - FO Patch cord switchable LC APC HD / LC APC HD Duplex Mini 9/125 μ , FRNC, OS2, Crossover, Length: xxxxx in cm
L-HLC/HLC09DRMxxxxx	HD - FO Patch cord switchable LC HD / LC HD Duplex Mini 9/125 μ , FRNC, OS2, Crossover, Length: xxxxx in cm
L-HLC/HLC50D4RMxxxxx	HD - FO Patch cord switchable LC HD / LC HD Duplex Mini 50/125 μ , FRNC, OM4, Crossover, Length: xxxxx in cm
L-HLC/HLC50D5RMxxxxx	HD - FO Patch cord switchable LC HD/ LC HD Duplex Mini 50/125 μ , FRNC, OM5, Crossover, Length: xxxxx in cm