

TN-XFP-LRM - MSA Compatible XFP Modules: 10GBase XFP Duplex LC, 10GBase-LRM 1310nm (LC) [300m/985 ft.]

10GBase-LRM, XFP with DMI, 1310nm multimode (LC) [300m/985 ft.] Link Budget: 4.5 dB

Product Description

10GBase-LRM, XFP with DMI, 1310nm multimode (LC) [300m/985 ft.] Link Budget: 4.5 dB

Features

- Hot-Pluggable XFP Footprint LC Optical Transceiver
- Digital Diagnostic Function
- Class 1 Laser International Safety Standard IEC-60825 Compliant
- Compatible with XFP Multi-Sourcing Agreement (MSA)
- XFP Optical Transceiver with duplex LC connector
- 10G Small Form-Factor Pluggable (XFP) MSA compatible
- INF-8077i Digital Diagnostic Function (DMI)
- Maximum Link Length of 100 km
- Single +3.3V Power Supply
- Low Power Dissipation < 2 Watts
- RoHS Compliant
- Compliant with IEEE 802.3ae 10GBase-LR/LW//ER/ZR
- Compliant with 10G Fiber Channel 1200-SM-LL-L
- Compliant with XFI 10G Serial Electrical Interface

Show product on manufacturers website: <https://www.transition.com/products/optical-devices/tn-xfp-lrm/>



tde[®] trans data elektronik GmbH

Hausanschrift:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Vertriebsbüro:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 914 36 99
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

TN-XFP-LRM - MSA Compatible XFP Modules: 10GBase XFP Duplex LC, 10GBase-LRM 1310nm
(LC) [300m/985 ft.]

Technische Daten

Specifications

Artikelvarianten & Zubehör

| Art.-Nr. | Beschreibung |
|------------|--|
| TN-XFP-LRM | TN-XFP-LRM - MSA Compatible XFP Modules: 10GBase XFP Duplex LC, 10GBase-LRM 1310nm (LC) [300m/985 ft.] |