


tDF® - FO splice module 3U/7HP, Splice through up to 12 fibers



## tDF® - tde Distribution Frame (ODF)

tDF® is a modular Central Office solution with the highest packing density. At 46U, up to 4032 fibers can be terminated with LC. In developing the tde has taken primarily attention on the user-friendly installation. So the patented modules are fully be fitted from the front. A 19-inch sub rack occupies three height units and is equipped with twelve splice modules. Per sub rack, up to 288 fibers can be terminated with LC. The splices will be stored in standard splice cassettes. A unique feature of the splice module is the built-in loose tube over length management, which compared to conventional solutions saves an additional rack unit for the over length tray. The trunk cables are brought to the sub rack side and splitted there. This results in very short stripping lengths for the trunk cables. Due to the tML® compatibility also MPO/MTP® modules can be equipped in the same sub rack. The modular design of the tDF rack system offers maximum flexibility. The racks can be ordered customized completely preconfigured.



**tde®** trans data elektronik GmbH

### Headquarter address:

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

### Sales office address:

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 8805 61 13  
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

tDF® - FO splice module 3U/7HP, Splice through up to 12 fibers

## Technical Data

Application	Splice through up to 12 fibers
Dimensions	3U/7HP
Pre-mounted	1 x Splice cassette 1 x Splice holder 1 x Splice cover 2 x 5mm Flex tube 12 x crimp splice protection

## Product variants & accessories

Art.-No.	Description
TDF-M-12SPICE	tDF® - FO splice module 3U/7HP, Splice through up to 12 fibers
TDF-M-24SPICE	tDF® - FO splice module 3U/7HP, Splice through up to 24 fibers