

TN-XFP-ZR - MSA Compatible XFP Modules: 10GBase XFP Duplex LC, 10GBase-ZR 1550nm (Duplex LC) [80 km/49.7 mi.]

10GBase-ZR 10G Fiber Channel, XFP with DMI, 1550nm single mode (Duplex LC) [80 km/49.7 mi.] Link Budget: 23.0 dB

Product Description

10GBase-ZR 10G Fiber Channel, XFP with DMI, 1550nm single mode (Duplex LC) [80 km/49.7 mi.] Link Budget: 23.0 dB

Features

- Hot-Pluggable XFP Footprint LC Optical Transceiver
- Digital Diagnostic Function
- Class 1 Laser International Safety Standard IEC-60825 Compliant
- Compatible with XFP Multi-Sourcing Agreement (MSA)
- XFP Optical Transceiver with duplex LC connector
- 10G Small Form-Factor Pluggable (XFP) MSA compatible
- INF-8077i Digital Diagnostic Function (DMI)
- Maximum Link Length of 100 km
- Single +3.3V Power Supply
- Low Power Dissipation < 2 Watts
- RoHS Compliant
- Compliant with IEEE 802.3ae 10GBase-LR/LW//ER/ZR
- Compliant with 10G Fiber Channel 1200-SM-LL-L
- Compliant with XFI 10G Serial Electrical Interface

Show product on manufacturers website: <https://www.transition.com/products/optical-devices/tn-xfp-zr/>



tde[®] trans data elektronik GmbH

Hausanschrift:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Vertriebsbüro:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 914 36 99
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

TN-XFP-ZR - MSA Compatible XFP Modules: 10GBase XFP Duplex LC, 10GBase-ZR 1550nm (Duplex LC) [80 km/49.7 mi.]

Technische Daten

Specifications

Artikelvarianten & Zubehör

Art.-Nr.	Beschreibung
TN-XFP-ZR	TN-XFP-ZR - MSA Compatible XFP Modules: 10GBase XFP Duplex LC, 10GBase-ZR 1550nm (Duplex LC) [80 km/49.7 mi.]