

Industrial DIN Rail Mounted Power Supply: 48VDC, 39.8Watts



Direct Attach Cables / Active Optical Cables

A simple to install, cost-effective and interoperable solution

Often used for data center short-reach interconnects, Direct Attach, Active Copper and Active Optical Cables are an indispensable part of any network.

Terminated with transceiver-style connectors, they are designed to be used in the same ports as a typical SFP+ or QSFP transceiver, with no need for adapters or converters. Our DAC and AOC cables offer compatibility with a huge range of vendors, enabling the connectivity you need within the Top of Rack and End of Row environments.

- 10G, 25G, 40G & 100G product solutions
- Seamless interoperability with network equipment
- Multi-code options enabling different OEM vendors at each end of the cable
- 4x breakout cables, 40G QSFP+ to 4x 10G SFP and 100G QSFP28 to 4x 25G SFP28
- Fast Delivery, Custom solutions
- Compatible with Over 90 Systems
- Savings of up to 70%



tde® trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

Industrial DIN Rail Mounted Power Supply: 48VDC, 39.8Watts

Industrial DIN Rail Mounted Power Supply

48VDC, 39.8Watts

Features

- Variable AC input range
- Protected against:
 - Overload
 - Over Voltage
- Convection air cooling
- DIN rail mountable
- UL 508 approved
- Full load burn in test
- RoHS Compliant

Technical Data

Power Output

- Output Voltage 48VDC
- Current Rating: 0.83A
- Power Rating: 39.8 Watts
- Ripple & Noise Max 120mVp-p
- Voltage Range: 48~56VDC
- Voltage Tolerance $\pm 1.0\%$
- Line Regulation: $\pm 1.0\%$
- Load Regulation $\pm 1.0\%$
- Setup, Rise Time 300ms, 30ms
- Hold Up Time: 20ms/115VAC

Power Input

- Voltage Range Switch Selectable: 88~264VAC, 120~370VDC
- Frequency Range: 47~63Hz
- Efficiency: 88%
- AC Current (Typical): ,

Industrial DIN Rail Mounted Power Supply: 48VDC, 39.8Watts

- Inrush Current (Cold): ,
- Leakage Current: <

Protection

- Overload 105~160%
- Overvoltage: 57.6~64.8V

Dimensions

- Width: 1.57" [40 mm]
- Depth: 3.94" [100 mm]
- Height: 3.54" [90 mm]

Environment

- Operating: -20°C to +70°C
- Storage: -40°C to +85°C
- Humidity: 20% to 90% (non-condensing)

Weight

- 0.66 lbs. [0.3 kg]

MTBF

- 301.7Khrs

Certifications

- Safety: UL508, TUV EN60950-1, NEC Class 2, LPS Compliant, UL60950-1, EN55011, EN55022, CISPR22, EN61204-3 Class B, EN61000-3-2, EN61000-3-3, EN61000-4-2, EN61000-4-3, EN61000-4-4, EN61000-4-5, EN61000-4-6, EN61000-4-8, EN61000-4-11, EN55024, EN61000-6-2, EN50082-2, EN61204-3 A, IEC60068-2-6 (Vibration)

Warranty

- Lifetime

Industrial DIN Rail Mounted Power Supply: 48VDC, 39.8Watts

Product variants & accessories

Art.-No.	Description
25130	Industrial DIN Rail Mounted Power Supply: 48VDC, 39.8Watts