

tML[®] Xtended - FO Dark Fiber Module 5HP 4x MPO/MTP[®] w/o Pins/6x MPO/MTP[®] w. Pins 50/125 μ
OM5, SR4



tML[®] Xtended

tML[®] Xtended is a patented, modular cabling system consisting of the three key components module, trunk cable and rack mount enclosure. The system components are 100 percent manufactured, pre-assembled and tested in Germany. They enable plug-and-play installation on site – especially in data centres, but also in industrial environments – within the shortest possible time. Heart of the system are the rear MPO/MTP[®] 12 fiber and Telco connectors, which can be used to connect at least six or twelve ports at a time. Depending on the module configuration, transfer rates of up to 200G are currently possible with SR4. The fibre optic and TP modules can be used together in a module carrier with a very high port density. The tde offers its tML[®] cabling system as a proven tML[®] standard system and in the highly innovative variants tML[®] 24 system and now tML[®] 32 system for extreme scalability and very easy migration to higher transmission rates such as 40G, 100G, 200G and 400G.



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 914 36 99
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

tML[®] Xtended - FO Dark Fiber Module 5HP 4x MPO/MTP[®] w/o Pins/6x MPO/MTP[®] w. Pins 50/125 μ OM5, SR4

Technical Data

The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP[®] plug has a defined fiber height of 1 - 3.5 μ . The max. adjacent fiber height difference is 0.2 μ m and for all fibers 0.3 μ m. All system components (modules, trunk cables and patch cords) are co-ordinated for the reaching of the performance particularly. The module is marked with sequential serial number and article number. The modules are ROHS compliant.

Entry	2 x MPO/MTP [®] Female Adapter (limegreen) back
Exit	6 x MPO/MTP [®] Male Adapter (limegreen) front
Tests	Interferometer, Insertion Loss, Return Loss and Visual Final Inspection; all measured values are electronically archived
	QS-Managementsystem ISO 9001, ISO 14001 and TL 9000

Box	Galvanized steel sheet
Front Panel	Stainless steel

FO Connectors

The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP[®] plug has a defined fiber height of 1 - 3.5 μ . The max. adjacent fiber height difference is 0.2 μ m and for all fibers 0.3 μ m.

Connector

Type	MPO/MTP [®] Female Push Pull Locking
Ferrule	12 Fiber MM Elite [®] ferrule, PPS
Boot colour	Black
Manufacturer	tde/US Conec

Optical Performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
50/125 μ OM5	MPO/MTP [®]	850 nm	\leq 0.16 dB	0.30 dB	30 dB

FO Connectors

The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP[®] plug has a defined fiber height of 1 - 3.5 μ . The max. adjacent fiber height difference is 0.2 μ m and for all fibers 0.3 μ m.

Connector

Type	MPO/MTP [®] Male Push Pull Locking with Elite Pins
------	---

tML[®] Xtended - FO Dark Fiber Module 5HP 4x MPO/MTP[®] w/o Pins/6x MPO/MTP[®] w. Pins 50/125 μ OM5, SR4

Ferrule	12 Fiber MM Elite [®] ferrule, PPS
Boot colour	Black
Manufacturer	tde/US Conec

Optical Performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
50/125 μ OM5	MPO/MTP [®]	850 nm	\leq 0.16 dB	0.30 dB	30 dB

FO Adapters

Type	MPO/MTP [®]
Application	Multimode OM5
Design	without Flange
Connector style	SC Simplex
Key Orientation	Type A, Key up/down
Color	Limegreen
Material	Plastic
Sleeve	--
Shutter	--
Standards	IEC 61754-7 TIA 604-5
Manufacturer	US Conec

FO Fiber

Type	Corning ClearCurve [®] 50/125 μ OM5 multimode fiber
Design	Optical fibre G50/125 μ m (conform to IEC 60793-2-10 type A1a.4b) with optical core 50 μ m +/- 2.5 μ m diameter and optical cladding 125 μ m +/- 1 μ m diameter

Geometrical properties

Core concentricity error	< 5 %
Coating concentricity error	< 1 %
Core coating eccentricity	< 1.5 μ m
Eccentricity of coating	< 12 μ m
Screen test	\geq 0.7 GPa (100 kpsi)

Transmission characteristics

Attenuation, maximum values 850 nm (cabled fibre)	2.5 dB/km
---	-----------

tML[®] Xtended - FO Dark Fiber Module 5HP 4x MPO/MTP[®] w/o Pins/6x MPO/MTP[®] w. Pins 50/125 μ OM5, SR4

Attenuation, maximum values 953 nm (cabled fibre)	1.8 dB/km
Attenuation, maximum values 1300 nm (cabled fibre)	0.7 dB/km
Attenuation, maximum values 850 nm (uncabled fibre)	2.34 dB/km
Attenuation, maximum values 953 nm (uncabled fibre)	1.7 dB/km
Attenuation, maximum values 1300 nm (uncabled fibre)	0.64 dB/km
Macrobending, induced attenuation 100 turns, 37.5 mm	≤ 0.5 dB (at 850 nm)
Macrobending, induced attenuation 100 turns, 37.5 mm	≤ 0.5 dB (at 1300 nm)
Macrobending, induced attenuation 2 turns, 15 mm	≤ 0.1 dB (at 850 nm)
Macrobending, induced attenuation 2 turns, 15 mm	≤ 0.3 dB (at 1300 nm)
Macrobending, induced attenuation 2 turns, 7.5 mm	≤ 0.3 dB (at 850 nm)
Macrobending, induced attenuation 2 turns, 7.5 mm	≤ 0.5 dB (at 1300 nm)
Bandwidth (OFL), minimum values 850 nm	3500 MHz x km
Bandwidth (OFL), minimum values 953 nm	1850 MHz x km
Bandwidth (OFL), minimum values 1300 nm	500 MHz x km
Effective modal Bandwidth-length product min. 850 nm	4700 MHz x km
Effective modal Bandwidth-length product min. 953 nm	2470 MHz x km
Numerical aperture	0.200 +/- 0.015
Effective group of refraction 850 nm	1.482
Effective group of refraction 1300 nm	1.477

Product variants & accessories

Art.-No.	Description
TML-T06MPP/04MP50G3X	tML [®] Xtended - FO Dark Fiber Module 5HP 4x MPO/MTP [®] w/o Pins/6x MPO/MTP [®] w. Pins 50/125 μ OM3, SR4
TML-T06MPP/04MP50G4X	tML [®] Xtended - FO Dark Fiber Module 5HP 4x MPO/MTP [®] w/o Pins/6x MPO/MTP [®] w. Pins 50/125 μ OM4, SR4
TML-T06MPP/04MP50G5X	tML [®] Xtended - FO Dark Fiber Module 5HP 4x MPO/MTP [®] w/o Pins/6x MPO/MTP [®] w. Pins 50/125 μ OM5, SR4