

10GBase-ER/1000Base-LX, SFP+ with DMI single mode (LC) 1533.47nm 195.50THZ [40 km/24.9 mi.]

Link Budget: 15.0 dB



## Lantronix / Transition Networks

### Features

- SFP+ Optical Transceiver with duplex LC connector
- 1G/10G Small Form-Factor Pluggable (SFP+) MSA compliant
- Compliant with 10GBase-ER/ZR
- Compliant with 1000Base-LX/ZX
- SFF-8472 Digital Diagnostic Function (DMI)
- SFF-8431 and SFF-8432 Compliant
- Maximum Link Length of 80KM
- Single +3.3 V Power Supply
- Lower power dissipation < 1.5 Watts
- RoHS Compliant



**tde<sup>®</sup>** trans data elektronik GmbH

#### Hausanschrift:

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

#### Vertriebsbüro:

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 8805 61 13  
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

10GBase-ER/1000Base-LX, SFP+ with DMI single mode (LC) 1533.47nm 195.50THZ [40 km/24.9 mi.]

Link Budget: 15.0 dB

## Technische Daten

### Standards

- IEEE 802.3
- IEEE 802.3ae
- IEEE 802.3z

### Dimensions

- Width: 0.52" [13 mm]
- Depth: 2.18" [55 mm]
- Height: 0.33" [8 mm]

### Power Input

- 3.3V

### Environment

- Operating: 0°C to 70°C
- Operating: -40°C to 85°C

### Certifications

- IEC 60825-1, FDA CDRH 21-CFR 1040.10 Class 1

### Warranty

- Lifetime

## Artikelvarianten & Zubehör

| Art.-Nr.           | Beschreibung                                                                                                        |
|--------------------|---------------------------------------------------------------------------------------------------------------------|
| TN-10GSFP-LR4M-D55 | 10GBase-ER/1000Base-LX, SFP+ with DMI single mode (LC) 1533.47nm 195.50THZ [40 km/24.9 mi.]<br>Link Budget: 15.0 dB |