

tML[®] Xtended - FO Micro Distribution Trunk Cable both sides 8xMPO/MTP[®] w. Pins 96G50/125 μ OM4
LSHF, Type B, Length: xx in m



tML[®] - tde Modular Link

tML[®] is a patented, modular cabling system consisting of the three key components module, trunk cable and rack mount enclosure. The system components are 100 percent manufactured, pre-assembled and tested in Germany. They enable plug-and-play installation on site – especially in data centres, but also in industrial environments – within the shortest possible time. Heart of the system are the rear MPO/MTP[®] and Telco connectors, which can be used to connect at least six or twelve ports at a time. Depending on the module configuration, transfer rates of up to 200G are currently possible with SR4. The fibre optic and TP modules can be used together in a module carrier with a very high port density. The tde offers its tML[®] cabling system as a proven tML[®] standard system and in the highly innovative variants tML[®] Xtended, tML[®] 24 System and now tML[®] 32 System for extreme scalability and very easy migration to higher transmission rates such as 40G, 100G, 200G and 400G.

The tML[®] Xtended - module will be installed in the link on one side rotated 180 degrees. The associated tML[®] Xtended trunk cable has a type B pin out. The complete link corresponds to EIA / TIA "Method B". The advantage is that before and after migration uniformly configured patch cables and modules are used.



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

tML® Xtended - FO Micro Distribution Trunk Cable both sides 8xMPO/MTP® w. Pins 96G50/125µ OM4
LSHF, Type B, Length: xx in m

Technical Data

The tML®- FO Micro Distribution trunk cable is preterminated with MPO/MTP®connectors on both ends. The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP®plug has a defined fiber height of 1 - 3.5µ. The max. adjacent fiber height difference is 0.2µm and for all fibers 0.3µm. All system components (modules, trunk cables and patch cords) are co-ordinated for the reaching of the performance particularly. The fan-out unit is optimized for tML® - Cable Mounting Bracket for Fan-out Units. The module is marked with sequential serial number and article number.

FO Connectors

The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP® plug has a defined fiber height of 1 - 3.5µ. The max. adjacent fiber height difference is 0.2µm and for all fibers 0.3µm.

Connector

Type	MPO/MTP® Male Push Pull Locking with Elite Pins (magenta)
Ferrule	12 Fiber MM Elite® ferrule, PPS
Boot colour	Black
Manufacturer	tde/US Conec

Optical Performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
50/125µ OM4	MPO/MTP®	850 /1300 nm	≤ 0.12 dB	0.25 dB	35 dB

FO Fan-Out

Length Fan-Out	50 mm
Max. Ø Fan-Out	20 mm
Parallel connectors	8

FO Cables

Standards	Environmental and mechanical tests according to EN 187000 and IEC 60794-1-2.
Flame retardant	IEC 60332-3
Halogen free	IEC 60754-1
Low smoke emission	IEC 61034-1/2
Reaction to fire (Euroclasses)	D _{ca}

Type	Micro Distribution Indoor Cable
Fibers	96 (8 x 12)

tML® Xtended - FO Micro Distribution Trunk Cable both sides 8xMPO/MTP® w. Pins 96G50/125µ OM4
LSHF, Type B, Length: xx in m

Strength members	Aramid Yarns
Outer jacket	LSZH
Color	Magenta (RAL4003)
Weight	96 kg/km
Outer Ø	9.5 ± 0.5 mm
Tensile Load	1500 N
Crush	700 N
Temperature range	-20°C to +70°C
Min. bending radius	10 x Ø Outer

FO Fiber

Type	Corning ClearCurve® 50/125µ OM4 multimode fiber
Optimized Data Rate over Distance	40/100 Gb over 170 m* 10 Gb/s over 550 m 1 Gb/s over 1100 m
Standard Compliance	ISO/IEC 11801: type OM4 fiber** IEC 60793-2-10: type A1a.3 fiber** TIA/EIA: 492AAAD ITU: ITU G651.1
*	Distances specified in the 40G/100G per IEEE 802.3ba standard are 150m on OM4 and 100m on OM3; Corning fibers are manufactured to tighter dispersion specifications and thereby support the extended distances shown in the table (assuming cable attenuation ≤3.0 dB/km and same 1.0 dB of connector loss for OM3 that the standard requires for OM4)
**	Assumes IEC draft standard is harmonized with 492AAAD which was approved by TIA

Optical Specifications

Bandwidth	High Performance EMB* (MHz.km): 4700 at 850 nm only Legacy Performance EMB** (MHz.km): 3500 at 850 nm / 500 at 1300 nm
Attenuation	At 850 nm max. ≤ 2.3 dB/km At 1300 nm max. ≤ 0.6 dB/km
Macrobend Loss	Mandrel Radius (mm): 37.2 / 15 / 7.5 Number of Turns: 100 / 2 / 2 Induced Attenuation (dB) at 850 nm: ≤ 0.05 / ≤ 0.1 / 0.2 Induced Attenuation (dB) at 1300 nm: ≤ 0.15 / ≤ 0.3 / ≤ 0.5
Numerical Aperture	0.200 ± 0.015
*	Ensured via miniEMBc, per TIA/EIA 455-220A and IEC 60793-1-49, for high performance laser-based systems (up to 10Gb/s)
**	OFL BW, per TIA/EIA 455-204 and IEC 60793-1-41, for legacy and LED-based systems (typically up to 100 Mb/s)

Dimensional Specifications

Core Diameter	50.0 ± 2.5 µm
Cladding Diameter	125.0 ± 1.0 µm
Core-Clad Concentricity	≤ 1.5 µm

tML[®] Xtended - FO Micro Distribution Trunk Cable both sides 8xMPO/MTP[®] w. Pins 96G50/125 μ OM4
LSHF, Type B, Length: xx in m

Cladding Non-Circularity	$\leq 1.0\%$
Core Non-Circularity	$\leq 5.0\%$
Coating Diameter	$242 \pm 5 \mu\text{m}$
Coating-Cladding Concentricity	$< 12 \mu\text{m}$

Environmental

Environmental Test	Test Condition	Induced Attenuation 850 nm & 1300 nm (dB/km)
Temperature Dependence	-60°C to +85°C	≤ 0.10
Temperature Humidity Cycling	-10°C to +85°C and 4% to 98% RH	≤ 0.10
Water Immersion	23°C \pm 2°C	≤ 0.20
Heat Aging	85°C \pm 2°C	≤ 0.20
Damp Heat	85°C at 85% RH	≤ 0.20
Operating Temperature Range	-60°C to +85°C	

Mechanical Specifications

Proof Test	The entire fiber length is subjected to a tensile stress ≥ 100 kpsi (0.7 GN/m ²).
Length	Fiber lengths available up to 17.6 km/spool.

Performance Characterizations

Refractive Index Difference	1%
Effective Group Index of Refraction	850 nm: 1.480 1300 nm: 1.479
Fatigue Resistance Parameter (nd)	20
Coating Strip Force	Dry: 0.6 lbs (2.7N) Wet: 14 days in 23°C water soak: 0.6 lbs (2.7N)
Chromatic Dispersion	Zero Dispersion Wavelength (λ_0): 1295 nm $\leq \lambda_0 \leq$ 1315 nm Zero Dispersion Slope (S_0): ≤ 0.101 ps/(nm ² *km)

Product variants & accessories

Art.-No.	Description
TML-MPP/MPP50I96G4Bxx	tML [®] Xtended - FO Micro Distribution Trunk Cable both sides 8xMPO/MTP [®] w. Pins 96G50/125 μ OM4 LSHF, Type B, Length: xx in m