

tML[®] - Fiber Optic TAP Module MPO/MTP[®] w. Pins 3x 9/125 μ OS2 40GBASE-LR4 50:50



tML[®] - tde Modular Link

tML[®] is a patented, modular cabling system consisting of the three key components module, trunk cable and rack mount enclosure. The system components are 100 percent manufactured, pre-assembled and tested in Germany. They enable plug-and-play installation on site – especially in data centres, but also in industrial environments – within the shortest possible time. Heart of the system are the rear MPO/MTP[®] and Telco connectors, which can be used to connect at least six or twelve ports at a time. Depending on the module configuration, transfer rates of up to 200G are currently possible with SR4. The fibre optic and TP modules can be used together in a module carrier with a very high port density. The tde offers its tML[®] cabling system as a proven tML[®] standard system and in the highly innovative variants tML[®] Xtended, tML[®] 24 System and now tML[®] 32 System for extreme scalability and very easy migration to higher transmission rates such as 40G, 100G, 200G and 400G.

The tML[®] - FO TAP Module is intended for the installation in the tML[®] Rack Mount Enclosure 1U (for 8 x Modules).



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

tML[®] - Fiber Optic TAP Module MPO/MTP[®] w. Pins 3x 9/125µ OS2 40GBASE-LR4 50:50

Technical Data

Entry	3 x MPO/MTP [®] Adapter with Pins (black) front
Exit	6 x MPO/MTP [®] Adapter with Pins (green) front
Tests	Interferometer, Insertion Loss, Return Loss and Visual Final Inspection; all measured values are electronically archived
	QS-Managementsystem ISO 9001, ISO 14001 and TL 9000

Box	Galvanized steel sheet
Front Panel	Stainless steel
Dimensions	110 x 108 x 20 mm

FO Adapters

Type	MPO/MTP [®]
Application	Singlemode OS2 APC
Design	without Flange
Connector style	SC Simplex
Key Orientation	Type A, Key up/down
Color	Green
Material	Plastic
Sleeve	--
Shutter	--
Standards	IEC 61754-7 TIA 604-5
Manufacturer	US Conec

FO Adapters

Type	MPO/MTP [®]
Application	Multimode
Design	without Flange
Connector style	SC Simplex
Key Orientation	Type A, Key up/down
Color	Black
Material	Plastic
Sleeve	--
Shutter	--
Standards	IEC 61754-7 TIA 604-5
Manufacturer	US Conec

FO Connectors

tML® - Fiber Optic TAP Module MPO/MTP® w. Pins 3x 9/125µ OS2 40GBASE-LR4 50:50

The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP® plug has a defined fiber height of 1 - 3.5µ. The max. adjacent fiber height difference is 0.2µm and for all fibers 0.3µm.

Connector

Type	MPO/MTP® APC Male Push Pull Locking with Elite Pins (green)
Ferrule	12 Fiber SM Elite® ferrule, PPS
Boot colour	Black
Temperature range	-40°C bis +75°C
Manufacturer	tde/US Conec

Optical Performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
9/125µ OS2	MPO/MTP®APC	1310 / 1550 nm	≤ 0.10 dB	0.25 dB	75 dB

FO Splitter

Type	Splitter
Port	1x2
Jumper Type	250 µ
Fiber Length	1 m
Operating Wavelength	1260 ~ 1650 nm
Max. Insertion Loss	4 dB
Uniformity	0.4 dB
Max. PDL	0.2 dB
WDL	0.3 dB
Min. Return Loss	55 dB
Min Directivity	55 dB
Operating temperature	-40°C to +85°C
Dimensions	4x4x40 mm (WxHxL)

Product variants & accessories

Art.-No.	Description
TML-M03MPP09E-TAP50	tML® - Fiber Optic TAP Module MPO/MTP® w. Pins 3x 9/125µ OS2 40GBASE-LR4 50:50
TML-M03MPP09E-TAP70	tML® - Fiber Optic TAP Module MPO/MTP® w. Pins 3x 9/125µ OS2 40GBASE-LR4 30:70
TML-M03MPP50G4TAP50	tML® - Fiber Optic TAP Module MPO/MTP® w. Pins 3x 50/125µ OM4 40GBASE-SR4 50:50
TML-M03MPP50G4TAP70	tML® - Fiber Optic TAP Module MPO/MTP® w. Pins 3x 50/125µ OM4 40GBASE-SR4 30:70