

AC POWER SUPPLY, ION 6-SLOT CHASSIS -SA Cord

Direct Attach Cables / Active Optical Cables

A simple to install, cost-effective and interoperable solution

Often used for data center short-reach interconnects, Direct Attach, Active Copper and Active Optical Cables are an indispensable part of any network.

Terminated with transceiver-style connectors, they are designed to be used in the same ports as a typical SFP+ or QSFP transceiver, with no need for adapters or converters. Our DAC and AOC cables offer compatibility with a huge range of vendors, enabling the connectivity you need within the Top of Rack and End of Row environments.

- 10G, 25G, 40G & 100G product solutions
- Seamless interoperability with network equipment
- Multi-code options enabling different OEM vendors at each end of the cable
- 4x breakout cables, 40G QSFP+ to 4x 10G SFP and 100G QSFP28 to 4x 25G SFP28
- Fast Delivery, Custom solutions
- Compatible with Over 90 Systems
- Savings of up to 70%

Redundant AC power supply for ION 6-Slot Chassis, 100 to 240 VAC input

Description

The IONPS6-A is an AC power supply module for the ION 6-slot chassis. The ION106-A chassis ships with one AC power supply, but the system can be made redundant with the use of the IONPS-A power supply module. The second power supply module works in a load-sharing mode, however a single power supply module can be used to power a fully loaded ION chassis. The IONPS6-A supports a universal power input voltage range of 100- 240 VAC.

Show product on manufacturers website: <https://www.lantronix.com/products/>



tde[®] trans data elektronik GmbH

Hausanschrift:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Vertriebsbüro:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

AC POWER SUPPLY, ION 6-SLOT CHASSIS -SA Cord

Artikelvarianten & Zubehör

Art.-Nr.	Beschreibung
IONPS6-A-SA	AC POWER SUPPLY, ION 6-SLOT CHASSIS -SA Cord