

tDF[®] - FO splice to patch HD module 6x LC APC Quad SM 3U/7HP with pigtailed 9/125 μ OS2 w. 5,0mm flex tube



tDF[®] - tde Distribution Frame (ODF)

tDF[®] is a modular Central Office solution with the highest packing density. At 46U, up to 4032 fibers can be terminated with LC. In developing the tde has taken primarily attention on the user-friendly installation. So the patented modules are fully be fitted from the front. A 19-inch sub rack occupies three height units and is equipped with twelve splice modules. Per sub rack, up to 288 fibers can be terminated with LC. The splices will be stored in standard splice cassettes. A unique feature of the splice module is the built-in loose tube over length management, which compared to conventional solutions saves an additional rack unit for the over length tray. The trunk cables are brought to the sub rack side and splitted there. This results in very short stripping lengths for the trunk cables. Due to the tML[®] compatibility also MPO/MTP[®] modules can be equipped in the same sub rack. The modular design of the tDF rack system offers maximum flexibility. The racks can be ordered customized completely preconfigured.

The tDF[®] HD module can be used only in combination with the tde HD patch cord.



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

tDF[®] - FO splice to patch HD module 6x LC APC Quad SM 3U/7HP with pigtails 9/125 μ OS2 w. 5,0mm flex tube

Technical Data

Pre-mounted	6 LC APC quad adapters 24 LC APC Fiber pigtails 09/125 μ OS2 24 Crimp Splice protectors 1 Splice cassettes 2 Splice holder 1 Splice cover 1,6m Flex tube
Alternative pre-mounted	TDF-M06-xxLCAQ9AS
xx	(01 - 06) quantity of adapters

FO Adapters

Type	LC Quad
Application	Singlemode OS2 APC
Design	with flange
Footprint	SC Duplex
Color	Green
Material	Plastic
Sleeve	Zirconia Straight Split
Shutter	--
Manufacturer	tde

FO Pigtails Standard

FO Connectors

Connector Type	LC APC Unibody Simplex
Housing	Plastic, Green
Ferrule	Zirconia Straight Split, Spring-loaded Axially
Ferrule Hole	125.5 μ
Ferrule Concentricity	$\leq 0.6 \mu$
Mating Cycles	500
Operating Temperature	-40°C up to +75°C
Strain Relief to	100 N
Manufacturer	tde

Optical performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
9/125 μ	LC APC	1550 nm	≤ 0.20 dB	0.45 dB	70 dB

tDF[®] - FO splice to patch HD module 6x LC APC Quad SM 3U/7HP with pigtailed 9/125µ OS2 w. 5,0mm flex tube

FO Cables

Tight Buffer	Low smoke (IEC 61034 and EN 50268) and free of halogens (LSOH)
	Non corrosive after IEC 60754-2 and EN 50267
	Flame resistant after IEC 60332-3C and EN 50266-2-4
	Completely dry design
	Free from metal, no grounding problems and potential differences
	Tight Buffer for simple and direct connector mounting

Characteristics

Fiber Count	1 (Tight Buffer)
Core-Ø	0.9 mm
Coreweight	1 kg/km
Min. Bending radius - Installation	30 mm
Min. Bending radius - Operation	30 mm
Removal	1500 mm
Fire load	0.15 MJ/m
Temperature range - Installation	-5 to +50°C
Temperature range - Operation	-20 to +60°C
Temperature range - Transport / Lagerung	-25 to +70°C

FO Fiber

Type	Corning Ultra SMF-28 [®] 09/125µ OS2 singlemode fiber
Maximum Attenuation	At 1310 nm max. 0.32 dB/km At 1383 nm max. 0.32 dB/km At 1490 nm max. 0.21 dB/km At 1550 nm max. 0.18 dB/km At 1625 nm max. 0.20 dB/km
Attenuation vs. Wavelength	Range: 1285 - 1330 nm; Ref. λ: 1310 nm; Max. Difference: 0.03 dB/km Range: 1525 - 1575 nm; Ref. λ: 1550 nm; Max. Difference: 0.02 dB/km
Macrobend Loss	Mandrel Radius: 10mm; Number of Turns: 1; Wavelength: 1550nm; Induced Attenuation: ≤ 0.50 dB Mandrel Radius: 10mm; Number of Turns: 1; Wavelength: 1625nm; Induced Attenuation: ≤ 1.5 dB Mandrel Radius: 15mm; Number of Turns: 10; Wavelength: 1550nm; Induced Attenuation: ≤ 0.05 dB Mandrel Radius: 15mm; Number of Turns: 10; Wavelength: 1625nm; Induced Attenuation: ≤ 0.30 dB Mandrel Radius: 25mm; Number of Turns: 100; Wavelength: 1310nm, 1550nm, 1625nm; Induced Attenuation: ≤ 0.01 dB
Point Discontinuity	Wavelength: 1310 nm; Point Discontinuity: ≤ 0.05 dB Wavelength: 1550 nm; Point Discontinuity: ≤ 0.05 dB
Cable Cutoff Wavelength (λ _{ccf})	λ _{ccf} ≤ 1260 nm
Mode-Field Diameter	At 1310 nm = 9.2 ± 0.4 µm At 1550 nm = 10.4 ± 0.5 µm
Dispersion	At 1550 nm = ≤ 18.0 [ps/(nm*km)] At 1625 nm = ≤ 22.0 [ps/(nm*km)] Zero Dispersion Wavelength (λ ₀): 1304 nm ≤ λ ₀ ≤ 1324 nm Zero Dispersion Slope (S ₀): ≤ 0.092 ps/(nm ² *km)

tDF[®] - FO splice to patch HD module 6x LC APC Quad SM 3U/7HP with pigtails 9/125 μ OS2 w. 5,0mm flex tube

Polarization Mode Dispersion (PMD)	PMD Link Design Value = ≤ 0.04 ps/ $\sqrt{\text{km}}$ Maximum Individual Fiber = ≤ 0.1 ps/ $\sqrt{\text{km}}$
------------------------------------	--

Dimensional Specifications

Fiber Curl	≥ 4.0 m radius of curvature
Cladding Diameter	125.0 ± 0.7 μm
Core-Clad Concentricity	≤ 0.5 μm
Cladding Non-Circularity	$\leq 0.7\%$
Coating Diameter	242 ± 5 μm
Coating-Cladding Concentricity	< 12 μm

Environmental Specifications

Environmental Test	Test Condition	Induced Attenuation 1310 nm, 1550 nm & 1625 nm
Temperature Dependence	-60°C to +85°C	≤ 0.05
Temperature Humidity Cycling	-10°C to +85°C up to 98% RH	≤ 0.05
Water Immersion	23°C \pm 2°C	≤ 0.05
Heat Aging	85°C \pm 2°C	≤ 0.05
Operating Temperature Range	-60°C to +85°C	

Mechanical Specifications

Proof Test	The entire fiber length is subjected to a tensile stress ≥ 100 kpsi (0.69 GPa).
Length	Fiber lengths available up to 63.0 km/spool.

Performance Characterizations

Core Diameter	8.2 μm
Numerical Aperture	0.14
Effective Group Index of Refraction	1310 nm: 1.4676 1550 nm: 1.4682
Fatigue Resistance Parameter (nd)	20
Coating Strip Force	Dry: 0.6 lbs (3N) Wet: 14 days room temperature: 0.6 lbs (3N)
Rayleigh Backscatter Coefficient (for 1 ns Pulse Width)	1310 nm: -77 dB 1550 nm: -82 dB

Product variants & accessories

Art.-No.	Description
TDF-M06-06LCAQ9AS-5	tDF [®] - FO splice to patch HD module 6x LC APC Quad SM 3U/7HP with pigtails 9/125 μ OS2 w. 5,0mm flex tube

tDF[®] - FO splice to patch HD module 6x LC APC Quad SM 3U/7HP with pigtails 9/125 μ OS2 w. 5,0mm flex tube

Art.-No.	Description
TDF-M06-06LCQ9S-5	tDF [®] - FO splice to patch HD module 6x LC PC Quad SM 3U/7HP with pigtails 9/125 μ OS2 w. 5,0mm flex tube
TDF-M06-06LCQ-G3S-5	tDF [®] - FO splice to patch HD module 6x LC Quad MM 3U/7HP with pigtails 50/125 μ OM3 w. 5,0mm flex tube
TDF-M06-06LCQ-G4S-5	tDF [®] - FO splice to patch HD module 6x LC Quad MM 3U/7HP with pigtails 50/125 μ OM4 w. 5,0mm flex tube